# Keysight Technologies 83059 Precision 3.5 mm Coaxial

Adapters DC - 26.5 GHz

Technical Overview





# Introduction

# **Outstanding Performance**

You don't have to sacrifice measurement integrity when using general purpose adapters and connector savers. The Keysight Technologies, Inc. 83059 instrument grade 3.5 mm coaxial adapters offer outstanding performance to 26.5 GHz. With SWR typically better than 1.05, these adapters are ideal for most connector saver and interconnect needs.

# **Applications**

Out-of-spec SMA and poor quality 3.5 mm connectors can cause considerable damage to expensive test port connectors. To help protect your test port connectors from damage, use 83059 adapters. These adapters offer test port safety without compromising accuracy.

You can use the 83059 adapters to perform adapter swap calibrations when testing non-insertable devices on network analyzers.

For general purpose test and measurement applications, the 83059 adapters offer far better performance than most instrument grade adapters available today.

### **Features**

- Low SWR
- Excellent repeatability
- Low loss
- Precision "instrument grade"
  3.5 mm coax connectors
- Ideal connector savers

### Convenient Kits

Damaged adapters can damage your test ports. The 83059 adapters are available in kits of three, packaged in protective foam to help reduce damage and are supplied in an attractive wooden box you can use to store them in so there's less chance of losing your adapters.

# Specifications


Specifications describe the instrument's warranted performance over the temperature range 0 to 55° C (except where noted). Supplemental Characteristics are intended to provide information useful in applying the instrument by giving typical but nonwarranted performance parameters. These are denoted as "typical," "nominal," or "approximate."

# Performance characteristics<sup>1</sup>

Model number	Connector type <sup>2</sup>	Frequency (GHz)	Typical min. return loss	Typical max. insertion loss <sup>3,4</sup>
83059A	3.5 mm (m-m)	DC - 26.5	− 32 dB	0.074 dB
83059B	3.5 mm (f-f)	DC - 26.5	- 32 dB	0.074 dB
83059C	3.5 mm (m-f)	DC - 26.5	- 32 dB	0.074 dB
83059K (kit)	3.5 mm (m-m) (f-f), (m-f)	DC - 26.5	- 32 dB	0.074 dB

- 1. Typical values are defined as 2 from the mean.
- 2. m = plug, f = jack
- 3. Typical measurements were taken from the f-f 83059B; they represent the worst case for the Keysight 83059 family.
- Insertion loss values were derived using a short circuit technique; values displayed are half the measured "round trin" values

"Instrument Grade" connectors are intended for use with precision test and measurement equipment where maintaining high performance through many connect/disconnect cycles is of paramount importance. They feature the traditional slotted female contacts, rather than the slotless design used by "Metrology Grade" connectors.



Dimensions in millimeters Net Weight: 14 Grams each

#### myKeysight

#### myKeysight

#### www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

#### www.axiestandard.org



AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.

#### www.lxistandard.org



LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.

#### www.pxisa.org



PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.

#### Three-Year Warranty



#### www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.

#### Keysight Assurance Plans



#### www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.

#### www.keysight.com/quality



Keysight Technologies, Inc. DEKRA Certified ISO 9001:2008 Quality Management System

## Keysight Channel Partners

#### www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

#### **Americas**

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

#### Asia Pacific

Australia China	1 800 629 485 800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

### Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-07-01-14)

