


**KEMET Part Number: PME271M610MR30**  
(P276CE104M275A)



Capacitor, film, 0.1 uF, +/-20% Tol, -40/+110C, Safety: X2, 275VAC, Lead Spacing=20.3 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	24	MAX
H	14	MAX
T	7.6	MAX
S	20.3	+/-0.5
LL	30	+5
F	0.8	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	250

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	0.1 uF
Rated Temperature:	110° C
Voltage AC:	275VAC
Tolerance:	+/-20%
Body Type:	Radial Molded
Dielectric:	Metallized Paper
Application:	Safety: X2
Temperature Range:	-40/+110C
Electrical Name (Other):	Self Resonant Frequency
Electrical Value (Other):	4.1
Electrical Units (Other):	mHz
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	600v/us

Agency Approvals	
Approvals:	ENEC,UL,cUL