
Keysight Technologies

30 MHz Function/Arbitrary Waveform Generators 33521A 1-Channel Function/Arbitrary Waveform Generator 33522A 2-Channel Function/Arbitrary Waveform Generator



Lowest jitter and total harmonic distortion in its class and true point-by-point arbitrary waveforms that are always alias-protected for exceptional accuracy



Achieving a new level of accuracy and flexibility

Everyday you're developing new technologies that are faster, more efficient, smaller, greener and require more accuracy than ever before. Keysight Technologies, Inc. 33500 Series function/arbitrary waveform generators offer the highest signal fidelity and implement a new breakthrough technology that provides you with the ability to generate more accurate arbitrary waveforms. With 10x better jitter than anything in their class, they offer unparalleled control of signal frequency for your most challenging measurements.

Key features

- 30 MHz sine, square, and pulse bandwidth cover more applications
- < 40 ps jitter and less than .04% total harmonic distortion for more precise signals
- 250 MSa/s, 16-bit sampling rate for higher time-resolution arbitrary waveforms
- True point-by-point arbitrary waveforms with sequencing for more accurate representation of user-defined signals
- Dual-channel mode with independent or coupled channels
- 1 MSa waveform memory standard, 16 MSa (optional) for more complicated arbitrary waveforms
- LXI Class C compliant
- Large, color, graphical display allows for simultaneous parameter setup and signal viewing/editing for intuitive operation
- Optional BenchLink Waveform Builder Pro software for custom user-defined waveforms

Signal fidelity

You depend upon the fidelity of generated signals to verify the development of your designs. The higher the fidelity of the generated signal, the more assurance the device under development will perform to your exacting standards. The 33500 Series function/arbitrary waveform generators have < 40 ps jitter for any signal - ten times better than existing function/arbitrary waveform generators. They provide 16-bit resolution, which is the highest resolution in their class. Combined with less than .04% total harmonic distortion and 250 MSa/s, 16-bit sampling, optional high-stability timebase and optional arbitrary waveform memory expansion, you now have access to an affordable new family of generators with unparallel signal fidelity.

Flexible signal generation

The 33521A and 33522A have the ability to create two-tone signals for dual-tone multi-frequency (DTMF) signal applications used in telecommunication device test. A feature specific to the 33522A generator is a flexible, dual-channel mode with frequency and amplitude coupling, differential channels, and combined output channels. This functionality is useful in applications where testing a device, such as a pacemaker, relies on the timing and interaction of two distinct signals to operate properly.

Point-by-point waveforms

The 33500 Series expands your signaling capability with true pointby-point arbitrary waveforms that are always alias-protected for exceptional accuracy. The 33521A and 33522A are first in their class to generate 30 MHz signals, including common waveforms, arbitrary waveforms and sophisticated modulated waveforms. Both models leverage proprietary technology to provide you with unprecedented input control when defining arbitrary waveforms. That control equates to the ability to define more complex point-by-point waveforms with sequencing.

User interface

A large, color, graphical display offers simultaneous parameter setup, signal viewing, and editing for easy operation. The 33500 Series is fully compliant with the LXI Class C specifications and offers USB 2.0 and 10/100 Base-T Ethernet connectivity for quick and easy connectivity to a PC or network. The 33500 Series also supports remote operation using a browser to connect to a built-in Web page. GPIB is offered as an optional interface.

Optional 33503A BenchLink Waveform Builder Pro Softrware

Benchlink Waveform Builder Pro is ideal for R&D engineers characterizing new designs and test system engineers validating production units. The software is a Microsoft Windows-based program that provides easy-to-use creation tools, such as an equation editor, waveform math and drawing tools, which can be used to create custom signals. It features a standard function library, waveform sequencer, and filters and; as well as windowing functions that allow you to easily modify and further refine your waveform. A library of built-in signals supports fast creation of more complex waveforms. With BenchLink Waveform Builder Pro, you gain access to advanced signal creation and editing capabilities, without requiring hours of programming. The result is quicker, easier creation of custom waveforms, coupled with deeper analysis insight into your signals. For additional information and to download a 30-day trial version of the software, visit: www.keysight.com/find/33503

Specifications

Unless otherwise stated, all specifications apply with a 50 Ω resistive load and auto range ON.

Instrument characteristics

Models & options	
33521A	1-channel
33522A	2-channel
Option 002	Increases arbitrary waveform memory to 16 MSa/channel
Option 010	OCXO timebase for ultra-high stability
Option 400	GPIB interface
Waveforms	
Standard	Sine, square, ramp, pulse, triangle, Gaussian noise, PRBS (Pseudorandom Binary Sequence), DC
Built-in arbitrary	Cardiac, exponential fall, exponential rise, Gaussian pulse, Haversine, Lorentz, D-Lorentz, negative ramp, sinc
User-defined arbitrary	Up to 1 MSa (16 MSa with Option 002) with multi-segment sequencing
Operating modes & modulation types	
Operating modes	Continuous, modulate, frequency sweep, burst, output gate
Modulation types	AM, FM, PM, FSK, BPSK, PWM, Sum (carrier + modulation)

Waveform characteristics

Sine			
Frequency range	1 μHz to 30 MHz, 1-μHz reso	ution	
Amplitude flatness (spec) ^{1, 2}	< 100 kHz:	± 0.10 dB	
(relative to 1 kHz)	100 kHz to 5 MHz:	± 0.15 dB	
	5 to 20 MHz:	± 0.30 dB	
	20 to 30 MHz:	± 0.40 dB	
Harmonic distortion (typ) ^{2, 3}	< 20 kHz:	< -70 dBc	
	20 to 100 kHz:	< -65 dBc	
	100 kHz to 1 MHz:	< -50 dBc	
	1 to 20 MHz:	< -40 dBc	
	20 to 30 MHz:	< -35 dBc	
THD (typ)	20 Hz to 20 kHz:	< 0.04%	
Non-harmonic spurious (typ) ^{2, 3}	Standard: < –75 dBc, increas	ng +20 dB/decade above 2 MHz	
	Option 010: < -75 dBc, increa	sing +20 dB/decade above 10 MHz	
	(or < –100 dBm, whichever is g	greater, below 500 MHz)	
Phase noise (SSB) (typ)	Standard	Option 010	
1 kHz offset:	-105	–110 dBc/Hz	
10 kHz offset:	–115	–125 dBc/Hz	
100 kHz offset:	-125	–135 dBc/Hz	

Waveform characteristics, *continued*

Square & pulse	
Frequency range	1 μHz to 30 MHz, 1 μHz resolution
Rise and fall times (nom)	Square: 8.4 ns, fixed Pulse: 8.4 ns to 1 μ s, independently variable, 100-ps or 3-digit resolution
Overshoot (typ)	
Duty cycle	0.01% to 99.99% ⁸
Pulse width	16 ns minimum, 100-ps resolution
Jitter (cycle-to-cycle, typ)	< 40 ps rms
Ramp & triangle	
Frequency range	1 μ Hz to 200 kHz, 1 μ Hz resolution
Ramp symmetry	0.0% to 100.0%, 0.1% resolution (0% is negative ramp, 100% is positive ramp, 50% is Triangle)
Nonlinearity (typ)	< 0.05% from 5% to 95% of the signal amplitude
Gaussian noise	
Bandwidth (typ)	1 mHz to 30 MHz, variable
Crest factor (nom)	4.6
Repetition period	> 50 years
Pseudorandom binary sequence (PRBS)	
Bit rate	1 mbps to 50 Mbps, 1 mbps resolution
Sequence length	2 ^m -1, m=7, 9, 11, 15, 20, 23
Rise and fall times (nom)	8.4 ns to 1 μ s, variable, 100-ps or 3-digit resolution

Arbitrary waveform characteristics

General	
Waveform length	8 Sa to 1 MSa (16 MSa with Option 002) in increments of 1 sample
Sample rate	1 μSa/s to 250 MSa/s, 1 μSa/s resolution
Voltage resolution	16 bits
Bandwidth (–3 dB, nom)	Filter Off: 40 MHz "Normal" Filter On: 0.27 x (Sample Rate) "Step" Filter On: 0.13 x (Sample Rate)
Rise and fall time	0.35 / Bandwidth (10 ns min) with "Normal" or "Step" filter On
Settling time (typ)	< 200 ns to 0.5% of final value
Jitter (typ)	Filter Off: < 40 ps rms "Normal" or "Step" filter On: < 5 ps

Arbitrary waveform characteristics, *continued*

Waveform sequencing	
Operation	Individual arbitrary waveforms (segments) can be combined into user-defined lists (sequences) to form longer, more complex waveforms. Each sequence step specifies whether to repeat the associated segment a certain number of times, to repeat it indefinitely, to repeat it until a Trigger event occurs, or to stop and wait for a Trigger event. Additionally, the behavior of the Sync output can be specified in each step. To improve throughput, up to 32 sequences totalling up to 1,024 segments can be pre-loaded into volatile memory.
Segment length	8 Sa to 1 MSa (16 MSa with Option 002) in increments of 1 sample
Sequence length	1 to 512 steps
Segment repeat count	1 to 1x10 ⁶ , or infinite
Output characteristics	
Isolation	
Outputs	Connector shells for channel output(s), Sync, and Mod In are connected together but isolated from the instrument's chassis. Maximum allowable voltage on isolated connector shells is ±42 Vpk
Signal output	
Output impedance (nom)	50 Ω
On, off, inverted	User-selectable for each channel
Voltage limit	User-definable V_{\rm MAX} and V_{\rm MIN} limits
Overload protection	Output turns off automatically when an overload is applied Instrument will tolerate a short-circuit to ground indefinitely
Amplitude	
Range	1 mVpp to 10 Vpp into 50 Ω 2 mVpp to 20 Vpp into open circuit
Resolution	4 digits
Units	Vpp, Vrms, or dBm, selectable
Accuracy ^{1,2} (spec)	±1% of setting ±1 mVpp at 1 kHz
DC offset	
Range ⁵	±(5 VDC - Peak AC) into 50 Ω ±(10 VDC - Peak AC) into open circuit
Resolution	4 digits
Units	VDC
Accuracy ^{1,2} (spec)	±1% of Offset setting ±0.25% of Amplitude setting ±2mV

Frequency accuracy

Standard freqeuncy reference (s	ec)	
1 year, 23 °C ± 5 °C	±1 ppm of setting ± 15 pHz	
1 year, 0 °C to 55 °C	±2 ppm of setting ± 15 pHz	
High-stability frequency refere	ce (spec): Option 010	
1 year, 0 °C to 55 °C	±0.1 ppm of setting ± 15 pHz	

Modulation types and operating modes

Carrier	AM	FM	PM	FSK	BPSK	PWM	Sum	Burst	Sweep
Sine and Square	٠	٠	•	•	•		•	•	•
Pulse	•	•	٠	•	•	٠	•	•	٠
Triangle and Ramp	•	•	٠	•	•		•	•	•
Gaussian Noise	•						•	● ^a	
PRBS	•	•	٠				•	•	
Single ARB	•		● ^b		● ^b		•	•	
Sequenced ARB	•						•		

a. Gated burst only. b. Applies to sample clock, not whole waveform.

Modulating signals

Carrier	Sine	Square	Triangle / Ramp	Noise	PRBS	ARB	External
Sine	•	•	•	•	•	•	•
Square and Pulse	•	٠	•	٠	•	٠	•
Triangle and Ramp	•	٠	•	٠	•	٠	•
Gaussian Noise	٠	٠	•		•	٠	•
PRBS	٠	•	•	٠		٠	•
ARB	٠	•	•	٠	•		•

Modulation characteristics

Amplitude modulation (AM)	
Source	Internal or external, or either channel with 33522A
Туре	Full-carrier or double-sideband suppressed-carrier
Depth ¹	0% to 120%, 0.01% resolution
Frequency modulation (FM) ⁷	
Source	Internal or external, or either channel with 33522A
Deviation	1 μ Hz to 15 MHz, 1 μ Hz resolution
Phase modulation (PM)	
Source	Internal or external, or either channel with 33522A
Deviation	0° to 360°, 0.1° resolution
Frequency shift key modulation (FS	K) ⁷
Source	Internal timer or ext trig connector
Mark & space	Any frequency within the carrier signal's range
Rate	0 Hz to 1 MHz
Binary phase shift key modulation	(BPSK)
Source	Internal timer or ext trig connector
Phase shift	0° to 360°, 0.1° resolution
Rate	0 Hz to 1 MHz
Pulse width modulation (PWM)	
Source	Internal or external, or either channel with 33522A
Deviation ⁸	0% to 100% of pulse width, 0.01% resolution
Additive modulation (Sum)	
Source	Internal or external, or either channel with 33522A
Ratio ⁶	0% to 100% of carrier amplitude, 0.01% resolution

Burst⁹

Duist	
Туре	Counted or gated
Count	1 to 1x10 ⁸ cycles, or infinite
Gated	Produces complete cycles while ext trig is asserted
Start/stop phase ⁴	–360° to 360°, 0.1° resolution
Trigger source	Internal timer or ext trig connector
Marker	Adjustable to any cycle; indicated by the trailing edge of the Sync pulse
Sweep ⁷	
Туре	Linear, Logarithmic, List (up to 128 user-defined frequencies)
Operation	Linear and Logarithmic sweeps are characterized by a Sweep time (during which the fre- quency changes smoothly from Start to Stop), a Hold time (during which the frequency stays at the Stop frequency), and a Return time (during which the frequency changes smoothly from Stop to Start). Returns are always linear.
Direction	Up (Start freq < Stop freq) or Down (Start freq > Stop freq)
Start and stop frequencies	Any frequency within the waveform's range
Sweep time	Linear: 1 ms to 3600 s, 1 ms resolution; 3601 s to 250,000 s, 1 s resolution Logarithmic: 1 ms to 500 s
Hold time	0 s to 3600 s, 1 ms resolution
Return time	0 s to 3600 s, 1 ms resolution
Trigger source ¹⁰	Immediate (continuous), external, single, bus, or timer
Marker	Adjustable to any frequency between Start and Stop for Linear and Logarithmic types or any frequency in the list for List type; indicated by the trailing edge of the sync pulse

Internal timer for FSK, BPSK, BURST, and SWEEP

Range	1 µs to 8000s, 6-digit or 4 ns resolution
Nallye	

2-channel characteristics (33522A only)

Operating modes Independent, coupled parameter(s), combined (Ch 1 + Ch 2), Equal (Ch 2 = Ch 1), or differential (Ch 2 = -Ch 1)			
Parameter coupling	None, frequency (ratio or difference) and/or amplitude and DC offset		
Relative phase	0° to 360°, 0.1° resolution		
Skew (typ)	< 200 ps (when performing identical operations)		
Crosstalk (typ)	< -85 dB		

Sync/marker output

Front-panel BNC, isolated from chassis	
Sync, sweep marker, burst marker, or arbitrary waveform marker	
Channel 1 or channel 2	
Normal or inverted	
3 Vpp into open circuit, 1.5 Vpp into 50 Ω	
50 Ω	
16 ns	

External trigger/gate

maximum (as input) n) into 50 Ω (as output)	
•	
•	
10 k $\Omega,$ DC-coupled (as input) 50 Ω (as output)	
l trigger events	

Modulation input

Connector	Rear-panel BNC, isolated
Assignment	Channel 1, Channel 2, or both
Voltage level	±5 V full-scale
Input impedance (nom)	5 k Ω
Bandwidth (–3 dB, typ)	0 Hz to 100 kHz

Frequency reference input

Connector	Rear-panel BNC, isolated from chassis and all other connectors	
Reference selection	Internal, external, or auto	
Frequency range	Standard: 10 MHz ± 20 Hz Option 010: 10 MHz ± 1 Hz	
Lock time (typ)	<2 s	
Voltage level	200 mVpp to 5 Vpp	
Input Impedance (nom)	1 k Ω 20 pF, AC-coupled	

Frequency reference output

Connector	Rear-panel BNC, chasis-referenced	
Frequency (nom)	10 MHz	
Output impedance (nom)	50 Ω, AC-coupled	
Level (nom)	0 dBm, 632 mVpp into 50 Ω	

Real-time clock/calendar

Set and read	Year, month, day, hour, minute, second
Battery	CR-2032 coin-type, replacable, >5-year life (typ)

Programming times (meas.)

Configuration change speed

	LAN (socket)	LAN (VXI-11)	USB 2.0	GPIB	
Change function	5 ms	6 ms	5 ms	5 ms	
Change frequency	2 ms	3 ms	2 ms	3 ms	
Change amplitude	20 ms	20 ms	19 ms	22 ms	
Select user arb (16 k)	9 ms	11 ms	9 ms	9 ms	

Arbitrary waveform download speed to volatile					
(binary transfer)	LAN (socket)	LAN (VXI-11)	USB 2.0	GPIB	
4 k sample	6 ms	18 ms	8 ms	39 ms	
1 M sample	1.3 s	2.6 s	13 s	9.1 s	

Memory

Aribtrary waveform and instrume	ent state memory		
Volatile	1x10 ⁶ samples per channel or 16x10 ⁶ samples per channel (Option 002) 512 sequence steps per channel		
Non-volatile	File sytem file space is limited to 64 MB (~32 MSa of arbitrary waveform records)		
Instrument state			
Store / Recall	User defined instrument states		
Power Off	Power Off state automatically saved		
Power On	Factory default settings or last power off settings		
USB File System			
Front-panel port	USB 2.0 high-speed mass storage (MSC) class device		
Capability	Read or write instrument configuration settings, instrument states and user arbitrary waveform and sequence files.		
Speed	10 MB/s (nom)		

General characteristics

Computer interfaces			
LXI- C (rev1.3)	10/100Base-T Ethernet (Sockets & VXI-11 protocol) USB2.0 (USB-TMC488 protocol) GPIB/IEEE-488.1, IEEE-488.2		
Web user interface	Remote operation and monitoring		
Programming language	SCPI-1999, IEEE-488.2 Keysight 33210A / 33220A compatibile		
Graphical display	4.3" Color TFT WQVGA (480x272) with LED backlight		
Mechanical			
Size	261.1 mm W x 103.8 mm H x 303.2 mm D (with bumpers installed) 212.8 mm W x 88.3 mm H x 272.3 mm D (with bumpers removed) 2U x 1/2 rack width		
Weight (nom)	3.3 kg (7.2 lbs)		
Environmental			
Storage temperature	–40 to 70 °C		
Warm-up time	1 hour		
Operating environment	EN61010, polution degree 2; indoor locations		
Operating temperature	0 to 55 °C		
Operating humidity	5% to 80% RH, non-condensing		
Operating altitude	Up to 3000 meters		
Regulatory			
Safety	Complies with European Low Voltage Directive and carries the CE-marking. Conforms to UL 61010-1, CSA C22.2 61010-1, and IEC 61010-1:2001		
EMC	Complies with European EMC Directive for test and measurement products. - IEC/EN 61326-1 - CISPR Pub 11 Group 1, class A - AS/NZS CISPR 11 - ICES/NMB-001 Complies with Australian standard and carries C-Tick mark This ISM device complies with Canadian ICES-001. Cet appareil ISM est conforme a la norme NMB-001 du Canada		
Acoustic Noise (nom)	SPL 35 dB(A)		
Line power			
Voltage	100 V - 240 V 50/60 Hz -5%, +10% 100 V - 120 V 400 Hz ±10%		
Power consumption (typ)	< 45 W, < 130 VA		
Warranty	1 year standard, 3 years optional		

Definitions

Specification (spec)

The warranted performance of a calibrated instrument that has been stored for a minimum of 2 hours within the operating temperature range of 0 - 55 °C and after a 45-minute warm up period. All specifications include measurement uncertainty and were created in compliance with ISO-17025 methods.

Data published in this document are specifications (spec) only where specifically indicated.

Typical (typ)

The characteristic performance, which 80% or more of manufactured instruments will meet. This data is not warranted, does not include measurement uncertainty, and is valid only at room temperature (approximately 23 °C).

Nominal (nom)

The mean or average characteristic performance, or the value of an attribute that is determined by design such as a connector type, physical dimension, or operating speed.

This data is not warranted and is measured at room temperature (approximately 23 °C).

Measured (meas)

An attribute measured during development for purposes of communicating the expected performance. This data is not warranted and is measured at room temperature (approximately 23 °C).

Accuracy

Represents the traceable accuracy of a specified parameter. Includes measurement error and timebase error, and calibration source uncertainty.

Random measuremet errors are combined using the root-sum-square method and are multiplied by M for the desired Confidence Level. Systematic errors are added linearly and include time skew errors, trigger timing errors, and timebase errors as appropriate for each measurement type.

Confidence level

For 99% Confidence use k = 2.5 in accuracy calculations. For 95% Confidence use k = 2.0 in accuracy calculations.

- 1. Add 1/10th of the output amplitude and offset accuracy specification per °C for operation at temperatures beyond 23 °C ± 5 °C.
- 2. Auto range ON.
- 3. DC Offset set to zero.
- 4. Limited to arbitrary waveforms that are < 1 million points; phase resolution limited by number of points in arbitrary waveforms < 3,600 points.
- 5. Output noise is typically 20 dB lower when (DC + Peak AC) < 320 mV (into 50 Ω) or 640 mV (into open circuit).
- 6. Subject to maximum output voltage limits.
- 7. All frequency changes are phase-continuous.
- 8. Subject to pulse width limits.
- 9. Counted Burst operation is not allowed for Gaussian Noise.
- 10. External trigger only for sweep time > 8000 sec.

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.



LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.



Keysight Assurance Plans www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



www.keysight.com/quality

Keysight Technologies, Inc. DEKRA Certified ISO 9001:2008 Quality Management System

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/33500

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia 1 800 629 485 China 800 810 0189 800 938 693 Hong Kong India 1 800 112 929 Japan 0120 (421) 345 080 769 0800 Korea Malaysia 1 800 888 848 1 800 375 8100 Singapore Taiwan 0800 047 866 Other AP Countries (65) 6375 8100

Europe & Middle East

United Kingdom

For other unlisted countries: www.keysight.com/find/contactus (BP-07-01-14)

0800 0260637



This information is subject to change without notice. © Keysight Technologies, 2011 - 2014 Published in USA, August 1, 2014 5990-5914EN www.keysight.com