



## Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 5

Loctite 2700 250ml EGFD

sds no. : 340671

V002.1

Revision: 08.12.2011

printing date: 07.10.2013

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

**Product identifier:**

Loctite 2700 250ml EGFD

**Relevant identified uses of the substance or mixture and uses advised against:**

Intended use:

Anaerobic Adhesive

**Details of the supplier of the safety data sheet:**

Henkel Limited

2 Bishop Square Business Park

AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933

Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

**Emergency Telephone Number:**

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

**Classification of the substance or mixture:**

**Classification (DPD):**

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

**Label elements (DPD):**

Risk phrases:

Not classified as hazardous.

**Other hazards:**

Not classified as hazardous.

### SECTION 3: Composition/information on ingredients

**General chemical description:**

Anaerobic adhesive

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

**Declaration of ingredients according to DPD (EC) No 1999/45:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

#### SECTION 4: First aid measures

**Description of first aid measures:**

**Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**

Rinse with running water and soap.  
Seek medical advice.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

**Ingestion:**

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.  
Seek medical advice.

**Indication of any immediate medical attention and special treatment needed:**

See section: Description of first aid measures

#### SECTION 5: Firefighting measures

**Combustion behaviour:**

Non flammable product (flash point is greater than 100°C (CC))

**Extinguishing media:**

**Suitable extinguishing media:**

Carbon dioxide, foam, powder

**Special hazards arising from the substance or mixture:**

Oxides of carbon.

Trace amounts of toxic and/or irritating fumes may be released and the use of breathing apparatus is recommended.

**Advice for firefighters:**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

#### SECTION 6: Accidental release measures

**Personal precautions, protective equipment and emergency procedures:**

Avoid skin and eye contact.

**Environmental precautions:**

Do not let product enter drains.

**Methods and material for containment and cleaning up:**

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

**Reference to other sections:**

See advice in chapter 8

#### SECTION 7: Handling and storage

**Precautions for safe handling:**

Use only in well-ventilated areas.

Avoid skin and eye contact.

Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

**Hygiene measures:**

- Wash hands before work breaks and after finishing work.
- Do not eat, drink or smoke while working.
- Good industrial hygiene practices should be observed.

**Conditions for safe storage, including any incompatibilities:**

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

**Specific end use(s):**

Anaerobic Adhesive

**SECTION 8: Exposure controls/personal protection****Control parameters:**

Valid for  
Great Britain

None

**Exposure controls:****Respiratory protection:**

Use only in well-ventilated areas.

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Wear protective glasses.

**Skin protection:**

Wear suitable protective clothing.

**SECTION 9: Physical and chemical properties****Information on basic physical and chemical properties:**

Appearance	liquid fluorescent green
Odor	characteristic
pH	No data available / Not applicable
Initial boiling point	> 149 °C (> 300.2 °F)
Flash point	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Vapour pressure	0,13 mbar
Density ( )	1,1 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable

Explosive properties	No data available / Not applicable
Solubility (qualitative)	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**Other information:**

No data available / Not applicable

### SECTION 10: Stability and reactivity

**Reactivity:**

Peroxides.

**Chemical stability:**

Stable under recommended storage conditions.

**Possibility of hazardous reactions:**

See section reactivity

**Conditions to avoid:**

Stable under normal conditions of storage and use.

### SECTION 11: Toxicological information

**General toxicological information:**

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**Oral toxicity:**

May cause irritation to the digestive tract.

**Inhalative toxicity:**

May cause irritation to respiratory system.

**Skin irritation:**

Prolonged or repeated contact may cause skin irritation.

**Eye irritation:**

May cause mild irritation to the eyes.

### SECTION 12: Ecological information

**General ecological information:**

Do not empty into drains / surface water / ground water.

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**Mobility:**

Cured adhesives are immobile.

### SECTION 13: Disposal considerations

**Waste treatment methods:**

**Product disposal:**

Dispose of in accordance with local and national regulations.  
Contribution of this product to waste is very insignificant in comparison to article in which it is used

**Disposal of uncleaned packages:**

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.  
Disposal must be made according to official regulations.

**Waste code**

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

### SECTION 14: Transport information

**General information:**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

### SECTION 15: Regulatory information

**Safety, health and environmental regulations/legislation specific for the substance or mixture:**

VOC content (1999/13/EC)	< 3 %
-----------------------------	-------

### SECTION 16: Other information

**Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and its subsequent amendments, and Commission Directive 1999/45/EC.