


Jigsaw Blades

Bi-metal



Precision milled teeth, 8% cobolt HSS cutting edge. High wear resistance for longer life and tooth sharpness for increased productivity and faster cutting. 2 blades per pack.

LENOX

489527

Part Number	Size(mm)	Size(in)	Teeth Per in	Application	Order Code	Price Each
20305-BT4065S	114 x 10 x 1.3	4 1/2 x 5/8 x 0.050	6	Fast, rough cutting in wood and composition material: 5/8-in (10mm-50mm) thick.	138-2268	
20306-BT410S	114 x 10 x 1.3	4 1/2 x 5/8 x 0.050	10	Woods 1/4-2in (6-50mm) thick. All steels 1/8-1/2in (3.2-13mm). Soft metals: 1/8-1in (3.2-25mm).	138-2269	
20313-BT450S	100 x 8 x 1.5	4 x 5/16 x 0.058	10	Ground teeth for fast, smooth cuts in wood, plastic and composition material: 5/16-1 1/2in (5-38mm) thick.	138-2270	
20314-BT450SR	100 x 8 x 1.5	4 x 5/16 x 0.058	10	Ground teeth for chip-free down cutting in formica, laminate and plastic 3/16-1 1/2in (5-38mm).	138-2271	
20302-BT318S	75 x 10 x 0.9	3 x 5/8 x 0.037	18	Stainless steel, structural steel: (1.5-5mm). Non ferrous metal: 1/16-5/16in (1.5-8mm).	138-2272	
20308-BT518S	135 x 10 x 1.3	5 1/4 x 5/8 x .050	18	Stainless steel, structural steel: (1.5-5mm). Non ferrous metal: 1/16-5/16in (1.5-8mm)	138-2274	
20303-BT324S	75 x 10 x 0.9	3 x 5/8 x 0.037	24	Stainless steel, sheet metal: < 1/8in (3.2mm) thick. Non ferrous metal < 1/4in (6mm) thick.	138-2273	