

MICRO-OHMMETERS 200A Digital











►SPECIFICATIONS

MODEL	6292
ELECTRICAL	
Test Current Range	Programmable from 5 to 200A (True DC
Resistance Range	0.1 μ Ω to 2 m Ω
	2 to $200 m\Omega$
	200m Ω to 1Ω
Accuracy	\pm 1% of reading from 50µ Ω to 1 Ω
Resolution	$0.1\mu\Omega$ to $2m\Omega < 0.1\mu\Omega$
	2 to $200 \text{m}\Omega < 10 \mu\Omega$
	$200 m\Omega$ to $1\Omega < 1 m\Omega$
Output Voltage	100Vac: 4.2V @ 200A
	220VAC: 8.6V @ 200A
Max. Load Resistance	100Vac: 20mΩ @ 200A
	220Vac: $42m\Omega$ @ 200A
Measurement Method	Four-terminal, Kelvin-type
Adjustable Test Time	5 to 120 seconds or unlimited
Memory	Stores up to 8000 measurements
Power Supply	100 to 240Vac, 50/60Hz













▶ FEATURES

- Programmable test currents from 5 to 200A
- Programmable test duration from 5 to 120 sec
- BSG Ground Test with optional current probe
- Accurately measures low contact resistance with test currents up to 200A
- Measures resistances from $0.1\mu\Omega$ to 1Ω
- Low resolution of 0.1μΩ
- Cooling system to improve the number of sequential tests that can be performed
- Backlit display
- · Measures objects with both sides grounded
- Stores up to 8000 test results
- Direct printout of measurement results using DataView® software and a PC
- Rugged, light-weight and water-resistant case

► PRODUCT INCLUDES

Set of 20 ft Kelvin test leads w/C clamp, ground lead (green) with clamp, 5 ft USB cable, 110V US power cord and 12A fuse (5x20mm)

USB Stick

Quick start user guide, and USB stick supplied with DataView® software and user manual







►ACCESSORIES

► Current Probe Model MR6292 Catalog #2129.86 (optional)



CATALOG NO.	DESCRIPTION	
2129.83	Micro-Ohmmeter Model 6292 (200A, manual and DataView® software)	
Accessories (Optio	nal)	
2129.86	Current Probe Model MR6292	
2129.87	Lead – Set of 2, 50 ft., Color-coded Kelvin Leads w/C-clamp	

