

Material Declaration for R40-300XX02

Product Information	
Part Number:	R40-300XX02
Part Description:	M4 M/F Spacer
Part Weight (g):	See table

Process Data	
Peak Reflow (Deg. C)	Not applicable
MSL	1
Lead Finish	Not applicable
RoHS Compliant Mark	n/a
Availability Date	Now
RoHS Compliant? (Y/N)	Yes

Part Number	Part Weight (g)	Base Material - Brass								Plating	Homogeneous Material Location
		Copper	Zinc	Lead	Iron	Tin	Nickel	Aluminium	Impurities	Nickel	Substance Name
		7440-50-8	7440-66-6	7439-92-1	7439-89-6	7440-31-5	7440-02-0	7429-90-5		7440-02-0	CAS #
		3	3	2	Max	Max	Max	Max	Max	20	Tolerance (%)
	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	
R40-3000602	2.494	1.446	0.972	0.075	0.0075	0.0075	0.0075	0.0012	0.005	0.00132	
R40-3000702	2.768	1.604	1.079	0.083	0.0083	0.0083	0.0083	0.0014	0.0055	0.00145	
R40-3000802	3.041	1.763	1.185	0.091	0.0091	0.0091	0.0091	0.0015	0.0061	0.00158	
R40-3000902	3.314	1.921	1.292	0.099	0.0099	0.0099	0.0099	0.0017	0.0066	0.00171	
R40-3001002	3.587	2.079	1.398	0.108	0.0108	0.0108	0.0108	0.0018	0.0072	0.00184	
R40-3001102	3.853	2.234	1.502	0.116	0.0116	0.0116	0.0116	0.0019	0.0077	0.00198	
R40-3001202	4.177	2.422	1.628	0.125	0.0125	0.0125	0.0125	0.0021	0.0084	0.00207	
R40-3001302	4.448	2.579	1.734	0.133	0.0133	0.0133	0.0133	0.0022	0.0089	0.00218	
R40-3001402	4.811	2.789	1.876	0.144	0.0144	0.0144	0.0144	0.0024	0.0096	0.00226	
R40-3001502	5.174	3	2.017	0.155	0.0155	0.0155	0.0155	0.0026	0.0103	0.00233	
R40-3001602	5.537	3.21	2.159	0.166	0.0166	0.0166	0.0166	0.0028	0.0111	0.00241	
R40-3001802	6.263	3.631	2.441	0.188	0.0188	0.0188	0.0188	0.0031	0.0125	0.00256	
R40-3002002	6.989	4.052	2.725	0.21	0.021	0.021	0.021	0.0035	0.014	0.00271	
R40-3002502	8.803	5.104	3.432	0.264	0.0264	0.0264	0.0264	0.0044	0.0176	0.00308	
R40-3003002	10.618	6.156	4.139	0.318	0.0318	0.0318	0.0318	0.0053	0.0212	0.00345	
R40-3003502	12.433	7.209	4.847	0.373	0.0373	0.0373	0.0373	0.0062	0.0249	0.00382	
R40-3004002	14.247	8.261	5.555	0.427	0.0427	0.0427	0.0427	0.0071	0.0285	0.0042	
R40-3004602	16.424	9.523	6.404	0.493	0.0493	0.0493	0.0493	0.0082	0.0328	0.00464	
R40-3006302	22.594	13.101	8.809	0.678	0.0678	0.0678	0.0678	0.0113	0.0452	0.00591	

Prepared by:



Miss Wendy Jane Bourne, BEng
 RoHS Compliance Project Manager
 leadfree@harwin.co.uk

On behalf of:

