



Description

- Standard 7 x 5mm crystal oscillator
Ceramic package with a seam sealed metal lid, hermetically sealed
- Model CFPS-73
- Model Issue number 12

Frequency Parameters

- Frequency 24.0MHz
- Frequency Tolerance @ 25°C INCLUSIVE
- Frequency Stability $\pm 50.00\text{ppm}$
- Operating Temperature Range -40.00 to 85.00°C
- Ageing $\pm 3\text{ppm}$ per year max

Electrical Parameters

- Supply Voltage 3.3V
- Supply Voltage Tolerance $\pm 10\%$
- Current Draw 12mA max

Output Details

- Output Compatibility HCMOS
- Output Load 50pF max
- Rise and Fall time 10ns max
- Duty Cycle 45/55

Output Control

- Logic '1' (>70% VS) to pad 1 enables oscillator output
- Logic '0' (<30% VS) to pad 1 disables oscillator output; the oscillator output goes to the high impedance state
- No connection to pad 1 enables oscillator output
- Standby Current: 10 μA max

Environmental Parameters

- Shock: MIL-STD-202, Method 213, Condition E
- Vibration: MIL-STD-883, Method 2007, Condition A
- Storage Temperature Range: -55 to 125°C

Compliance


- RoHS Status Compliant
- REACH Status Compliant

Packaging


- Pack Type: Reel Tape and reel in accordance with EIA-481-D
 - Pack Size 1,000
 - Alternative packing option available
- This document is correct at the time of printing; please contact your local office for the latest version.*



Outline (mm)




- Pad Connections
- Standby Operation
 - GND
 - Output
 - +Vs




Underside View

Solder Pad Layout



Test Circuit



* Inclusive of jigging and equipment capacitance

Sales Office Contact Details:

UK: +44 (0)1460 270200

Germany: +49 (0)7264 9145-62

France: +33 (0)5 34 50 91 18


USA: +1 408.273.4530

Email: info@iqdfrequencyproducts.com


Web: www.iqdfrequencyproducts.com



Wave Form



Phaise Noise / Jitter



Sales Office Contact Details:

UK: +44 (0)1460 270200

Germany: +49 (0)7264 9145-62

France: +33 (0)5 34 50 91 18

USA: +1 408.273.4530

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com