



Soldering Tips - Weller

C SERIES

COMPATIBLE STATIONS:Weller WTCPT, Weller WTCPTD, Weller WTCPTFE, Weller WTCPN, Weller WTCPS, Weller TC201T, Weller TC201FE

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times. All Plato soldering tips manufactured since January 2004 are tinned with Lead-Free solder.

Long Life: Using a high quality Plato soldering tip increases soldering speed and decreases the total cost of manufacture. Higher temperatures and high tin content solders, common in lead-free soldering processes, place additional strain on soldering iron tips. The long life of a Plato soldering iron tip reduces tip changes, decreasing the total number of tips used and decreasing production time.

Rapid Heat Recovery: Plato soldering tips are constructed from highly conductive premium grade copper to transmit heat to the work more quickly than other brands of soldering tips. This quick heat recovery enables more joints to be soldered per minute, thus reducing manufacturing time and costs.



- Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- Fewer tip change overs

Product Dimensions

C-3039-7 700°F screwdriver

Cross Reference: Weller PTA7, Weller PTR7
1.6mm
10 units/case



C-3039-8 800°F screwdriver

Cross Reference: Weller PTA8, Weller PTR8
1.6mm
10 units/case




C-3039-9 900°F screwdriver

Cross Reference: Weller PTA9, Weller PTR9
1.6mm
10 units/case



C-3040-7 700°F screwdriver

Cross Reference: Weller PTB7
2.4mm
10 units/case





C-3040-8 800°F screwdriver

Cross Reference: Weller PTB8
2.4mm
10 units/case



C-3040-9 900°F screwdriver

Cross Reference: Weller PTB9
2.4mm
10 units/case



C-3036-7 700°F screwdriver

Cross Reference: Weller PTC7
3.2mm
10 units/case



C-3036-8 800°F screwdriver

Cross Reference: Weller PTC8
3.2mm
10 units/case




C-3036-9 900°F screwdriver

Cross Reference: Weller PTC9
3.2mm
10 units/case




C-1016-7 700°F screwdriver

Cross Reference: Weller PTD7, Weller PTE7
4.8mm
10 units/case




C-1016-8 800°F screwdriver

Cross Reference: Weller PTD8, Weller PTE8
4.8mm
10 units/case



C-1016-9 900°F screwdriver

Cross Reference: Weller PTD9, Weller PTE9
4.8mm
10 units/case



C-3100-7 700°F screwdriver

Cross Reference: Weller PTH7, Weller PTJ7
0.8mm
10 units/case



C-3100-8 800°F screwdriver

Cross Reference: Weller PTH8, Weller PTJ8
0.8mm
10 units/case





C-3100-9 900°F screwdriver

Cross Reference: Weller PTH9, Weller PTJ9
0.8mm
10 units/case



C-3043-7 700°F long screwdriver

Cross Reference: Weller PTK7
1.2mm
10 units/case



C-3043-8 800°F long screwdriver

Cross Reference: Weller PTK8
1.2mm
10 units/case



C-3043-9 900°F long screwdriver

Cross Reference: Weller PTK9
1.2mm
10 units/case



C-3044-7 700°F long screwdriver

Cross Reference: Weller PTL7
2.0mm
10 units/case



C-3044-8 800°F long screwdriver

Cross Reference: Weller PTL8
2.0mm
10 units/case



C-3044-9 900°F long screwdriver

Cross Reference: Weller PTL9
2.0mm
10 units/case



C-3102-7 700°F long screwdriver

Cross Reference: Weller PTM7
3.2mm
10 units/case





C-3102-8 800°F long screwdriver

Cross Reference: Weller PTM8
3.2mm
10 units/case



C-3102-9 900°F long screwdriver

Cross Reference: Weller PTM9
3.2mm
10 units/case



C-4223-7 700°F long conical

Cross Reference: Weller PT07
0.8mm
10 units/case



C-4223-8 800°F long conical

Cross Reference: Weller PT08
0.8mm
10 units/case



C-4223-9 900°F long conical

Cross Reference: Weller PT09
0.8mm
10 units/case



C-462-7 700°F conical

Cross Reference: Weller PTP7, Weller PTT7
0.8mm
10 units/case



C-462-8 800°F conical

Cross Reference: Weller PTP8
0.8mm
10 units/case



C-462-9 900°F conical

Cross Reference: Weller PTP9, Weller PTT9
0.8mm
10 units/case



C-494-7 700°F long conical

Cross Reference: Weller PTS7
0.4mm
10 units/case



C-494-8 800°F long conical

Cross Reference: Weller PTS8, Weller PTT8
0.4mm
10 units/case





C-494-9 900°F long conical

Cross Reference: Weller PTS9
0.4mm
10 units/case




C-5143-7 700°F bevel

Cross Reference: Weller PTBB7
2.4mm
10 units/case




C-5143-8 800°F bevel

Cross Reference: Weller PTBB8
2.4mm
10 units/case



C-5143-9 900°F bevel

Cross Reference: Weller PTBB9
2.4mm
10 units/case



C-5141-7 700°F bevel

Cross Reference: Weller PTCC7, Weller PTDD7
3.2mm
10 units/case



C-5141-8 800°F bevel

Cross Reference: Weller PTCC8, Weller PTDD8
3.2mm
10 units/case



C-5141-9 900°F bevel

Cross Reference: Weller PTCC9, Weller PTDD9
3.2mm
10 units/case



Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.



Techspray
P.O. Box 949, Amarillo, TX 79105
800-858-4043 • www.techspray.com



Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW