

# HBL4715C -- Twist-Lock Flanged Receptacle



2P3W, 15A 125V, L5-15R, White Nylon


## Product Specifications

### Product Type



<b>Product Item</b>	Flanged Receptacle
<b>Wiring Scheme</b>	2 Pole, 3 Wire Grounding
<b>Amperage</b>	15A
<b>Voltage</b>	125V AC
<b>NEMA Configuration</b>	L5-15R
<b>Item Style</b>	Standard
<b>Device Color</b>	White
<b>Horsepower</b>	0.5
<b>Terminal Retainer Material</b>	Clear polycarbonate
<b>Terminal Clamp Material</b>	.062" cold rolled steel-nickel-plated
<b>Terminal Screw Material</b>	#8-32 Brass (white finish on neutral screw when used)

<b>Ground Screw Material</b>	Brass (green finish)
<b>Body Contact Carrier Material</b>	Natural White Nylon
<b>Contact Spring Material</b>	Brass
<b>Spring Binding Plate Material</b>	Brass
<b>Flanged Casing Material</b>	Natural White Nylon
<b>Mounting Screw Material</b>	Nickel-plated Brass Round head screws
<b>Ground Contact Material</b>	.032" Bronze
<b>Ratings</b>	Molded into face.
<b>Dielectric Voltage Withstand</b>	2,000V minimum
<b>Current Interrupting</b>	Certified for current interrupting at full rated current.
<b>Temperature Rise</b>	Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
<b>Terminal Accommodation</b>	15A #14AWG
<b>Terminal Identification</b>	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
<b>Flammability</b>	HB or better per UL 94 or CSA 22.2 No. 0.6
<b>Operating Temperatures</b>	Maximum Continuous 75 C Minimum -40 C (w/o impact)
<b>Listings</b>	UL/CSA
<b>Catalog Page</b>	<a href="#">Click here for catalog page B12</a>
<b>Brochures</b>	<a href="#">Click here for product brochure</a>
<b>Hubbellnet</b>	<a href="#">Click here for Hubbellnet</a>
<b>Catalog Section</b>	<a href="#">Click here for Section-B</a>
<b>UPC Number</b>	78358517100
<b>Weight in LBs</b>	0.15



**Hubbell Incorporated (Delaware)**  
**185 Plains Road**  
**Milford, CT 06460-2420**  
**Ph: (203) 882-4800**  
**Fax: (800) 255-1031**



**Wiring Device-Kellems**