




RESET CALL POINT



We found the STI ReSet call point very easy to install & very reliable. The option of different resistance and dead short terminals, allows our engineers to install these call points to all standard non addressable systems. Our customers find the call points to be very easy to use; we have also noticed that the sites that have these call points no longer call for help due to test keys jammed or glasses dislodged or broken etc.

Derek Fay – Alarm Manager
Churches Fire Security Ltd




- 1) Positive action – mimics the feel of breaking glass
- 2) A warning indicator drops in to view when the call point is activated
- 3) To reset a simple key is inserted in to the bottom of the call point
- 4) A quick turn of the key and the call point is reset and ready for use again straight away

FEATURES

- EN54-11 approved (Cert No. 653a/01)
- IP67 Waterproof and addressable models available
- Glass appearance maintains operator deterrence
- Positive activation that mimics the feel of breaking glass
- Visible warning flag confirms activation
- Simple key to reset operating element – no broken glass
- No glass elements to break, lose or incorrectly fit during installation
- Complete functional test with every activation
- Extremely attractive, high value look and feel
- Low profile, heavy-duty terminations – Two built-in resistor values
- Available in five colours

▼ ReSet dimensions and technical information



HOW TO ORDER

All ReSet call point numbers begin with RP and contain 4 other characters

EG: RP-RS-01/CI = ReSet Point, Red Surface Mounted, Series 01 with optional integral cover

RP Prefix	R Denotes colour options R = Red Y = Yellow G = Green B = Blue W = White	S Denotes mounting options S = Surface Mounting F = Flush Mounting
---------------------	---	--

*Gold contacts are especially suitable for low current and voltages. Typically they are used in the range from 5V 1 mA to 12V 100 mA DC.

STI RESET CALL POINT

The 'ReSet' is a unique manual call point that mimics the feel of breaking glass whilst offering the user the benefits and environmental advantages of a re-settable operating element.

The 'ReSet' uses a simple yet ingenious patented mechanism which consists of a rigid plastic operating element and an over centre spring mechanism. This arrangement provides real action on operation and simulates break glass activation.

An activation indicator drops into view at the top of the window after the 'ReSet' has been operated. The unit is then simply reset with a key and is ready for re-use straight away.


APPLICATIONS

The 'ReSet' call point is compatible with most conventional fire alarm systems. It is safe for use in areas where glass cannot be used, e.g. food processing plants and swimming/leisure centres.

As the unit can be simply reset it provides an ideal solution for areas that suffer from a high number of false activations such as schools, shopping centres and other public places.


ELECTRICAL ARRANGEMENT

Series 01



Series 01 denotes a ReSet call point that will interface with most conventional fire alarm systems. It is fitted with two internal resistors 470 (R1) and 680 (R2) ohms. These are easily accessed through the installer terminals as illustrated.

Series 02



Series 02 denotes a ReSet call point that is fitted with a single pole changeover switch both the normally open and normally closed contacts are easily accessed through the installer terminals as illustrated.

Series 03




Series 03 denotes a ReSet call point that is fitted with a double pole normally open switch easily accessed through the installer terminals as illustrated.

Series 04



Series 04 denotes a ReSet call point that is fitted with a double pole normally closed switch easily accessed through the installer as illustrated.

Series 11



Series 11 denotes a ReSet call point that incorporates two independent single pole changeover switches providing double pole changeover contacts. Easily accessed through the installer terminals as illustrated.

Switch arrangements shown with ReSet in standby.

Technical Specifications

Current Rating (All Series)	3 Amps 12 – 24V DC
Current Rating (Series 02-04 & 11)	3 Amps 125 – 250V AC
Low Current Rating* (All Series)	1-100 mA 5 – 12V DC 0.1 Amps 125 – 250V AC
Housing and Mounting Box Material	Polycarbonate
Electrical Contact Material	Silver plated brass
Operating Temperature	-20°C to +65°C
Installation Terminal Conductor Size	0.5mm – 2.5mm
Colours	Red, Yellow, Green, Blue & White
Mounting	Flush or surface with back box

01 Denotes series and electrical arrangement 01 = Conventional fire model includes two resistor values 470 & 680 ohms 02 = Single pole changeover 03 = Double pole – normally open 04 = Double pole – normally closed 11 = Double pole changeover	CI Denotes optional cover CN = No Cover CI = Integral Cover CM = Mini Stopper CP = Call Point Stopper CS = Stopper CSS = Stopper with Sounder CW = Weather Stopper
--	---