MULL12060-200

UNCONTROLLED DOCUMENT

PHYSICAL DIMENSIONS:

A 120.0[4.724] ± 2.00[.0787]

B 60.0[2.362] ± 2.00[.0787]


C 0.10[0.004] ± 0.02[.0008]


D 0.20[0.008] MAX



ELECTRICAL CHARACTERISTICS:			
Initial Permeability(u') (13.56MHz)	150±20%		
Initial Permeability(u'') (13.56MHz)	5 Max		

PRODUCTS SHAPE AND DIMENSIONS





MEASURED BY ANGILENT E4991A, 1Ts.

NOTES: UNLESS OTHERWISE SPECIFIED

- 1. OPERATING TEMPERATURE RANGE -40°C TO 85°C.
- 2. FLEXIBLE FERRITE SHEET.
- 3. D IS MEASURED AFTER REMOVING PAPER LINER OF ADHESIVE

	DIMENSIONS ARE IN mm [INCHE	s].		This print is the property of Laird	_
				Tech, and is loaned in confidence	
				subject to return upon request and with the understanding that	
				no copies shall be made without	
				the written consent of Laird Tech.	•
				All rights to design or invention are reserved.	
				PROJECT/PART NUMBER: REV PART TYPE: DRAWN B	ĴΥ:
				→ MULL12060-200 A co-fire qu	
				DATE: 10/08/14 SCALE: NTS SHEET:	
Α	ORIGINAL DRAFT	10/08/14	ਫ਼ੋ		
REV	DESCRIPTION	DATE	INT		