

**Productname :** ADHESIVE QS 900  
**Ref.Nr.:** UDS000121\_3\_20111108

**Creationdate :** 08.11.11 Version : 1.0  
**Replaces:** UK10028

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**ADHESIVE QS 900**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Adhesives

### 1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.  
Ambersil House - Wylds Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to 67/548/EEC or 1999/45/EC:

<b>Health:</b>	R67: Vapours may cause drowsiness and dizziness.
<b>Physical:</b>	R12: Extremely flammable. EXTREMELY FLAMMABLE
<b>Environment:</b>	R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

### 2.2. Label elements

**Warning symbol(s) :**

EXTREMELY FLAMMABLE



N : DANGEROUS FOR THE ENVIRONMENT

**Ambersil**

1 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** ADHESIVE QS 900  
**Ref.Nr.:** UDS000121\_3\_20111108

**Creationdate :** 08.11.11 Version : 1.0  
**Replaces:** UK10028



<b>Risk-phrase(s) :</b>	R12: Extremely flammable. R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. R67: Vapours may cause drowsiness and dizziness.
<b>Safety-phrase(s) :</b>	S2: Keep out of the reach of children. S16: Keep away from sources of ignition - No smoking. S23: Do not breathe vapours/spray. S35: This material and its container must be disposed of in a safe way. S51: Use only in well-ventilated areas.
<b>Extra label elements according to Aerosol Dispenser Directive 75/324/EC:</b>	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.
<b>Other extra label elements:</b>	Remark: Preparations classified as harmful on the basis of an aspiration hazard need not be labelled as harmful with R65 when placed on the market in aerosol containers or in containers fitted with a sealed spray attachment. (EU-Directive 67/548 Annex VI 9.4)

### 2.3. Other hazards

None

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
Hydrocarbons, C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	30-60	F+	12	K
acetone; propan-2-one; propanone	67-64-1	200-662-2	<20	F,Xi	11-36-66-67	A
Naphtha (petroleum), hydrosulfurized light (benzene<0.1%)	92045-53-9	295-434-2	5-15	F,Xn,N	11-38-51/53-65-67	B,P
cyclohexane	110-82-7	203-806-2	1-5	F,Xn,N	11-38-50/53-65-67	A
Naphtha (petroleum), hydrotreated light	64742-49-0	265-151-9	1-5	F,Xn,N	11-38-51/53-65-67	B,P
n-hexane	110-54-3	203-777-6	0-1	F,Xn,N	11-38-48/20-62-65-67-51/53	A
<b>Explanation notes</b>						
A : substance with Community workplace exposure limit						
B : substance with national established workplace exposure limit						
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)						
P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)						

**Productname :** ADHESIVE QS 900  
**Ref.Nr.:** UDS000121\_3\_20111108

**Creationdate :** 08.11.11 Version : 1.0  
**Replaces:** UK10028

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
acetone; propan-2-one; propanone	01-2119471330-49	67-64-1	200-662-2	<20	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	A
cyclohexane		110-82-7	203-806-2	1-5	Flam. Liq. 2, Asp. Tox. 1, Skin Irrit. 2, STOT SE 3, Aquatic Acute 1, Aquatic Chronic 1	H225,H304,H315,H336,H400,H410	A
n-hexane		110-54-3	203-777-6	0-1	Flam. Liq. 2, Repr. 2, Asp. Tox. 1, STOT RE 2, Skin Irrit. 2, STOT SE 3, Aquatic Chronic 2	H225,H361f,H304,H373,H315,H336,H411	A

**Explanation notes**

A : substance with Community workplace exposure limit

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water Seek medical attention if irritation persists
<b>Contact with skin :</b>	Wash with water and soap. Seek medical attention if irritation persists
<b>Inhalation :</b>	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
<b>Ingestion :</b>	Ingestion is unlikely to occur If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	May cause irritation. Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

**Productname :** ADHESIVE QS 900  
**Ref.Nr.:** UDS000121\_3\_20111108

**Creationdate :** 08.11.11 Version : 1.0  
**Replaces:** UK10028

foam, carbon dioxide or dry agent

## 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

## 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

# SECTION 6: Accidental release measures

## 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

## 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

## 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

## 6.4. Reference to other sections

For further information see section 8

# SECTION 7: Handling and storage

## 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.

## 7.2. Conditions for safe storage, including any incompatibilities

**Productname :** ADHESIVE QS 900  
**Ref.Nr.:** UDS000121\_3\_20111108

**Creationdate :** 08.11.11 Version : 1.0  
**Replaces:** UK10028

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

### 7.3. Specific end use(s)

Adhesives

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
n-hexane	110-54-3	TWA	20 ppm
cyclohexane	110-82-7	TWA	200 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
<b>National established exposure limits, United Kingdom</b>			
cyclohexane	110-82-7	TWA	100 ppm
		STEL	300 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
		STEL	1500 ppm

### 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
<b>hands and skin :</b>	Wear suitable protective gloves against chemicals (nitrile)
<b>eyes :</b>	Wear safety goggles.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

<b>Apperance : physical state :</b>	Propane/butane propelled liquid.
<b>colour :</b>	Yellow.
<b>odour :</b>	Solvent.
<b>pH :</b>	Not applicable.



5 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** ADHESIVE QS 900  
**Ref.Nr.:** UDS000121\_3\_20111108

**Creationdate :** 08.11.11 Version : 1.0  
**Replaces:** UK10028

<b>Boiling point/range :</b>	56 °C
<b>Flash point :</b>	- 18 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	13 %
<b>lower limit :</b>	1.1 %
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.8 g/cm3.
<b>Solubility in water :</b>	Immiscible with water
<b>Auto-ignition :</b>	> 200 °C
<b>Viscosity :</b>	80 - 120 mPa.s.

## 9.2. Other information

**VOC:** 560 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

<b>Inhalation :</b>	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.



**Productname :** ADHESIVE QS 900  
**Ref.Nr.:** UDS000121\_3\_20111108

**Creationdate :** 08.11.11 Version : 1.0  
**Replaces:** UK10028

**Skin contact :** Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis  
**Eye contact :** May cause irritation.

**Toxicological data :**

Hazardous ingredient	CAS-nr.	method	
cyclohexane	110-82-7	LD50 oral rat	> 5000 mg/kg
acetone; propan-2-one; propanone	67-64-1	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg

**SECTION 12: Ecological information****12.1. Toxicity**

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**Ecotoxicological data:**

Hazardous ingredient	CAS-nr.	method	
cyclohexane	110-82-7	EC50 daphnia	0.9 mg/l
acetone; propan-2-one; propanone	67-64-1	IC50 algae	> 100 mg/l
		LC50 fish	> 100 mg/l
		EC50 daphnia	> 100 mg/l

**12.2. Persistence and degradability**

No information available

**12.3. Bioaccumulative potential**

No information available

**12.4. Mobility in soil**

Immiscible with water

**12.5. Results of PBT and vPvB assessment**

No information available

**12.6. Other adverse effects**

No information available

Productname : ADHESIVE QS 900  
Ref.Nr.: UDS000121\_3\_20111108

Creationdate : 08.11.11 Version : 1.0  
Replaces: UK10028

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**Contaminated packaging :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

### 14.4. Packing group

Packing group: Not applicable.

### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes  
IMDG - Marine pollutant: Marine pollutant  
IATA/ICAO - Environmentally hazardous: Yes

### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

### 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

## SECTION 15: Regulatory information



8 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com



**Productname :** ADHESIVE QS 900  
**Ref.Nr.:** UDS000121\_3\_20111108

**Creationdate :** 08.11.11 Version : 1.0  
**Replaces:** UK10028

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1907/2006 (REACH)

### 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

- \*Explanation risk-phrases:
- R11: Highly flammable.
  - R12: Extremely flammable.
  - R36: Irritating to eyes.
  - R38: Irritating to skin.
  - R62: Possible risk of impaired fertility.
  - R65: Harmful: may cause lung damage if swallowed.
  - R66: Repeated exposure may cause skin dryness or cracking.
  - R67: Vapours may cause drowsiness and dizziness.
  - R48/20: Harmful: danger of serious damage to health by prolonged exposure through inhalation.
  - R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
  - R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
  - R51/53
- \*Explanation hazard statements:
- H225 : Highly flammable liquid and vapour.
  - H304 : May be fatal if swallowed and enters airways.
  - H315 : Causes skin irritation.
  - H319 : Causes serious eye irritation.
  - H336 : May cause drowsiness or dizziness.
  - H361f : H361f
  - H373 : May cause damage to organs through prolonged or repeated exposure
  - .
  - H400 : Very toxic to aquatic life.
  - H410 : Very toxic to aquatic life with long lasting effects.
  - H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.