

Product Detail Page



TXS-611SET

Number: 25.3650

Multifrequency microphone system,
with UHF PLL technology.

- 1 hand-held microphone transmitter (cardioid characteristic), 1 receiver, 1 plug-in PSU
- True diversity system
- 80 selectable UHF channels (863-865 MHz)
- ACT function for transmitting the selected frequency to the hand-held microphone via infrared signal
- Autoscanner
- Volume and squelch controls
- Transmitting power can be switched at the hand-held microphone (high/low)
- Indication for channel, antenna A/B, ACT status and AF audio level (receiver), channel and battery status (hand-held microphone)
- Robust metal housing (receiver)

Licence-free system in the EU.

Technical Facts

Carrier frequency	863-865 MHz
Transmitting power	< 10 mW (EIRP)
RF S/N ratio	105 dB
Audio range	50-18,000 Hz, ± 3 dB
Dynamic range	120 dB
THD	< 0.5 %
Audio output	350 mV/10 k Ω (jack) 25 mV/10 k Ω (XLR, bal.)
Operating range	approx. 30 m
Admiss. ambient temp.	0-40 °C
Power supply	
Transmitter	2 x 1.5 V batt. AA size
Receiver	via suppl. plug-in PSU
Dimensions	
Transmitter	Ø 52 mm x 275 mm
Receiver	152x38x120 mm
Weight	
Transmitter	235 g
Receiver	482 g



Connections

1 x 6.3 mm jack, unbal.

1 x XLR, bal.

