

TXS-631SET - Wireless Microphone



Multifrequency microphone system, with UHF PLL technology.

- 1 pocket transmitter, 1 tie clip microphone, 1 receiver, 1 plug-in PSU
- True diversity system
- 80 selectable UHF channels (863-865 MHz)
- ACT function for transmitting the selected frequency to the pocket transmitter via infrared signal
- Autoscanner
- Volume and squelch controls
- Gain can be adjusted at the pocket transmitter
- Indication for channel, antenna A/B, ACT status and AF audio level (receiver), channel and battery status (pocket transmitter)
- Robust metal housing (receiver)

Licence-free in the EU.

Technical data

Carrier frequency	: 863-865 MHz
Transmitting power	: < 10 mW (EIRP)
RF S/N ratio	: 105 dB
Audio range	: 50-18,000 Hz, ± 3 dB
Dynamic range	: 120 dB
THD	: < 0.5 %
Audio output	: 350 mV/10 k Ohm (jack) 25 mV/10 k Ohm (XLR, bal.)
Operating range	: approx. 30 m
Admiss. ambient temp.	: 0-40 °C
Power supply	:
Transmitter	: 2 x 1.5 V batt. AA size
Receiver	: via suppl.plug-in PSU
Dimensions	:
Transmitter	: 62x105x25 mm
Receiver	: 152x38x120 mm
Weight	:
Transmitter	: 88 g
Receiver	: 482 g
Connections	: 1 x 6.3 mm jack, unbal. 1 x XLR, bal.