



Einhell

HOME

TH-SM 2131 Dual Sliding Mitre Saw

Features

- Motor head continuously tiltable from 0° to +45° To the left & right side
- Carbide tipped saw blade in professional quality (3), cutting capacity more than 200 m in chipboard
- Double pivoted sliding feature (1)
- Incl. dust bag (2) and bilateral support clamps (4)
- Incl. laser (line operated) (5)
- Work piece bar with movable rails to the left and right side (6)
- Table inlay with scale (7)
- Rotating table for precise angle cuts ranging -45° to +45° with positions of lock (8)
- Clamping device for safely fixing of the work Piece (9)

Technical Data

- Mains: 230 V ~ 50 Hz
- Power: 1,800 W S2 5 min
1,500 W S1
- Idle speed: 5,000 min⁻¹
- TCT saw blade / teeth: Ø 210 x Ø 30 mm / 48 Z
- Max. saw width 90° / 45°: 310 x 62 mm / 210 x 62 mm
- Max. saw width 2 x 45°: left: 210 x 36 mm
right: 210 x 20 mm
- Cutting width max.: 310 mm
- Product weight: 10.3 kg

Logistic Data

- Net weight: 11.9 kg
- Gross weight: 14.2 kg
- Packing dimensions: 725 x 455 x 390 mm
- Bar code: 4006825 584936
- Sales Unit: 1 pc

