



Einhell

CLASSIC

TH-BG 150 Bench grinder

Features

- Spark reflectors with large glasses
- Adjustable tool rests
- Lateral closed wheels
- Robust metal housing for long life-time
- Incl. 1 rough and 1 fine grinding wheel
- Free from float ball beared spindle
- 4 rubber feet for stable low-vibration stand

Technical Data

- Mains: 230 V ~ 50 Hz
- Power: 150 W S2 30 min
- No load speed: 2,950 rpm
- Grinding wheels: Ø 150 x Ø 12.7 x 16 mm
- Product weight: 5.7 kg

Logistic Data

- Net weight: 6 kg
- Gross weight: 6.5 kg
- Packing dimensions: 295 x 205 x 205 mm
- Bar code: 4006825 595765
- Sales Unit: 1 pc

