

## Heavy Duty Vertical Wall Bracket *VPB Series*

### Features



- Constructed in 14-gauge steel.
- 19" mounting EIA-310-D compliant rails with 10-32 tapped clip nuts.
- Horizontal or vertical equipment mounting.
- Rear cable access for cable management.
- Finished in textured black powder paint.
- Includes four (4) 10-32 black rack screws with washers and clip nuts per rack unit.
- Tested to nearly double the suggested load rating of 135 lbs.
- RoHS Compliant.
- Manufactured in North America.



### Accessories

[Outlet Strips](#)

[Mounting Hardware](#)

[Two Post Mounting Cantilever Shelf](#)

[Hinged Acrylic Door Panel Cover](#)



Part No.	Overall Dimensions			Mounting Dimensions		Rack	
	Height	Width	Depth	Height	Width	Units	Shipping Weight
VPB192UBK	7.69	19.19	4.19	3.50	19.00	2U	2
VPB194UBK	7.69	19.19	7.69	7.00	19.00	4U	5
VPB196UBK	11.19	19.19	11.19	10.50	19.00	6U	10

*Data subject to change without notice.*