# **Common mode Noise Filters**

# Type: EXC34CG/CE




### ■ Features

- Low-profile (L 2.0 mm×W 1.25 mm×H 0.50 mm)
- Filtering the noise of high-speed differential signaling lines and minimizing deformations of transmitted signal waveforms
- Rigid multi-layer sintered structure with high resistance to reflow heat and mounting reliability
- Lead, halogen, and antimony free
- RoHS compliant


### ■ Recommended Applications

- Digital AV equipment (TV, Digital displays, DVD) Information equipment (PCs, HDD)
- Interface examples USB, LVDS, HDMI, LAN


## ■ Explanation of Part Numbers




#### ■ Construction



### ■ Dimensions in mm (not to scale)



## ■ Circuit Configuration (No Polarity)




## ■ Ratings

Part Number	Impedance ( $\Omega$ ) at 100MHz	Rated Current	Rated Voltage	Insulation Resistance	Withstand Voltage	DC Resistance
	Common Mode	(mA DC)	(V DC)	(M $\Omega$ min.)	(V DC)	$(\Omega)$ max.
EXC34CE670U	67 Ω±25 %	250	5	10 MΩ	125	0.8
EXC34CE900U	90 Ω±25 %	250	5	10 MΩ	125	0.8
EXC34CE121U	120 Ω±25 %	200	5	10 MΩ	125	1.0
EXC34CE201U	200 Ω±25 %	200	5	10 MΩ	125	1.0
EXC34CG900U	90 Ω±25 %	100	5	10 MΩ	125	3.0

● Category Temperature Range -40 °C to +85 °C

# ■ Impedance Characteristics (Typical)



■ Packaging Methods, Land Pattern, Soldering Conditions and Safety Precautions Please see Related Information