

Technical drawing of a 2-layer shrinkable bag. The drawing shows two views: a front view on the left and a side view on the right.

Front View (Left):

- Overall width: 120 ± 10
- Overall height: 72 ± 1
- Inner width (excluding side flaps): 56 ± 1
- The bag features two vertical side flaps and two vertical internal lines.

Side View (Right):

- Overall width: 38 ± 1
- The bag is labeled "2 Layer shrinkable" at the top.

The diagram shows a rectangular box with rounded corners, labeled 'Safetyboard'. A cable, labeled 'red and black wire AWG22', extends from the right side of the box. The cable has two conductors, one red and one black, which are shown as two parallel lines. The cable ends in a connector that fits into a slot on the right side of the box.

Li-Ion Rechargeable 18650 352P

Nominal voltage:	11.1V
Max. charge voltage:	12.6V
Nominal capacity:	5200mAh
Minimum capacity:	5000mAh
Energy:	57.7Wh

Safety advice:
Do not crush, heat, incinerate, short circuit.
Dispose of batteries in any liquid or it may well be rupture.
Do not charge below 0°C
Discharge -20°C to +60°C
Tested and approved to UN38.3
part. no.: 2447-3050-01


no fire


Li-Ion





Verwendungsbereich/Application range für Anfrage/for inquiry IS-2013-00429				Zul. Abweichung/ Allowable deviation		Oberfläche/ Surface		Maßstab/Scale (DIN A2): 1:1		Gewicht/Weight	
				Allgemeintoleranz DIN ISO 2768-m				Werkstoff/Work material, Modell-Nr.			
				2013	Datum/Date	Name		Zeichnungsname/Drawing name			
				Erstellt/ Drawn by	23.10.	JE		Li-Ion Battery 11.1V 5200mAh with safetyboard			
								Zeichnungsnummer/Drawing number Artikelnummer/Part number		Blatt/ Sheet	
								2447-3050-01		1	
VO	---	XX.XX.XX	XX	Ursprung/Origin Proj. IS-2013-00429				Ersatz für/Replaced by		Ersatz durch/Replacement through:	
Version	Änderung/Change	Datum/Date	Name								