

700PD3 Dual Pressure Module (± 340 mbar)



- Display pressure readings in any of 10 different pressure units you specify in the calibrator setup
- Rugged urethane molded case protects the module from rough handling and harsh conditions
- Features internal temperature compensation from 0° C to 50° C for full-accuracy performance
- Includes NIST-traceable calibration certificate
- Module can be calibrated locally using the Fluke 700PCK Pressure Calibration Kit, a PC, and a precision pressure source
- One year warranty

Specifications	
Range	± 5 psi / ± 34 kPa
Resolution	0.0001 / 0.001
Reference Uncertainty (23 \pm 3° C)	0.040%
Total¹ Uncertainty 1 year	0.070
High Side Media²	316 SS
Low Side Media²	Dry
Note	1) Total uncertainty, one year for temperature range 0° C + 50° C. Total uncertainty, 1.0% of full span for temperature range - 10° C to 0° C. Compensated temperature range is 15° C to 35° C. 2) "Dry" indicates dry air or non-corrosive gas as compatible media. "316 SS" indicates media compatible with Type 316 Stainless Steel. "C276" indicates media compatible with Hastelloy C276.