

## 700P03 Differential Pressure Module (340 mbar)



- Display pressure readings in any of 10 different pressure units you specify in the calibrator setup
- Rugged urethane molded case protects the module from rough handling and harsh conditions
- Features internal temperature compensation from 0° C to 50° C for full-accuracy performance
- Includes NIST-traceable calibration certificate
- Module can be calibrated locally using the Fluke 700PCK Pressure Calibration Kit, a PC, and a precision pressure source
- One year warranty

Specifications	
<b>Range</b>	5 psi / 34 kPa
<b>Resolution</b>	0.0001 / 0.001
<b>Reference Uncertainty (23 ± 3° C)</b>	0.050%
<b>Total<sup>1</sup> Uncertainty 1 year</b>	0.100
<b>High Side Media<sup>2</sup></b>	Dry
<b>Low Side Media<sup>2</sup></b>	Dry
<b>Note</b>	<b>1)</b> Total uncertainty, one year for temperature range 0° C + 50° C. Total uncertainty, 1.0% of full span for temperature range - 10° C to 0° C. Compensated temperature range is 15° C to 35° C. <b>2)</b> "Dry" indicates dry air or non-corrosive gas as compatible media. "316 SS" indicates media compatible with Type 316 Stainless Steel. "C276" indicates media compatible with Hastelloy C276.