



MATERIAL SAFETY DATA SHEET

Page 1 of 7

MSDS-E-DFG213

Prepared to OSHA, ACC, ANSI, WHMIS, NOHSC & 2001/58 EC Standards

MSDS Revision: 2.0

MSDS Revision Date: 01/06/2011

1. PRODUCT IDENTIFICATION

CHEMICAL RESPONSE CARD:

031.1 Product Name: **DeoxIT® FaderGrease DFG-213**

1.2 Chemical Name: See ingredients listed in section 3

1.3 Synonyms: DeoxIT® FaderGrease Type 213

1.4 Trade Names: DeoxIT® FaderGrease DFG-213

1.5 Product Use: Lubricant for conductive plastics

1.6 Manufacturer's Name: CAIG Laboratories, Inc.

1.7 Manufacturer's Address: 12200 Thatcher Court, Poway, CA 92064-6876

1.8 Business Phone: +1 (800) 224-4123

1.9 Emergency Phone:

CHEMTREC +1 (703) 527-3887 / +1 (800) 424-93001.10 Other Product Names: DeoxIT® FaderGrease, DFG-213, 28 grams (Part No. DFG-213-1)
DeoxIT® FaderGrease, DFG-213, 226 grams (Part No. DFG-213-8)**RESPONSE
TEAM PPE:****WHMIS:****HEALTH:****0****FLAMMABILITY:****1****PHYSICAL HAZARDS:****0****PERSONAL PROTECTION:****B**

2. HAZARD IDENTIFICATION

2.1 Hazard Identification:

This product is NOT classified as a HAZARDOUS SUBSTANCE or as DANGEROUS GOODS according to the classification criteria of NOHSC:1088 (2004) and ADG Code (Australia). DeoxIT® Fader Lube Grease is non-volatile, non-hazardous and non-flammable. Not expected to cause prolonged or significant eye or skin irritation. High-Pressure Equipment Information: Accidental high-velocity injection under the skin of materials of this type may result in serious injury. Seek immediate medical attention should an accident of this type occur. Contains petroleum-based mineral oil. May cause respiratory irritation or other pulmonary effects following prolonged or repeated inhalation of oil mist at airborne levels above the recommended mineral oil mist exposure limit. Heating can generate vapors that may cause respiratory irritation, nausea and headaches, irritating to the upper respiratory tract.

2.2 Routes of Entry:

Inhalation:

YES

Absorption:

YES

Ingestion:

NO

2.3 Effects of Exposure:

EYES:

Non-irritating when used as directed. Can cause irritation, tearing, and temporary blurred vision.

SKIN:

Non-irritating when used as directed. Prolonged or repeated contact may cause temporary contact dermatitis (localized redness or rash).

INGESTION:

Not probable. Small amounts if swallowed may cause temporary gastrointestinal irritation.

INHALATION:

Unlikely route of exposure. Should vapor concentrations exceed recommended exposure levels, they are temporary irritating to the eyes, nose, throat, and the respiratory tract; may cause temporary headaches and dizziness.

2.4 Symptoms of Overexposure:

EYES:

Non-irritating when used as directed. Can cause temporary irritation, tearing, and blurred vision.

SKIN:

Non-irritating when used as directed. Prolonged or repeated contact may cause temporary contact dermatitis (localized redness or rash).

INGESTION:

Not probable. Small amounts if swallowed may cause temporary gastrointestinal irritation.

INHALATION:

Unlikely route of exposure. Should vapor concentrations exceed recommended exposure levels, they are temporary irritating to the eyes, nose, throat, and the respiratory tract; may cause headaches and dizziness.

2.5 Acute Health Effects:

EYES:

None reported when used as directed. Mild to moderate temporary irritation.

SKIN:

Unlikely when used as directed. Repeated exposure at site of contact may cause temporary contact dermatitis (localized redness or rash).

INGESTION:

Not probable. Small amount may cause temporary gastrointestinal irritation and central nervous system depression.

INHALATION:

Unlikely route of exposure. Should vapor concentrations exceed recommended exposure levels, they are temporary irritating to the eyes, nose, throat, and the respiratory tract; may cause headaches and dizziness.

2.6 Chronic Health Effects:

None reported by the manufacturer.

2.7 Target Organs:

Eyes, Skin

NA = Not Available; ND = Not Determined; NE = Not Established; NF = Not Found; C = Ceiling Limit; See Section 16 for Additional Definitions of Terms Used

NOTE: all WHMIS required information is included. It is located in appropriate sections based on the ANSI Z400.1-2004 format.



MATERIAL SAFETY DATA SHEET

Page 3 of 7
MSDS-E-DFG213

Prepared to OSHA, ACC, ANSI, WHMIS, NOHSC & 2001/58 EC Standards

MSDS Revision: 2.0

MSDS Revision Date: 01/06/2011

5. FIREFIGHTING MEASURES

5.1	Flashpoint & Method: > 101.1 °C (214 °F) CC (Closed Cup)
5.2	Autoignition Temperature: NA
5.3	Flammability Limits: Lower Explosive Limit (LEL): ND Upper Explosive Limit (UEL): ND
5.4	Fire & Explosion Hazards: Carbon dioxide, carbon monoxide, hydrocarbons.
5.5	Extinguishing Methods: CO₂, Alcohol foam, Dry Chemical, Water Fog
5.6	Firefighting Procedures: Wear NIOSH/MSHA approved self-contained breathing apparatus and protective clothing. Use a water spray to cool containers involved in fire. Do not use direct water stream. Container storage areas exposed to direct flame contact should be cooled with large quantities of water as needed to prevent weakening of container structure. Keep containers cool until well after the fire is out to prevent rupture. Prevent runoff from fire control or dilution from entering sewers, drains, drinking water supply, or any natural waterway.

Need symbol 0-1-0

6. ACCIDENTAL RELEASE MEASURES

6.1	Spills: Secure spill area and deny entry to all unprotected individuals. Individuals involved in the cleanup should wear appropriate personal protective equipment. Area may become slippery. Absorb product onto porous material, such as sand, clay, diatomaceous earth or commercial absorbent material. Place into leak-proof, approved containers. If necessary, cover all drains and dike well ahead of the spill to prevent runoff into sewers, drains, and all waterways. Contact appropriate local or provincial authorities for assistance and/or reporting requirements.
-----	---

7. HANDLING & STORAGE INFORMATION

7.1	Work & Hygiene Practices: Wash hands thoroughly after using this product and before eating, drinking, or smoking. Remove soiled clothing to prevent prolonged skin contact.
7.2	Storage & Handling: Store at temperatures between 59 °F and 95 °F (15 °C and 35 °C) in a dry, well-ventilated location. Keep away from heat, sparks, open flame, and other sources of ignition. Container is not designed to contain pressure. Do not use pressure to empty container or it may rupture with explosive force. Normal shelf-life: 2-3 years.
7.3	Special Precautions: Empty containers may contain product residues. Avoid contaminating soil or releasing this material into sewage and drainage systems and bodies of water.

8. EXPOSURE CONTROLS & PERSONAL PROTECTION

8.1	Ventilation & Engineering Controls: Use with adequate ventilation (e.g., open doors and windows, local exhaust ventilation). Ensure appropriate decontamination equipment is available (e.g., sink, safety shower, eye-wash station).
8.2	Respiratory Protection: None required, when used with adequate ventilation. If user operations generate an oil mist, use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below the recommended mineral oil mist exposure limits.
8.3	Eye Protection: Wear safety glasses with side shields (ANSI Z87) under normal use conditions.
8.4	Hand Protection: None required under normal conditions of use. However, may cause skin irritation in some sensitive individuals. In such cases, wear rubber or impervious plastic gloves.
8.5	Body Protection: Use as necessary to prevent skin contact.



MATERIAL SAFETY DATA SHEET

Page 4 of 7
MSDS-E-DFG213

Prepared to OSHA, ACC, ANSI, WHMIS, NOHSC & 2001/58 EC Standards

MSDS Revision: 2.0

MSDS Revision Date: 01/06/2011

9. PHYSICAL & CHEMICAL PROPERTIES

9.1	Density:	1.1
9.2	Boiling Point:	> 240 °C (464 °F)
9.3	Melting Point:	ND
9.4	Evaporation Rate:	ND
9.5	Vapor Pressure:	ND
9.6	Molecular Weight:	ND
9.7	Appearance & Color:	Translucent white
9.8	Odor Threshold:	odorless
9.9	Solubility:	ND
9.10	Ph	ND
9.11	Viscosity:	ND
9.12	Other Information:	ND

10. STABILITY & REACTIVITY

10.1	Stability:	Stable under normal conditions of use (see section 7).
10.2	Hazardous Decomposition Products:	Thermal breakdown of this product during fire or very high heat conditions may evolve the following decompositions products: Carbon oxides and traces of incompletely burned carbon compounds. Silicon dioxide. Formaldehyde.
10.3	Hazardous Polymerization:	Will not occur.
10.4	Conditions to Avoid:	Use or storage near open flames, sparks, high heat (>100 °F) or other heat sources, and proximity to incompatible substances.
10.5	Incompatible Substances:	Strong oxidizers such as peroxides, nitrates, and chlorates.

11. TOXICOLOGICAL INFORMATION

11.1	Toxicity Data:	This product has not been tested on animals to obtain toxicological data. There are toxicology data for the components of this product, which are found in the scientific literature. These data have not been presented in this document.	
11.2	Acute Toxicity:	See section 2.5	
11.3	Chronic Toxicity:	See section 2.6	
11.4	Suspected Carcinogen:	No.	
11.5	Reproductive Toxicity:	This product is not reported to produce reproductive toxicity in humans.	
	Mutagenicity:	This product is not reported to produce mutagenic effects in humans.	
	Embryotoxicity:	This product is not reported to produce embryotoxic effects in humans.	
	Teratogenicity:	This product is not reported to produce teratogenic effects in humans.	
	Reproductive Toxicity:	This product is not reported to produce reproductive effects in humans.	
11.6	Irritancy of Product:	See Section 2.3	
11.7	Biological Exposure Indices:	NE	
11.8	Physician Recommendations:	Treat symptomatically.	



MATERIAL SAFETY DATA SHEET

Page 5 of 7
MSDS-E-DFG213

Prepared to OSHA, ACC, ANSI, WHMIS, NOHSC & 2001/58 EC Standards

MSDS Revision: 2.0

MSDS Revision Date: 01/06/2011

12. ECOLOGICAL INFORMATION

12.1	Environmental Stability: This product will slowly volatile from soil. Components of this product will slowly decompose into organic compounds.
12.2	Effects on Plants & Animals: There is no specific data available for this product.
12.3	Effects on Aquatic Life: This material should be kept out of sewage and drainage systems and all bodies of water. Releases of large volumes of this product are expected to be harmful or fatal to overexposed aquatic life.

13. DISPOSAL CONSIDERATIONS

13.1	Waste Disposal: Dispose of in accordance with federal, state or local regulations.
13.2	Special Considerations: NA

14. TRANSPORTATION INFORMATION

The basic description (ID Number, proper shipping name, hazard class & division, packing group) is shown for each mode of transportation. Additional descriptive information may be required by 49 CFR, IATA/ICAO, IMDG and the CTDGR.

14.1	49 CFR (GND): NOT REGULATED	
14.2	IATA (AIR): NOT REGULATED	
14.3	IMDG (OCN): NOT REGULATED	
14.4	TDGR (Canadian GND): NOT REGULATED	
14.5	ADR/RID (EU): NOT REGULATED	
14.6	MEXICO (SCT): NOT REGULATED	
14.7	ADGR (AUS): NOT REGULATED	

15. REGULATORY INFORMATION

15.1	SARA Reporting Requirements: This material does not contain chemicals which are subject to the reporting requirements of Section 313 of SARA Title III and 40 CFR Part 373.	
15.2	SARA Threshold Planning Quantity: NA	
15.3	TSCA Inventory Status: All chemical substances of this product are listed on the TSCA inventory or are otherwise exempt from inventory status.	
15.4	CERCLA Reportable Quantity (RQ): This product has no CERCLA Reportable Quantity. However, release into a waterway may require reporting to the National Response Center.	
15.5	Other Federal Requirements: NA	
15.6	Other Canadian Regulations This product has been classified according to the hazard criteria of the Controlled Products Regulations (CPR) and the MSDS contains all of the information required by the CPR. The components of this product are listed on the DSL/NDL. None of the components of this product are listed on the Priorities Substances List.	
15.7	State Regulatory Information: Components of this product are <u>not</u> listed on any of the following state criteria lists: California OSHA; California Proposition 65; Wisconsin Hazardous Substances List NR 605.09; Minnesota Hazardous Substances List; New York Right to Know List; Pennsylvania Right to Know list; Michigan Critical Substances List; and Florida Toxic Substances List. Under New Jersey Right to Know Act L-1983 this product is to be identified as follows: Petroleum Oil (Grease).	



MATERIAL SAFETY DATA SHEET

Page 6 of 7
MSDS-E-DFG213

Prepared to OSHA, ACC, ANSI, WHMIS, NOHSC & 2001/58 EC Standards

MSDS Revision: 2.0

MSDS Revision Date: 01/06/2011

15. REGULATORY INFORMATION- continued

15.8 67/548/EEC (European Union) Requirements:

The primary component of this product is listed in Annex I of EU Directive 67/548/EEC:
(Xn) Harmful. R: 42/43-48/20 - May cause sensitization by inhalation and skin contact. Harmful: danger of serious damage to health by prolonged exposure through inhalation. S: 2-29-36 - Keep out of the reach of children. Do not empty into drains. Wear suitable protective clothing.



16. OTHER INFORMATION

16.1 Other Information:

NA

16.2 Terms & Definitions:

See last page of this MSDS.

16.3 Disclaimer:

This Material Safety Data Sheet is offered pursuant to OSHA's Hazard Communication Standard, 29 CFR §1910.1200. Other government regulations must be reviewed for applicability to this product. To the best of ShipMate's & CAIG Laboratories, Inc.'s knowledge, the information contained herein is reliable and accurate as of this date; however, accuracy, suitability or completeness are not guaranteed and no warranties of any type, either expressed or implied, are provided. The information contained herein relates only to the specific product(s). If this product(s) is combined with other materials, all component properties must be considered. Data may be changed from time to time. Be sure to consult the latest edition.

16.4 Prepared for:

CAIG Laboratories, Inc.
12200 Thatcher Court
Poway, CA 92064-6876
+1 (800) CAIG-123 (244-4123) phone
+1 (858) 486-8398 fax
<http://www.caig.com/>



16.5 Prepared by:

ShipMate, Inc.
PO Box 787
Sisters, OR 97759-0787 USA
Phone: +1 (310) 370-3600
Fax: +1 (310) 370-5700
e-mail: shipmate@shipmate.com





MATERIAL SAFETY DATA SHEET

Page 7 of 7
MSDS-E-DFG213

Prepared to OSHA, ACC, ANSI, WHMIS, NOHSC & 2001/58 EC Standards

MSDS Revision: 2.0

MSDS Revision Date: 01/06/2011

DEFINITION OF TERMS

A large number of abbreviations and acronyms appear on a MSDS. Some of these that are commonly used include the following:

GENERAL INFORMATION:

CAS No.	Chemical Abstract Service Number
---------	----------------------------------

EXPOSURE LIMITS IN AIR:

ACGIH	American Conference on Governmental Industrial Hygienists
TLV	Threshold Limit Value
OSHA	U.S. Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
IDLH	Immediately Dangerous to Life and Health

FIRST AID MEASURES:

CPR	Cardiopulmonary resuscitation - method in which a person whose heart has stopped receives manual chest compressions and breathing to circulate blood and provide oxygen to the body.
-----	--

HAZARDOUS MATERIALS IDENTIFICATION SYSTEM: HMIS

HEALTH, FLAMMABILITY & REACTIVITY RATINGS:

0	Minimal Hazard
1	Slight Hazard
2	Moderate Hazard
3	Severe Hazard
4	Extreme Hazard

HEALTH	
FLAMMABILITY	
PHYSICAL HAZARDS	
PERSONAL PROTECTION	

PERSONAL PROTECTION RATINGS:

A		G	
B		H	
C		I	
D		J	
E		K	
F		X	Consult your supervisor or S.O.P. for special handling directions.

Safety Glasses	Splash Goggles	Face Shield & Eye Protection	Gloves
Boots	Synthetic Apron	Full Suit	Dust Respirator
Vapor Respirator	Dust & Vapor Respirator	Full Face Respirator	Airline Hood/Mask or SCBA
Note: the dotted circle indicates that this respiratory protective equipment is required for high concentrations or for large volume spills or releases of product.			

OTHER STANDARD ABBREVIATIONS:

NA	Not Available
NR	No Results
NE	Not Established
NF	Not Found
ND	Not Determined
ML	Maximum Limit
SCBA	Self-Contained Breathing Apparatus


NATIONAL FIRE PROTECTION ASSOCIATION: NFPA

FLAMMABILITY LIMITS IN AIR:

Autoignition Temperature	Minimum temperature required to initiate combustion in air with no other source of ignition
LEL	Lower Explosive Limit - lowest percent of vapor in air, by volume, that will explode or ignite in the presence of an ignition source
UEL	Upper Explosive Limit - highest percent of vapor in air, by volume, that will explode or ignite in the presence of an ignition source

HAZARD RATINGS:

0	Minimal Hazard
1	Slight Hazard
2	Moderate Hazard
3	Severe Hazard
4	Extreme Hazard
ACD	Acidic
ALK	Alkaline
COR	Corrosive
-W	Use No Water
OX	Oxidizer



TOXICOLOGICAL INFORMATION:

LD ₅₀	Lethal Dose (solids & liquids) which kills 50% of the exposed animals
LC ₅₀	Lethal concentration (gases) which kills 50% of the exposed animal
ppm	Concentration expressed in parts of material per million parts
TD ₁₀	Lowest dose to cause a symptom
TCLO	Lowest concentration to cause a symptom
TD ₁₀ , LD ₁₀ , & LD ₀ or TC, TC ₀ , LC ₁₀ , & LC ₀	Lowest dose (or concentration) to cause lethal or toxic effects
IARC	International Agency for Research on Cancer
NTP	National Toxicology Program
RTECS	Registry of Toxic Effects of Chemical Substances
BCF	Bioconcentration Factor
TL _m	Median threshold limit
log K _{ow} or log K _{oc}	Coefficient of Oil/Water Distribution

REGULATORY INFORMATION:

WHMIS	Canadian Workplace Hazardous Material Information System
DOT	U.S. Department of Transportation
TC	Transport Canada
EPA	U.S. Environmental Protection Agency
DSL	Canadian Domestic Substance List
NDSL	Canadian Non-Domestic Substance List
PSL	Canadian Priority Substances List
TSCA	U.S. Toxic Substance Control Act
EU	European Union (European Union Directive 67/548/EEC)

EC INFORMATION:

C	E	F	N	O	T+	Xi	Xn
Corrosive	Explosive	Flammable	Harmful	Oxidizing	Toxic	Irritant	Harmful