

MATERIAL SAFETY DATA SHEET



Date Issued: 09/08/2010
MSDS No: 1572-Bulk

Eco-Stencil AQ

1. PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: Eco-Stencil AQ
PRODUCT DESCRIPTION: Stencil Cleaner Concentrate
PRODUCT CODE: 1572-Q,G,5G

MANUFACTURER

Techspray, L.P.
1001 N.W. 1st Street
P.O. Box 949
Amarillo TX 79107

Emergency Contact: Chemtrec
Product Stewardship: 1-800-858-4043
Service Number: 1-800-858-4043

24 HR. EMERGENCY TELEPHONE NUMBERS

CHEMTREC (US Transportation) :(800) 424 - 9300
CANUTEC (Canadian Transportation) :(613) 996 - 6666
Emergency Phone :(800) 858 - 4043

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

IMMEDIATE CONCERNS: Possible aspiration hazard if swallowed.

POTENTIAL HEALTH EFFECTS

EYES: Avoid contact with eyes; may cause redness, irritation and conjunctivitis.

SKIN: Prolonged or repeated contact can result in defatting and drying of the skin which may result in skin irritation and dermatitis (rash). Absorption through intact skin is possible.

SKIN ABSORPTION: No negative effects anticipated via absorption.

INGESTION: Ingestion may cause nausea and diarrhea.

INHALATION: No hazard in normal industrial use.

SIGNS AND SYMPTOMS OF OVEREXPOSURE

EYES: Symptoms of overexposure include: stinging, tearing, redness and pain.

SKIN: Prolonged or exposure may cause skin irritation.

SKIN ABSORPTION: Glycol ether ingredients may be absorbed through skin.

INGESTION: Aspiration hazard if swallowed.

INHALATION: Vapor inhalation can result in headache, nausea, and coordination problems.

CARCINOGENICITY: NOT listed

3. COMPOSITION / INFORMATION ON INGREDIENTS

MATERIAL SAFETY DATA SHEET



Date Issued: 09/08/2010
MSDS No: 1572-Bulk

Eco-Stencil AQ

Chemical Name	Wt.%	CAS	EINECS
3-methyl-3-methoxy-1-butanol	30 - 40	56539-66-3	
Aliphatic Ethoxylated Alcohols	10 - 25	78330-20-8	
Ethoxyl-Propoxyl Terpene	1 - 5	174955-61-4	
Poly(oxy-1,2-ethanediyl), a-hydro-w-hydroxy-	< 2	25322-68-3	xxx-xxx-x

4. FIRST AID MEASURES

EYES: Immediately flush eyes with plenty of water for at least 15 minutes. Get immediate medical attention.

SKIN: Immediately wash skin with soap and plenty of water. Remove contaminated clothing. Get medical attention if symptoms occur. Wash clothing before reuse.

INGESTION: If swallowed, gently wipe or rinse the inside of the mouth with water. DO NOT induce vomiting. Sips of water may be given if person is fully conscious. Never give anything by mouth to an unconscious or convulsing person. Immediately contact a poison control center, emergency room or physician as further treatment may be necessary.

INHALATION: Remove to fresh air. If not breathing, give artificial respiration or give oxygen by trained personnel. Seek immediate medical attention.

5. FIRE FIGHTING MEASURES

FLASHPOINT AND METHOD: None to boiling point --- TAG CC

EXTINGUISHING MEDIA: Use alcohol foam, carbon dioxide, or water spray when fighting fires involving this material.

6. ACCIDENTAL RELEASE MEASURES

LARGE SPILL: SPILLED MATERIAL IS EXTREMELY SLIPPERY. Dike area to contain spill. Take precautions as necessary to prevent contamination of ground and surface waters. Recover spilled material on adsorbent, such as sawdust or vermiculite, and sweep into closed containers for disposal. After all visible traces have been removed thoroughly mop and wet vacuum the area. Do not flush to sewer. If area of spill is porous, remove as much contaminated earth, gravel, etc. as necessary and place in closed containers for disposal.

GENERAL PROCEDURES: Isolate hazard area. Keep unnecessary and unprotected personnel from entering.

7. HANDLING AND STORAGE

HANDLING: Ground and bond containers when transferring material.

STORAGE: Store in a cool, dry area in a tightly closed container. Keep away from ignition sources.

STORAGE TEMPERATURE: 20°C Minimum to 30°C Maximum

MATERIAL SAFETY DATA SHEET



Date Issued: 09/08/2010
MSDS No: 1572-Bulk

Eco-Stencil AQ

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

ENGINEERING CONTROLS: Local exhaust ventilation may be necessary to control any air contaminants to within their TLVs during the use of this product.

PERSONAL PROTECTIVE EQUIPMENT

EYES AND FACE: For normal conditions, wear safety glasses. Where there is reasonable probability of liquid contact, wear splash-proof goggles.

SKIN: Gloves of the following materials may provide protection against permeation: Viton, solvex, Buna, Butyl, and Neoprene.

RESPIRATORY: NIOSH/MSHA approved air purifying respirator with an organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits. Protection provided by air purifying respirators is limited. Use a positive pressure air supplied respirator if there is any potential for an uncontrolled release, exposure levels are not known, or any other circumstances where air purifying respirators may not provide adequate protection.

WORK HYGIENIC PRACTICES: Wash hands before eating and wash before reuse.

OTHER USE PRECAUTIONS: Emergency shower and eyewash facility should be in close proximity.

9. PHYSICAL AND CHEMICAL PROPERTIES

PHYSICAL STATE: Liquid

ODOR: Clean ethereal odor

APPEARANCE: Clear, mobile liquid.

COLOR: Light blue.

pH: 7 to 8

BOILING POINT: 90°C (194°F)

Notes: Initial boiling point

FLASHPOINT AND METHOD: None to boiling point --- TAG CC

SOLUBILITY IN WATER: Fully miscible

EVAPORATION RATE: < 1 (H₂O=1)

DENSITY: ~ 1 at 25°C (77°F)

(VOC): < 5.500 % by weight (EPA)

Notes: When diluted as recommended.

10. STABILITY AND REACTIVITY

STABILITY: Stable under normal conditions.

POLYMERIZATION: Will not occur.

CONDITIONS TO AVOID: Heat, flames, ignition sources, and incompatibles.

MATERIAL SAFETY DATA SHEET



Date Issued: 09/08/2010
MSDS No: 1572-Bulk

Eco-Stencil AQ

HAZARDOUS DECOMPOSITION PRODUCTS: Hazardous decomposition products include oxides of carbon and nitrogen.

INCOMPATIBLE MATERIALS: Oxidizing materials.

11. TOXICOLOGICAL INFORMATION

EYE EFFECTS: Mixture is a moderate eye irritant.

SKIN EFFECTS: The mixture is a mild to severe skin irritant but is not a skin sensitizer in animals.

CARCINOGENICITY

IARC: NOT listed

NTP: NOT listed

OSHA: NOT listed

12. ECOLOGICAL INFORMATION

ENVIRONMENTAL DATA: There is limited information available on the environmental fate and effects of this material. The primary environmental concern for release is the impact on aquatic and terrestrial species. Due care should be taken to avoid the accidental release of this material into the environment.

13. DISPOSAL CONSIDERATIONS

DISPOSAL METHOD: Federal, State, and Local laws governing disposal of materials can differ. Ensure compliance with proper authorities before disposal.

14. TRANSPORT INFORMATION

DOT (DEPARTMENT OF TRANSPORTATION)

PROPER SHIPPING NAME: Not regulated

ROAD AND RAIL (ADR/RID)

PROPER SHIPPING NAME: Not regulated

AIR (ICAO/IATA)

SHIPPING NAME: Not regulated

VESSEL (IMO/IMDG)

SHIPPING NAME: Not regulated

15. REGULATORY INFORMATION

UNITED STATES

SARA TITLE III (SUPERFUND AMENDMENTS AND REAUTHORIZATION ACT)

PRESSURE GENERATING: Yes **ACUTE:** Yes **CHRONIC:** Yes

MATERIAL SAFETY DATA SHEET



Date Issued: 09/08/2010
MSDS No: 1572-Bulk

Eco-Stencil AQ

313 REPORTABLE INGREDIENTS: Not considered a SARA 313 "Toxic Chemical".

CERCLA (COMPREHENSIVE RESPONSE, COMPENSATION, AND LIABILITY ACT)

CERCLA REGULATORY: None of the ingredients are CERCLA/Superfund hazardous chemicals.

TSCA (TOXIC SUBSTANCE CONTROL ACT)

Chemical Name	CAS
3-methyl-3-methoxy-1-butanol	56539-66-3
Poly(oxy-1,2-ethanediyl), a-hydro-w-hydroxy-	25322-68-3

OCCUPATIONAL SAFETY AND HEALTH ADMINISTRATION (OSHA)

29 CFR1910.119---PROCESS SAFETY MANAGEMENT OF HIGHLY HAZARDOUS

CHEMICALS: None of the chemicals in this product are considered highly hazardous by OSHA.

CALIFORNIA PROPOSITION 65: This product contains no listed substances known to the State of California to cause cancer, birth defects or other reproductive harm, at levels which would require a warning under the statute.

CANADA

WHMIS CLASS: Class D2B - Toxic Materials

16. OTHER INFORMATION


APPROVED BY: Pierce A. Pillon **TITLE:** Chemist

REVISION SUMMARY: New MSDS

HMIS RATING

HEALTH:	1
FLAMMABILITY:	1
PHYSICAL HAZARD:	0
PERSONAL PROTECTION:	C

NFPA CODES



MANUFACTURER DISCLAIMER: To the best of our knowledge, the information contained herein is accurate. However, neither Tech Spray, LLC, or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards which exist.