



## Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

### SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

**PRODUCT NAME:** SHARPSHOOTER(TM) EXTRA STRENGTH NO RINSE MARK REMOVER  
**MANUFACTURER:** 3M  
**DIVISION:** Building & Commercial Services Division  
**ADDRESS:** 3M Center, St. Paul, MN 55144-1000

**EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)**

**Issue Date:** 03/30/11  
**Supersedes Date:** 01/19/10

**Document Group:** 19-7627-3

#### Product Use:

**Specific Use:** This no-rinse cleaner removes tough stains such as grease, lipstick, crayon, black heel marks, pencil marks and smoke film from most washable hard surfaces.  
**Intended Use:** Hard Surface Cleaner

### SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
WATER	7732-18-5	80 - 95
2-BUTOXYETHANOL	111-76-2	3 - 7
ETHANOLAMINE	141-43-5	1 - 5
ALCOHOLS, C6-12, ETHOXYLATED	68439-45-2	0.5 - 1.5
ALCOHOLS, C12-14-SECONDARY, ETHOXYLATED	84133-50-6	0.5 - 1.5

### SECTION 3: HAZARDS IDENTIFICATION

#### 3.1 EMERGENCY OVERVIEW

**Odor, Color, Grade:** Clear, colorless; mild solvent odor

**General Physical Form:** Liquid

**Immediate health, physical, and environmental hazards:** Contact with aluminum or zinc in a pressurized system may generate hydrogen gas which could create an explosion hazard. May cause chemical eye burns. May cause target organ effects.

### 3.2 POTENTIAL HEALTH EFFECTS

**Eye Contact:**

Corrosive (Eye Burns): Signs/symptoms may include cloudy appearance of the cornea, chemical burns, severe pain, tearing, ulcerations, significantly impaired vision or complete loss of vision.

**Skin Contact:**

Moderate Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, and dryness.  
May be absorbed through skin and cause target organ effects.

**Inhalation:**

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.  
May be absorbed following inhalation and cause target organ effects.

**Ingestion:**

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.  
May be absorbed following ingestion and cause target organ effects.

**Target Organ Effects:**

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Blood Effects: Signs/symptoms may include generalized weakness and fatigue, skin pallor, changes in blood clotting time, internal bleeding, and/or hemoglobinemia.

Prolonged or repeated exposure may cause:

Liver Effects: Signs/symptoms may include loss of appetite, weight loss, fatigue, weakness, abdominal tenderness and jaundice.

Kidney/Bladder Effects: Signs/symptoms may include changes in urine production, abdominal or lower back pain, increased protein in urine, increased blood urea nitrogen (BUN), blood in urine, and painful urination.

## SECTION 4: FIRST AID MEASURES

### 4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

**Eye Contact:** Immediately flush eyes with large amounts of water for at least 15 minutes. Get immediate medical attention.

**Skin Contact:** Remove contaminated clothing and shoes. Immediately flush skin with large amounts of water. Get medical attention. Wash contaminated clothing and clean shoes before reuse.

**Inhalation:** Remove person to fresh air. If signs/symptoms develop, get medical attention.

**If Swallowed:** Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

## SECTION 5: FIRE FIGHTING MEASURES

### 5.1 FLAMMABLE PROPERTIES

Autoignition temperature	<i>Not Applicable</i>
Flash Point	<i>Not Applicable</i>
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>

## 5.2 EXTINGUISHING MEDIA

Non-combustible. Choose material suitable for surrounding fire.

## 5.3 PROTECTION OF FIRE FIGHTERS

**Special Fire Fighting Procedures:** Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

**Unusual Fire and Explosion Hazards:** Contact with aluminum or zinc in a pressurized system may generate hydrogen gas which could create an explosion hazard. Non-flammable: ordinary combustible material.

**Note:** See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Personal precautions, protective equipment and emergency procedures

### 6.2. Environmental precautions

#### Clean-up methods

Refer to other sections of this MSDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment. Call 3M-HELPS line (1-800-364-3577) for more information on handling and managing the spill. Clean up residue with water.

**In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.**

## SECTION 7: HANDLING AND STORAGE

### 7.1 HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Keep away from aluminum and zinc. Avoid breathing of vapors, mists or spray. Keep out of the reach of children. Avoid skin contact. Avoid eye contact.

### 7.2 STORAGE

Store away from areas where product may come into contact with food or pharmaceuticals. Store under normal warehouse conditions.

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### 8.1 ENGINEERING CONTROLS

Use in an enclosed process area is recommended. Use in a well-ventilated area. Do not use in a confined area or areas with little or no air movement.

### 8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

**8.2.1 Eye/Face Protection**

Avoid eye contact with vapors, mists, or spray.  
 The following eye protection(s) are recommended: Full Face Shield  
 Indirect Vented Goggles.

**8.2.2 Skin Protection**

Avoid skin contact.  
 Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.  
 Gloves made from the following material(s) are recommended: Butyl Rubber  
 Neoprene  
 Nitrile Rubber

**8.2.3 Respiratory Protection**

Avoid breathing of vapors, mists or spray. Under normal use conditions, airborne exposures are not expected to be significant enough to require respiratory protection.

**8.2.4 Prevention of Swallowing**

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

**8.3 EXPOSURE GUIDELINES**

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
ETHANOLAMINE	ACGIH	TWA	3 ppm	
ETHANOLAMINE	ACGIH	STEL	6 ppm	
ETHANOLAMINE	OSHA	TWA	6 mg/m3	
2-BUTOXYETHANOL	ACGIH	TWA	20 ppm	
2-BUTOXYETHANOL	OSHA	TWA	240 mg/m3	Skin Notation*

\* Substance(s) refer to the potential contribution to the overall exposure by the cutaneous route including mucous membrane and eye, either by airborne or, more particularly, by direct contact with the substance. Vehicles can alter skin absorption.

SOURCE OF EXPOSURE LIMIT DATA:

- ACGIH: American Conference of Governmental Industrial Hygienists
- CMRG: Chemical Manufacturer Recommended Guideline
- OSHA: Occupational Safety and Health Administration
- AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

**SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES**

<b>Odor, Color, Grade:</b>	Clear, colorless; mild solvent odor
<b>General Physical Form:</b>	Liquid
<b>Autoignition temperature</b>	<i>Not Applicable</i>
<b>Flash Point</b>	<i>Not Applicable</i>
<b>Flammable Limits(LEL)</b>	<i>Not Applicable</i>
<b>Flammable Limits(UEL)</b>	<i>Not Applicable</i>
<b>Boiling Point</b>	Approximately 212 °F
<b>Density</b>	Approximately 1.002 g/ml
<b>Vapor Pressure</b>	< 27 psia [@ 131 °F]
<b>Specific Gravity</b>	Approximately 1.01 [Ref Std: WATER=1]

pH	12.5 - 13.5
Solubility in Water	Complete
Evaporation rate	Approximately 1 [ <i>Ref Std:</i> WATER=1]
Volatile Organic Compounds	5 - 10 % [ <i>Test Method:</i> calculated per CARB title 2]
Percent volatile	64 - 100 % weight
VOC Less H2O & Exempt Solvents	577 - 1154 g/l [ <i>Test Method:</i> calculated per CARB title 2]
Viscosity	< 100 centipoise

## SECTION 10: STABILITY AND REACTIVITY

**Stability:** Stable.

**Materials and Conditions to Avoid:**

**10.1 Conditions to avoid**

None known

**10.2 Materials to avoid**

None known

**Hazardous Polymerization:** Hazardous polymerization will not occur.

### Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	Not Specified
Carbon dioxide	Not Specified
Oxides of Nitrogen	Not Specified

## SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

## SECTION 12: ECOLOGICAL INFORMATION

### ECOTOXICOLOGICAL INFORMATION

Not determined.

### CHEMICAL FATE INFORMATION

Not determined.

## SECTION 13: DISPOSAL CONSIDERATIONS

**Waste Disposal Method:** Dispose of waste product in a permitted hazardous waste facility.

**EPA Hazardous Waste Number (RCRA):** D002 (Corrosive)

Since regulations vary, consult applicable regulations or authorities before disposal.

## SECTION 14: TRANSPORT INFORMATION

**ID Number(s):**

70-0712-8530-1, 70-0712-8531-9, 70-0712-8533-5, 70-0712-8534-3

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

## SECTION 15: REGULATORY INFORMATION

### US FEDERAL REGULATIONS

**311/312 Hazard Categories:**

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

**Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):**

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
2-BUTOXYETHANOL (GLYCOL ETHERS)	111-76-2	3 - 7

### STATE REGULATIONS

### CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

The components of this material are in compliance with the new chemical notification requirements for the Korean Existing Chemicals Inventory.

The components of this product are listed on the Australian Inventory of Chemical Substances.

All the components of this product are listed on China's Inventory of Chemical Substances.

The components of this product are listed on the Canadian Domestic Substances List.

### INTERNATIONAL REGULATIONS

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

## SECTION 16: OTHER INFORMATION

**NFPA Hazard Classification**

**Health: 3 Flammability: 0 Reactivity: 0 Special Hazards: None**

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Revision Changes:

Section 16: Disclaimer (second paragraph) was modified.  
Section 8: Eye/face protection information was modified.  
Section 8: Skin protection - recommended gloves information was modified.  
Section 14: Transportation legal text was modified.  
Section 9: Vapor pressure value was modified.  
Section 9: Boiling point information was modified.  
Section 5: Flammable limits (UE) information was modified.  
Section 5: Flammable limits (LEL) information was modified.  
Section 9: Flammable limits (LEL) information was modified.  
Section 9: Flammable limits (UEL) information was modified.  
Section 8: Exposure guidelines ingredient information was modified.  
Section 10: Materials to avoid physical property was modified.  
Section 10: Conditions to avoid physical property was modified.  
Section 14: ID Number Heading Template 1 was added.  
Section 14: ID Number(s) Template 1 was added.  
Section 6: 6.2. Environmental precautions heading was added.  
Section 6: 6.1. Personal precautions, protective equipment and emergency procedures heading was added.  
Section 16: Web address was added.  
Section 1: Address was added.  
Copyright was added.  
Company logo was added.  
Section 6: Clean-up methods heading was added.  
Telephone header was added.  
Company Telephone was added.  
Section 1: Emergency phone information was added.  
Section 1: Emergency phone information was deleted.  
Company Logo was deleted.  
Copyright was deleted.  
Section 16: Web address heading was deleted.  
Section 6: Release measures heading was deleted.  
Section 1: Address line 1 was deleted.  
Section 1: Address line 2 was deleted.  
Section 8: Exposure guidelines legend was deleted.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

**3M USA MSDSs are available at [www.3M.com](http://www.3M.com)**



## Transport Information Document

**Date:** April 24, 2012

**3M ID Number:** 70-0712-8531-9

**Product Description:** 3M(TM) Sharpshooter(TM) Extra Strength No-Rinse Mark Remover, Quart, 12/case

**Transport Protective Service:** PROTECTIVE SERVICE NOT REQUIRED

**NMFC Item:** 048580

**NMFC Sub:** 03

**NMFC Class:** 055.0

**Flash Point (Closed-cup):** No Flash Point

### UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

NOT REGULATED

### UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

NOT REGULATED

### INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

NOT REGULATED

### INTERNATIONAL MARITIME ORGANIZATION (IMO)

NOT REGULATED

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit [3M.com/Transportinfo](http://3M.com/Transportinfo)  
or call 1-800-364-3577 or 651-737-6501 for assistance.