

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002

MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

1. PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: Zero Charge Anti Stat

PRODUCT DESCRIPTION: Zero Charge Anti-Stat

PRODUCT CODE: 1726/CAN/EUR-2FP, PT,QT, G, 5G

ACTIVE INGREDIENT(S): Water

MANUFACTURER

Techspray, L.P.
1001 N.W. 1st Street
P.O. Box 949
Amarillo TX 79107

Emergency Contact: Chemtrec

Product Stewardship: 1-800-858-4043

Service Number: 1-800-858-4043

24 HR. EMERGENCY TELEPHONE NUMBERS

CHEMTREC (US Transportation) :(800) 424 - 9300

CANUTEC (Canadian Transportation) :(613) 996 - 6666

Emergency Phone :(800) 858 - 4043

2. HAZARDS IDENTIFICATION

HAZARD DESIGNATION

"Xn" - Harmful

R20/22 - Harmful by inhalation and if swallowed.

"Xi" - Irritant

R36/38 - Irritating to eyes and skin.

EMERGENCY OVERVIEW

IMMEDIATE CONCERNS: Contains small amounts of methanol, which is harmful if swallowed.

POTENTIAL HEALTH EFFECTS

EYES: Moderately irritating to the eyes.

SKIN: Prolonged or repeated contact can result in defatting and drying of the skin which may result in skin irritation and dermatitis (rash).

SKIN ABSORPTION: No negative effects anticipated via absorption.

INGESTION: Harmful if swallowed --- contains small amounts of methanol.

INHALATION: No hazard in normal industrial use.

SIGNS AND SYMPTOMS OF OVEREXPOSURE

EYES: Symptoms of overexposure include: stinging, tearing, redness and pain.

SKIN: Prolonged exposure causes redness, pain, drying and cracking of the skin.

SKIN ABSORPTION: None Expected.

INGESTION: Ingestion may result in diarrhea and/or nausea.

INHALATION: No observable effects of overexposure.

ACUTE TOXICITY: Low hazard for usual industrial or commercial handling.

CHRONIC EFFECTS: Not Established

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002

MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

CARCINOGENICITY: Not Available

MUTAGENICITY: Not Established

REPRODUCTIVE TOXICITY

TERATOGENIC EFFECTS: Contains Methanol which has been established as a teratogen by inhalation. See Sec.11 for details.

3. COMPOSITION / INFORMATION ON INGREDIENTS

| Chemical Name | Wt. % | CAS | EINECS |
|--|---------|------------|-----------|
| Water | 80 - 90 | 7732-18-5 | 231-791-2 |
| Ethylbis (hydroxyethyl) tallow alkyl, ethoxylated, Et sulfates | 1 - 5 | 68071-95-4 | |
| Ethanol | 5 - 10 | 64-17-5 | 200-578-6 |
| 2-Propanol | < 1 | 67-63-0 | 200-661-0 |
| Methanol | < 1 | 67-56-1 | 200-659-6 |

4. FIRST AID MEASURES

EYES: Immediately flush eyes with plenty of water. Get medical attention, if irritation persists.

SKIN: Wash with soap and water. Get medical attention if irritation develops or persists.

INGESTION: If swallowed, do not induce vomiting. If conscious and alert, give two glasses of water. Seek medical attention.

INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.

5. FIRE FIGHTING MEASURES

FLASHPOINT AND METHOD: None

FLAMMABLE LIMITS: NA to NA

EXTINGUISHING MEDIA: Water, foam, dry chemical, carbon dioxide.

HAZARDOUS COMBUSTION PRODUCTS: Smoke, fumes and oxides of carbon.

FIRE FIGHTING EQUIPMENT: As in any fire, wear self-contained breathing apparatus pressure-demand, (MSHA/NIOSH approved or equivalent) and full protective gear.

HAZARDOUS DECOMPOSITION PRODUCTS: None Expected.

6. ACCIDENTAL RELEASE MEASURES

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002

MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

SMALL SPILL: Avoid runoff into storm sewers and ditches which lead to waterways.

GENERAL PROCEDURES: Absorb the liquid and scrub the area with detergent and water.

7. HANDLING AND STORAGE

GENERAL PROCEDURES: Wash thoroughly after handling. Use only in a well ventilated area. Follow all MSDS/label precautions even after container is emptied because they may retain product residues. Store in a cool dry place.

HANDLING: Use with adequate ventilation.

STORAGE: Store in a cool place in original container and protect from sunlight.

STORAGE TEMPERATURE: Store in adequate storage area at ambient temp.

STORAGE PRESSURE: Store at local atmospheric pressure.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

EXPOSURE GUIDELINES

| OSHA HAZARDOUS COMPONENTS (29 CFR1910.1200) | | | | | | | |
|--|------|-----------------|---------------------------|-----------|------------------------|-------------|----------------------|
| | | EXPOSURE LIMITS | | | | | |
| | | OSHA PEL | | ACGIH TLV | | SupplierOEL | |
| Chemical Name | | ppm | mg/m ³ | ppm | mg/m ³ | ppm | mg/m ³ |
| Ethanol | TWA | 1000 ppm | 1900 mg/m ³ | 1000 ppm | 1880 mg/m ³ | NL | NL |
| | STEL | NL ppm | NL mg/m ³ | NL ppm | NL mg/m ³ | NL | NL |
| 2-Propanol | TWA | 400 ppm | 980 mg/m ³ | 400 ppm | 983 mg/m ³ | NL [1] | NL [1] |
| | STEL | 500 ppm | 1225 mg/m ³ | 500 ppm | 1230 mg/m ³ | NL | NL |
| Methanol | TWA | S 200 ppm [2] | 260 mg/m ³ [2] | S 200 ppm | 262 mg/m ³ | NL ppm | NL mg/m ³ |
| | STEL | 250 ppm | 310 mg/m ³ | 250 ppm | 328 mg/m ³ | NL ppm | NL |
| OSHA TABLE COMMENTS: 1. NL = Not Listed 2. S = Skin | | | | | | | |

PERSONAL PROTECTIVE EQUIPMENT

EYES AND FACE: For normal conditions, wear safety glasses. Where there is reasonable probability of

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002

MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

liquid contact, wear splash-proof goggles.

SKIN: The glove(s) listed below may provide protection against permeation. Gloves of other chemically resistant materials may not provide adequate protection. Viton, Solvex, Butyl, Buna, Neoprene.

RESPIRATORY: NIOSH/MSHA approved air purifying respirator with an organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits. Protection provided by air purifying respirators is limited. Use a positive pressure air supplied respirator if there is any potential for an uncontrolled release, exposure levels are not known, or any other circumstances where air purifying respirators may not provide adequate protection.

PROTECTIVE CLOTHING: NOT listed

WORK HYGIENIC PRACTICES: Wash hands before eating and wash before reuse.

9. PHYSICAL AND CHEMICAL PROPERTIES

| Chemical Name | Flash Point (°C) | Boiling Point (°C) | Specific Gravity |
|---------------|------------------|--------------------|------------------|
| 2-Propanol | 53.6 | 82.4 | 0.785 |

PHYSICAL STATE: Liquid

ODOR: Pleasant

APPEARANCE: Clear, Colorless liquid

COLOR: Colorless

pH: 7.0

PERCENT VOLATILE: 97

VAPOR PRESSURE: Not Applicable

VAPOR DENSITY: Not Available

BOILING POINT: 100°C (212°F) (760 mmHg)

FREEZING POINT: 0°C (32°F)

FLASHPOINT AND METHOD: None

SOLUBILITY IN WATER: 100

Notes: % by weight in water

EVAPORATION RATE: Not Established

DENSITY: 0.978 at 25°C

VISCOSITY: Not Applicable

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002

MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

MOLECULAR WEIGHT: Not Applicable

(VOC): 58.140 g/L

10. STABILITY AND REACTIVITY

STABLE: No

HAZARDOUS POLYMERIZATION: No

STABILITY: Stable.

POLYMERIZATION: Will not occur.

HAZARDOUS DECOMPOSITION PRODUCTS: Oxides of Carbon (CO and CO₂) may form when heated to decomposition.

INCOMPATIBLE MATERIALS: Strong acids and alkalis, reactive metals and strong oxidizing agents.

11. TOXICOLOGICAL INFORMATION

ACUTE

| Chemical Name | ORAL LD ₅₀ (rat) | DERMAL LD ₅₀ (rabbit) | INHALATION LC ₅₀ (rat) |
|---------------|--------------------------------|-------------------------------------|-----------------------------------|
| Methanol | 6.2 to 12.98 mg/kg | 16 g/kg | 64000 ppm |

EYES: Moderately to severely irritating

DERMAL LD₅₀: Not Established

SKIN ABSORPTION: Not Established

ORAL LD₅₀: Not Established

INHALATION LC₅₀: None Expected.

NOTES: Not Established

EYE EFFECTS: Mixture is a moderate eye irritant.

SKIN EFFECTS: Draize test, rabbit, skin: 500 mg Mild.

CHRONIC: Not Established

SUBCHRONIC: Not Established

CARCINOGENICITY

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002

MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

| Chemical Name | NTP Status | IARC Status | OSHA Status |
|---------------|------------|-------------|-------------|
| Ethanol | NOT LISTED | NOT LISTED | NOT LISTED |
| 2-Propanol | NOT LISTED | NOT LISTED | NOT LISTED |
| Methanol | NOT LISTED | NOT LISTED | NOT LISTED |

IARC: Not Established

NEUROTOXICITY: None Expected.

REPRODUCTIVE EFFECTS: None known.

TERATOGENIC EFFECTS: Not Established

MUTAGENICITY: Not Established

12. ECOLOGICAL INFORMATION

ENVIRONMENTAL DATA: Not Available

ECOTOXICOLOGICAL INFORMATION: Isopropyl alcohol has a high biochemical oxygen demand and a potential to cause oxygen depletion in aqueous systems, a low potential to affect aquatic organisms, a low potential to affect secondary waste treatment microbial metabolism, a low potential to affect the germination of some plants, a high potential to biodegrade (low persistence) with unacclimated microorganisms from activated sludge.

13. DISPOSAL CONSIDERATIONS

DISPOSAL METHOD: Federal, State, and Local laws governing disposal of materials can differ. Ensure compliance with proper authorities before disposal.

GENERAL COMMENTS: Dispose of in a manner consistent with federal, state, and local regulations.

14. TRANSPORT INFORMATION

DOT (DEPARTMENT OF TRANSPORTATION)

PROPER SHIPPING NAME: Nonhazardous

PRIMARY HAZARD CLASS/DIVISION: Not Regulated

UN/NA NUMBER: NA

PACKING GROUP: NA

ROAD AND RAIL (ADR/RID)

HAZARD CLASS: Not Regulated

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002

MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

AIR (ICAO/IATA)

SHIPPING NAME: Nonhazardous

UN/NA NUMBER: NA

PRIMARY HAZARD CLASS/DIVISION: Not Regulated

PACKING GROUP: NA

VESSEL (IMO/IMDG)

SHIPPING NAME: Nonhazardous

UN/NA NUMBER: NA

PRIMARY HAZARD CLASS/DIVISION: Not Regulated

PACKING GROUP: NA

15. REGULATORY INFORMATION

UNITED STATES

SARA TITLE III (SUPERFUND AMENDMENTS AND REAUTHORIZATION ACT)

311/312 HAZARD CATEGORIES: ACUTE

FIRE: No **PRESSURE GENERATING:** No **REACTIVITY:** No **ACUTE:** Yes **CHRONIC:** No

313 REPORTABLE INGREDIENTS: Methanol (<1%) 2-propanol (<1%)

EPCRA SECTION 313 SUPPLIER NOTIFICATION

| Chemical Name | Wt. % | CAS |
|---------------|-------|---------|
| 2-Propanol | < 1 | 67-63-0 |

302/304 EMERGENCY PLANNING

EMERGENCY PLAN: Methanol (#67-56-1)

CERCLA (COMPREHENSIVE RESPONSE, COMPENSATION, AND LIABILITY ACT)

CERCLA REGULATORY: Methanol (#67-56-1)

| Chemical Name | Wt. % | CERCLA RQ |
|---------------|-------|-----------|
| Methanol | < 1 | 5000 lbs. |

CERCLA RQ: 5000 lbs

TSCA (TOXIC SUBSTANCE CONTROL ACT)

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002

MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

| Chemical Name | CAS |
|---------------|-----------|
| Water | 7732-18-5 |
| Ethanol | 64-17-5 |
| 2-Propanol | 67-63-0 |
| Methanol | 67-56-1 |

TSCA STATUS: All components of this product are either listed or exempt from listing in the TSCA inventory.

CLEAN AIR ACT

40 CFR PART 68---RISK MANAGEMENT FOR CHEMICAL ACCIDENT RELEASE

PREVENTION: Methanol (CAS# 67-56-1)

OCCUPATIONAL SAFETY AND HEALTH ADMINISTRATION (OSHA)

29 CFR1910.119---PROCESS SAFETY MANAGEMENT OF HIGHLY HAZARDOUS

CHEMICALS: None of the chemicals in this product are considered highly hazardous by OSHA.

CALIFORNIA PROPOSITION 65: This product does not contain any chemicals known to the State of California to cause cancer.

RCRA STATUS: U154

OSHA HAZARD COMM. RULE: Contents of this MSDS comply with the OSHA Hazard Communication Standard 29 CFR 1910.1200.

EUROPEAN COMMUNITY

EEC LABEL SYMBOL AND CLASSIFICATION



"Xn" - Harmful
R20/22 - Harmful by inhalation and if swallowed.



"Xi" - Irritant
R36/38 - Irritating to eyes and skin.

16. OTHER INFORMATION

APPROVED BY: Pierce A. Pillon **TITLE:** Chemist

PREPARED BY: Steve Cook

REVISION SUMMARY: Revision #: 6. This MSDS replaces the November 30, 2006 MSDS. Any changes in information are as follows: In Section 1: Comments

MATERIAL SAFETY DATA SHEET

Finished Product



Date Issued: 12/31/2002


MSDS No: 1726

Date Revised: 11/11/2009

Revision No: 6

Zero Charge Anti Stat

NFPA CODES



DATA SOURCES: Code of Federal Regulations (CFR) The Sigma-Aldrich Library of Regulatory and Safety Data OSHA Hazard Communication Standard (29CFR1910.1200) Various Federal, State and Local Regulations

MANUFACTURER DISCLAIMER: To the best of our knowledge, the information contained herein is accurate. However, neither Tech Spray, L.P., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards which exist.