

DOW CORNING CORPORATION
Material Safety Data Sheet

Page: 1 of 8

Version: 1.8

Revision Date: 2011/11/15

DOW CORNING(R) 734 FLOWABLE SEALANT, CLEAR**1. PRODUCT AND COMPANY IDENTIFICATION**

Dow Corning Corporation
South Saginaw Road
Midland, Michigan 48686

24 Hour Emergency Telephone: (989) 496-5900

Customer Service: (989) 496-6000

Product Disposal Information: (989) 496-6315

CHEMTREC: (800) 424-9300

MSDS No.: 01907506

Revision Date: 2011/11/15

Generic Description: Silicone elastomer

Physical Form: Viscous Liquid

Color: Colorless

Odor: Acetic acid odor

NFPA Profile: Health 1 Flammability 2 Instability/Reactivity 0

Note: NFPA = National Fire Protection Association

2. HAZARDS IDENTIFICATION**POTENTIAL HEALTH EFFECTS****Acute Effects**

Eye: Direct contact may cause mild irritation.

Skin: May cause mild irritation.

Inhalation: No significant effects expected from a single short-term exposure.

Oral: Low ingestion hazard in normal use.

Prolonged/Repeated Exposure Effects

Skin: No known applicable information.

Inhalation: No known applicable information.

Oral: No known applicable information.

Signs and Symptoms of Overexposure

No known applicable information.

Medical Conditions Aggravated by Exposure

No known applicable information.

DOW CORNING(R) 734 FLOWABLE SEALANT, CLEAR

The above listed potential effects of overexposure are based on actual data, results of studies performed upon similar compositions, component data and/or expert review of the product. Please refer to Section 11 for the detailed toxicology information.

3. COMPOSITION/INFORMATION ON INGREDIENTS

<u>CAS Number</u>	<u>Wt %</u>	<u>Component Name</u>
4253-34-3	1.0 - 5.0	Methyltriacetoxysilane

The above components are hazardous as defined in 29 CFR 1910.1200.

4. FIRST AID MEASURES

Eye:	Immediately flush the contaminated eye(s) with lukewarm, gently flowing water for 5 minutes while holding the eyelid(s) open. Obtain medical attention.
Skin:	No health effects expected. If irritation does occur flush with lukewarm, gently flowing water for 5 minutes. If irritation persists, obtain medical advice.
Inhalation:	If symptoms are experienced remove source of contamination or move victim to fresh air. If irritation persists, obtain medical advice.
Oral:	If irritation or discomfort occur, obtain medical advice.
Notes to Physician:	Treat according to person's condition and specifics of exposure.

5. FIRE FIGHTING MEASURES

Flash Point:	188.6 °F / 87 °C (Closed Cup)
Autoignition Temperature:	Not determined.
Flammability Limits in Air:	Not determined.
Extinguishing Media:	On large fires use dry chemical, foam or water spray. On small fires use carbon dioxide (CO ₂), dry chemical or water spray. Water can be used to cool fire exposed containers.
Fire Fighting Measures:	Self-contained breathing apparatus and protective clothing should be worn in fighting large fires involving chemicals. Determine the need to evacuate or isolate the area according to your local emergency plan. Use water spray to keep fire exposed containers cool.
Unusual Fire Hazards:	None.

DOW CORNING CORPORATION
Material Safety Data Sheet

Page: 3 of 8

Version: 1.8

Revision Date: 2011/11/15

DOW CORNING(R) 734 FLOWABLE SEALANT, CLEAR**6. ACCIDENTAL RELEASE MEASURES**

Containment/Clean up: Determine whether to evacuate or isolate the area according to your local emergency plan. Observe all personal protection equipment recommendations described in Sections 5 and 8. For large spills, provide diking or other appropriate containment to keep material from spreading. If diked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absorbant. Clean area as appropriate since spilled materials, even in small quantities, may present a slip hazard. Final cleaning may require use of steam, solvents or detergents. Dispose of saturated absorbant or cleaning materials appropriately, since spontaneous heating may occur. Local, state and federal laws and regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which federal, state and local laws and regulations are applicable. Sections 13 and 15 of this MSDS provide information regarding certain federal and state requirements.

Note: See Section 8 for Personal Protective Equipment for Spills. Call (989) 496-5900, if additional information is required.

7. HANDLING AND STORAGE

Use with adequate ventilation. Product evolves acetic acid (HOAc) when exposed to water or humid air. Provide ventilation during use to control HOAc within exposure guidelines or use respiratory protection. Avoid eye contact. Avoid skin contact.

Static electricity will accumulate and may ignite vapors. Prevent a possible fire hazard by bonding and grounding or inert gas purge. Keep container closed and away from heat, sparks, and flame. Keep container closed and store away from water or moisture.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION**Component Exposure Limits**

<u>CAS Number</u>	<u>Component Name</u>	<u>Exposure Limits</u>
4253-34-3	Methyltriacetoxysilane	See acetic acid comments.

Acetic acid is formed upon contact with water or humid air. Provide adequate ventilation to control exposures within guidelines of OSHA PEL: TWA 10 ppm and ACGIH TLV: TWA 10 ppm, STEL 15 ppm.

Engineering Controls

Local Ventilation: Recommended.
General Ventilation: Recommended.

Personal Protective Equipment for Routine Handling

DOW CORNING(R) 734 FLOWABLE SEALANT, CLEAR

Eyes:	Use proper protection - safety glasses as a minimum.
Skin:	Wash at mealtime and end of shift. Contaminated clothing and shoes should be removed as soon as practical and thoroughly cleaned before reuse. Chemical protective gloves are recommended.
Suitable Gloves:	Handle in accordance with good industrial hygiene and safety practices.
Inhalation:	No respiratory protection should be needed.
Suitable Respirator:	None should be needed.

Personal Protective Equipment for Spills

Eyes:	Use proper protection - safety glasses as a minimum.
Skin:	Wash at mealtime and end of shift. Contaminated clothing and shoes should be removed as soon as practical and thoroughly cleaned before reuse. Chemical protective gloves are recommended.
Inhalation/Suitable Respirator:	No respiratory protection should be needed.
Precautionary Measures:	Avoid eye contact. Avoid skin contact. Use reasonable care.
Comments:	Product evolves acetic acid (HOAc) when exposed to water or humid air. Provide ventilation during use to control HOAc within exposure guidelines or use respiratory protection.

Note: These precautions are for room temperature handling. Use at elevated temperature or aerosol/spray applications may require added precautions. For further information regarding aerosol inhalation toxicity, please refer to the guidance document regarding the use of silicone-based materials in aerosol applications that has been developed by the silicone industry (www.SEHSC.com) or contact the Dow Corning customer service group.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical Form:	Viscous Liquid
Color:	Colorless
Odor:	Acetic acid odor
Specific Gravity @ 25°C:	1.03
Viscosity:	350 mm ² /s
Freezing/Melting Point:	Not determined.
Boiling Point:	> 100 °C
Vapor Pressure @ 25°C:	Not determined.
Vapor Density:	Not determined.
Solubility in Water:	Not determined.
pH:	Not determined.
Volatile Content:	Not determined.

DOW CORNING(R) 734 FLOWABLE SEALANT, CLEAR

Flash Point: 188.6 °F / 87 °C (Closed Cup)
Autoignition Temperature: Not determined.
Flammability Limits in Air: Not determined.

Note: The above information is not intended for use in preparing product specifications. Contact Dow Corning before writing specifications.

10. STABILITY AND REACTIVITY

Chemical Stability: Stable.

Hazardous Polymerization: Hazardous polymerization will not occur.

Conditions to Avoid: None.

Materials to Avoid: Oxidizing material can cause a reaction. Water, moisture, or humid air can cause hazardous vapors to form as described in Section 8.

Hazardous Decomposition Products

Thermal breakdown of this product during fire or very high heat conditions may evolve the following decomposition products: Carbon oxides and traces of incompletely burned carbon compounds. Silicon dioxide. Formaldehyde.

11. TOXICOLOGICAL INFORMATION

Special Hazard Information on Components

No known applicable information.

12. ECOLOGICAL INFORMATION

Environmental Fate and Distribution

Complete information is not yet available.

Environmental Effects

Complete information is not yet available.

Fate and Effects in Waste Water Treatment Plants

Complete information is not yet available.

Ecotoxicity Classification Criteria

Hazard Parameters (LC50 or EC50)
Acute Aquatic Toxicity (mg/L)

High
<=1

Medium
>1 and <=100

Low
>100

DOW CORNING CORPORATION
Material Safety Data Sheet

Page: 6 of 8

Version: 1.8

Revision Date: 2011/11/15

DOW CORNING(R) 734 FLOWABLE SEALANT, CLEAR

Acute Terrestrial Toxicity	<=100	>100 and <= 2000	>2000
----------------------------	-------	------------------	-------

This table is adapted from "Environmental Toxicology and Risk Assessment", ASTM STP 1179, p.34, 1993.

This table can be used to classify the ecotoxicity of this product when ecotoxicity data is listed above. Please read the other information presented in the section concerning the overall ecological safety of this material.

13. DISPOSAL CONSIDERATIONS**RCRA Hazard Class (40 CFR 261)**

When a decision is made to discard this material, as received, is it classified as a hazardous waste? No

State or local laws may impose additional regulatory requirements regarding disposal. Call (989) 496-6315, if additional information is required.

14. TRANSPORT INFORMATION**DOT Road Shipment Information (49 CFR 172.101)**

Proper Shipping Name: Combustible liquid, n.o.s.

Hazard Technical Name: Methyltriacetoxysilane / Ethyltriacetoxysilane

Hazard Class: C

UN/NA Number: NA 1993

Packing Group: III

Hazard Label(s): None

Remarks: Above applies only to containers over 119 gallons or 450 liters.

Ocean Shipment (IMDG)

Not subject to IMDG code.

Air Shipment (IATA)

Not subject to IATA regulations.

Call Dow Corning Transportation, (989) 496-8577, if additional information is required.

15. REGULATORY INFORMATION

Contents of this MSDS comply with the OSHA Hazard Communication Standard 29 CFR 1910.1200.

DOW CORNING(R) 734 FLOWABLE SEALANT, CLEAR

TSCA Status: All chemical substances in this material are included on or exempted from listing on the TSCA Inventory of Chemical Substances.

EPA SARA Title III Chemical Listings**Section 302 Extremely Hazardous Substances (40 CFR 355):**

None.

Section 304 CERCLA Hazardous Substances (40 CFR 302):

None.

Section 311/312 Hazard Class (40 CFR 370):

Acute: No
Chronic: No
Fire: Yes
Pressure: No
Reactive: No

Section 313 Toxic Chemicals (40 CFR 372):

None present or none present in regulated quantities.

Note: Chemicals are listed under the 313 Toxic Chemicals section only if they meet or exceed a reporting threshold.

Supplemental State Compliance Information**California**

Warning: This product contains the following chemical(s) listed by the State of California under the Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65) as being known to cause cancer, birth defects or other reproductive harm.

None known.

Massachusetts

No ingredient regulated by MA Right-to-Know Law present.

New Jersey

<u>CAS Number</u>	<u>Wt %</u>	<u>Component Name</u>
70131-67-8	85.0 - 100.0	Dimethyl siloxane, hydroxy-terminated
112945-52-5	7.0 - 13.0	Amorphous fumed silica
4253-34-3	1.0 - 5.0	Methyltriacetoxysilane

DOW CORNING CORPORATION
Material Safety Data Sheet

Page: 8 of 8

Version: 1.8

Revision Date: 2011/11/15

DOW CORNING(R) 734 FLOWABLE SEALANT, CLEAR**Pennsylvania**

<u>CAS Number</u>	<u>Wt %</u>	<u>Component Name</u>
70131-67-8	85.0 - 100.0	Dimethyl siloxane, hydroxy-terminated
112945-52-5	7.0 - 13.0	Amorphous fumed silica

16. OTHER INFORMATION

Prepared by: Dow Corning Corporation

These data are offered in good faith as typical values and not as product specifications. No warranty, either expressed or implied, is hereby made. The recommended industrial hygiene and safe handling procedures are believed to be generally applicable. However, each user should review these recommendations in the specific context of the intended use and determine whether they are appropriate.

(R) indicates Registered Trademark