



Revision Number: 002.1

Issue date: 05/06/2010

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: 3942 Light Cure Medical Device
Adhesive Visible/UV Cure Fluorescent
IDH number: 434089
Product type: Adhesive
Item number: 36481
Region: United States
Company address:
 Henkel Corporation
 One Henkel Way
 Rocky Hill, Connecticut 06067
Contact information:
 Telephone: 860.571.5100
 Emergency telephone: 860.571.5100
 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

HMIS:

Physical state:	Liquid	HEALTH:	*2
Color:	Transparent, Hazy	FLAMMABILITY:	2
Odor:	Sharp	PHYSICAL HAZARD:	1
		Personal Protection:	See MSDS Section 8
WARNING:	COMBUSTIBLE LIQUID AND VAPOR. CAUSES EYE AND SKIN IRRITATION. MAY CAUSE ALLERGIC SKIN REACTION. MAY CAUSE RESPIRATORY TRACT IRRITATION. MAY BE HARMFUL IF SWALLOWED.		

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation:	May cause respiratory tract irritation.
Skin contact:	Causes skin irritation. May cause allergic skin reaction.
Eye contact:	Vapors may irritate eyes. Contact with eyes will cause irritation.
Ingestion:	May cause gastrointestinal tract irritation if swallowed.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders. Acrylic acid: Respiratory disorders. Lung disease.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Isobornyl acrylate	5888-33-5	30 - 60
Polyurethane Methacrylate Resin	Proprietary	10 - 30
2-Hydroxyethyl methacrylate	868-77-9	10 - 30
High boiling methacrylate	7534-94-3	5 - 10
Acrylic acid	79-10-7	5 - 10
Hydroxyalkyl methacrylate	27813-02-1	1 - 5
Photoinitiator	947-19-3	1 - 5
Gamma-glycidoxypropyl trimethoxysilane	2530-83-8	1 - 5
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	75980-60-8	1 - 5
Ethylene glycol	107-21-1	0.1 - 1

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. If symptoms develop and persist, get medical attention. Wash clothing before reuse.
Eye contact:	Flush with copious amounts of water, preferably, lukewarm water for at least 15 minutes, holding eyelids open all the time. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Keep individual calm. Never give anything by mouth to an unconscious person. Get medical attention.

5. FIRE FIGHTING MEASURES

Flash point:	70 °C (158°F) Pensky Martens closed cup
Autoignition temperature:	Not available
Flammable/Explosive limits - lower:	Not available
Flammable/Explosive limits - upper:	Not available
Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. Water may be unsuitable as an extinguishing media, but may be helpful in keeping adjacent containers cool.
Unusual fire or explosion hazards:	Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers.
Hazardous combustion products:	Oxides of carbon. Oxides of nitrogen. Oxides of silicon. Isocyanates. Hydrogen cyanide. Amines. Formaldehyde. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Ensure adequate ventilation. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

Handling:	Use only with adequate ventilation. Keep away from heat, spark and flame. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not taste or swallow. Refer to Section 8.
Storage:	For safe storage, store at or below 38 °C (100.4 °F) Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Isobornyl acrylate	None	None	None	None
Polyurethane Methacrylate Resin	None	None	None	None
2-Hydroxyethyl methacrylate	None	None	None	3 ppm Ceiling1
High boiling methacrylate	None	None	None	None
Acrylic acid	2 ppm TWA (SKIN)	None	None	1 ppm TWA 3 ppm STEL (SKIN)
Hydroxyalkyl methacrylate	None	None	None	1 ppm TWA 3 ppm STEL
Photoinitiator	None	None	None	None
Gamma-glycidoxypropyl trimethoxysilane	None	None	None	None
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	None	None	None	None
Ethylene glycol	100 mg/m ³ Ceiling1 Aerosol.	None	None	None

Engineering controls:

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection:

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection:

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection:

Use impermeable gloves and protective clothing as necessary to prevent skin contact. Neoprene, Butyl-rubber, or nitrile-rubber gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Transparent, Hazy
Odor:	Sharp
Odor threshold:	Not available
pH:	Not applicable
Vapor pressure:	< 10 mm hg (24 °C (75.2 °F))
Boiling point/range:	> 149 °C (> 300.2 °F)
Melting point/ range:	Not available
Specific gravity:	1.1284
Vapor density:	Not available
Flash point:	70 °C (158°F) Pensky Martens closed cup
Flammable/Explosive limits - lower:	Not available
Flammable/Explosive limits - upper:	Not available
Autoignition temperature:	Not available
Evaporation rate:	Not available
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available
VOC content:	0.79 %; 8.91 g/l ASTM D5403 Process volatiles 0.32 %; 3.61 g/l (potential) 1.10 %; 12.41 g/l (total) (ASTM D5403)

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	May occur.
Hazardous decomposition products:	Oxides of carbon. Oxides of nitrogen. Oxides of silicon. Isocyanates. Hydrogen cyanide. Amines. Formaldehyde. Irritating organic vapours.
Incompatible materials:	Strong oxidizing agents. Strong reducing agents. Peroxides. Heavy metals. Water. Humid air.
Conditions to avoid:	Heat, flames, sparks and other sources of ignition. Ultraviolet radiation. Direct sunlight. Freezing conditions. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Acute oral product toxicity:	LD50 (rat) > 5,000 mg/kg (Estimated)
Acute dermal product toxicity:	LD50 (rabbit) > 2,000 mg/kg (Estimated)

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Isobornyl acrylate	No	No	No
Polyurethane Methacrylate Resin	No	No	No
2-Hydroxyethyl methacrylate	No	No	No
High boiling methacrylate	No	No	No
Acrylic acid	No	No	No
Hydroxyalkyl methacrylate	No	No	No
Photoinitiator	No	No	No
Gamma-glycidoxypropyl trimethoxysilane	No	No	No
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	No	No	No
Ethylene glycol	No	No	No

Hazardous components	Health Effects/Target Organs
Isobornyl acrylate	Irritant, Allergen
Polyurethane Methacrylate Resin	Irritant, Allergen
2-Hydroxyethyl methacrylate	Irritant, Allergen
High boiling methacrylate	Irritant, Allergen
Acrylic acid	Allergen, Corrosive, Irritant, Kidney, Liver
Hydroxyalkyl methacrylate	Irritant, Allergen
Photoinitiator	No Records
Gamma-glycidoxypropyl trimethoxysilane	Irritant, Allergen
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	No Records
Ethylene glycol	Blood, Bone Marrow, Central nervous system, Developmental, Eyes, Irritant, Kidney, Liver, Metabolic

12. ECOLOGICAL INFORMATION

Ecological information:	Not available
--------------------------------	---------------

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of according to Federal, State and local governmental regulations.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Combustible liquid, n.o.s. (Acrylic acid)
Hazard class or division: Combustible Liquid
Identification number: NA 1993
Packing group: III

International Air Transportation (ICAO/IATA)

Proper shipping name: Environmentally hazardous substance, liquid, n.o.s. (Isobornyl acrylate)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III

Water Transportation (IMO/IMDG)

Proper shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Isobornyl acrylate)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III
Marine pollutant: Isobornyl acrylate

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

TSCA 12(b) Export Notification: None above reporting de minimus

CERCLA/SARA Section 302 EHS: None above reporting de minimus

CERCLA/SARA Section 311/312: Fire, Immediate Health, Delayed Health

CERCLA/SARA 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Acrylic acid (CAS# 79-10-7).

California Proposition 65: This product contains a chemical known in the State of California to cause cancer.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

WHMIS hazard class: B.3, D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: New Material Safety Data Sheet format.

Prepared by: Tricia Voghell, Regulatory Affairs Specialist

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.