




MODEL 50-23

CHIP-LOK™
COB ARRAY HOLDER

FEATURES/BENEFITS:



- METAL HOLDER BASE IS RESISTANT TO CREEP TO PREVENT THERMAL AND ELECTRICAL ISSUES TYPICAL AT ELEVATED OPERATING TEMPERATURES OVER TIME
- COB HOLDING ARM SECURES ARRAY TO HOLDER FOR EASE OF INSTALLATION
- KEYWAYS ALLOW FOR PRE-INSTALLATION OF SCREWS TO EASE ASSEMBLY AND MINIMIZE DAMAGE TO PHOSPHOR
- TOUCH-SAFE DESIGN IS UL RECOGNIZED FOR 250V TO ALLOW USE IN DAISY CHAINED APPLICATIONS
- STAINLESS STEEL BODY PROVIDES ADDITIONAL HEAT SINKING PATHS TO ALLOW ARRAY TO RUN COOLER COMPARED WITH SCREWS AND PLASTIC HOLDERS.

ELECTRICAL:

VOLTAGE: 250 V MAX
CURRENT: 4 A MAX

MECHANICAL:

DIAMETER: 2.56 in (65.0 mm)
HEIGHT: 0.27 in (6.98 mm) MAX
WEIGHT: 0.39 oz (10.3 grams)
SCREW SIZE: #5-40 (M3)
SCREW TORQUE: 5 in-lb(0.5 Nm) MAX
SCREW CIRCLE DIA: 1.97 in (50.0 mm)
WIRE STRIP LENGTH: 1/4"-5/16" (7 mm)

PHYSICAL:

BASE PLATE: 301 SS
CONTACT HOUSING: THERMOPLASTIC
ELECTRICAL CONTACTS: COPPER ALLOY
PLATING: SILVER OVER NICKEL
TEMPERATURE: 110°C

RoHS AND REACH COMPLIANT
HALOGEN FREE, NON-CHLORINATED & NON-BROMINATED FLAME RETARDANT

STANDARDS & SPECIFICATIONS:



RECOGNIZED COMPONENT UL 496 (US/CANADA)
EIA -364-1000 (THERMAL CYCLING)
EIA-364-31 (THERMAL SHOCK & HUMIDITY)
EIA-364-17 (ELEVATED TEMPERATURE - LIFE)
UL 2459 (CURRENT CYCLING - TEMP RISE)
IEC 60068-2-7 (VIBRATION)

US & FOREIGN PATENTS PENDING

WIRE RANGE:

	AWG (UL 496)	METRIC
SOLID	18-24 AWG	0,75 - 0,25 mm2
STRANDED	18-22 AWG	0,75 - 0,25 mm2
TIN BONDED	18-24 AWG	0,75 - 0,25 mm2

DIMENSIONS:



ORDERING INFO:

CATALOG #	MANUFACTURER	COB ARRAY		CARTON QTY:	WEIGHT LBS (KG):
50-2303CR	CREE	CXA35		320	8.0 (3,6)

FACTORY CONTACT:

ENGINEERED SOLUTIONS
IDEAL INDUSTRIES, INC.
1375 PARK AVENUE SYCAMORE IL USA 60178
P: 1-800-324-9571
F: 1-888-222-6140
E: oem@idealindustries.com

SALES CONTACT: