




Insulated Gate Bipolar Transistor (Trench IGBT), 100 A



SOT-227

FEATURES

- Trench IGBT technology with positive temperature coefficient
- Speed 4 kHz to 30 kHz
- Square RBSOA
- 3 μ s short circuit capability
- FRED Pt[®] antiparallel diodes with ultrasoft reverse recovery
- T_J maximum = 175 °C
- Fully isolated package
- Very low internal inductance (\leq 5 nH typical)
- Industry standard outline
- UL approved file E78996 
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

PRODUCT SUMMARY	
V_{CES}	600 V
I_C DC	100 A at 117 °C
$V_{CE(on)}$ typical at 100 A, 25 °C	1.72 V
I_F DC	100 A at 25 °C
Package	SOT-227
Circuit	Single Switch Diode

BENEFITS

- Designed for increased operating efficiency in power conversion: UPS, SMPS, welding, induction heating
- Easy to assemble and parallel
- Direct mounting to heatsink
- Plug-in compatible with other SOT-227 packages
- Lower conduction losses and switching losses
- Low EMI, requires less snubbing

ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Collector to emitter voltage	V_{CES}		600	V
Continuous collector current	I_C ⁽¹⁾	$T_C = 25\text{ °C}$	184	A
		$T_C = 80\text{ °C}$	137	
Pulsed collector current	I_{CM}		350	
Clamped inductive load current	I_{LM}		350	
Diode continuous forward current	I_F	$T_C = 25\text{ °C}$	100	
		$T_C = 80\text{ °C}$	71	
Peak diode forward current	I_{FSM}		200	
Gate to emitter voltage	V_{GE}		± 20	V
Power dissipation, IGBT	P_D	$T_C = 25\text{ °C}$	577	W
		$T_C = 117\text{ °C}$	223	
Power dissipation, diode	P_D	$T_C = 25\text{ °C}$	205	
		$T_C = 117\text{ °C}$	79	
Isolation voltage	V_{ISOL}	Any terminal to case, t = 1 min	2500	V

Note

⁽¹⁾ Maximum continuous collector current must be limited to 100 A to do not exceed the maximum temperature of terminals




ELECTRICAL SPECIFICATIONS (T _J = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Collector to emitter breakdown voltage	V _{BR(CES)}	V _{GE} = 0 V, I _C = 250 μA	600	-	-	V
Collector to emitter voltage	V _{CE(on)}	V _{GE} = 15 V, I _C = 100 A	-	1.72	2.0	
		V _{GE} = 15 V, I _C = 100 A, T _J = 125 °C	-	2.0	2.2	
Gate threshold voltage	V _{GE(th)}	V _{CE} = V _{GE} , I _C = 250 μA	3.5	4.6	6.5	
Temperature coefficient of threshold voltage	ΔV _{GE(th)} /ΔT _J	V _{CE} = V _{GE} , I _C = 1 mA (25 °C to 125 °C)	-	-16.8	-	mV/°C
Collector to emitter leakage current	I _{CES}	V _{GE} = 0 V, V _{CE} = 600 V	-	0.6	100	μA
		V _{GE} = 0 V, V _{CE} = 600 V, T _J = 125 °C	-	0.15	3	mA
Forward voltage drop	V _{FM}	I _F = 40 A, V _{GE} = 0 V	-	1.78	2.21	V
		I _F = 40 A, V _{GE} = 0 V, T _J = 125 °C	-	1.39	1.74	
Gate to emitter leakage current	I _{GES}	V _{GE} = ± 20 V	-	-	± 200	nA


SWITCHING CHARACTERISTICS (T _J = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Turn-on switching loss	E _{on}	I _C = 100 A, V _{CC} = 360 V, V _{GE} = 15 V, R _g = 5 Ω, L = 500 μH, T _J = 25 °C	-	0.35	-	mJ
Turn-off switching loss	E _{off}		-	2.08	-	
Total switching loss	E _{tot}		-	2.43	-	
Turn-on switching loss	E _{on}	I _C = 100 A, V _{CC} = 360 V, V _{GE} = 15 V, R _g = 5 Ω, L = 500 μH, T _J = 125 °C	-	0.41	-	ns
Turn-off switching loss	E _{off}		-	2.83	-	
Total switching loss	E _{tot}		-	3.24	-	
Turn-on delay time	t _{d(on)}		-	162	-	
Rise time	t _r		-	55	-	
Turn-off delay time	t _{d(off)}		-	150	-	
Fall time	t _f	-	129	-		
Reverse bias safe operating area	RBSOA	T _J = 175 °C, I _C = 350 A, R _g = 22 Ω, V _{GE} = 15 V to 0 V, V _{CC} = 400 V, V _P = 600 V, L = 500 μH	Fullsquare			
Diode reverse recovery time	t _{rr}	I _F = 50 A, dI _F /dt = 200 A/μs, V _R = 200 V	-	61	85	ns
Diode peak reverse current	I _{rr}		-	4	7	A
Diode recovery charge	Q _{rr}		-	120	297	nC
Diode reverse recovery time	t _{rr}	I _F = 50 A, dI _F /dt = 200 A/μs, V _R = 200 V, T _J = 125 °C	-	133	154	ns
Diode peak reverse current	I _{rr}		-	12	15	A
Diode recovery charge	Q _{rr}		-	750	1150	nC
Short circuit safe operating area	SCSOA	T _J = 175 °C, R _g = 22 Ω, V _{GE} = 15 V to 0 V, V _{CC} = 400 V, V _P = 600 V	3			μs




THERMAL AND MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL		MIN.	TYP.	MAX.	UNITS
Junction and storage temperature range	T_J, T_{Stg}		-40	-	175	°C
Junction to case	IGBT	R_{thJC}	-	-	0.26	°C/W
	Diode		-	-	0.73	
Case to heatsink	R_{thCS}	Flat, greased surface	-	0.05	-	
Weight			-	30	-	g
Mounting torque			-	-	1.3	Nm
Case style	SOT-227					




93185_01 **I_C - Continuous Collector Current (A)**
Fig. 1 - Maximum DC IGBT Collector Current vs. Case Temperature




93185_02 **V_{CE} (V)**
Fig. 3 - Typical IGBT Collector Current Characteristics
 $V_{GE} = 15\text{ V}$



93185_02 **V_{CE} (V)**
Fig. 2 - IGBT Reverse Bias SOA
 $T_J = 175\text{ °C}, V_{GE} = 15\text{ V}$




93185_04 **I_F - Continuous Forward Current (A)**
Fig. 4 - Maximum DC Forward Current vs. Case Temperature




93185_05

Fig. 5 - Typical Diode Forward Characteristics




93185_08

Fig. 8 - Typical IGBT Collector to Emitter Voltage vs. Junction Temperature, $V_{GE} = 15\text{ V}$




93185_06

Fig. 6 - Typical IGBT Zero Gate Voltage Collector Current




93185_09

Fig. 9 - Typical IGBT Energy Loss vs. I_C
 $T_J = 125\text{ °C}$, $L = 500\text{ }\mu\text{H}$, $V_{CC} = 360\text{ V}$,
 $R_g = 5\text{ }\Omega$, $V_{GE} = 15\text{ V}$




93185_07

Fig. 7 - Typical IGBT Threshold Voltage




93185_10

Fig. 10 - Typical IGBT Switching Time vs. I_C
 $T_J = 125\text{ °C}$, $L = 500\text{ }\mu\text{H}$, $V_{CC} = 360\text{ V}$,
 $R_g = 5\text{ }\Omega$, $V_{GE} = 15\text{ V}$




93185_11

Fig. 11 - Typical IGBT Energy Loss vs. R_g
 $T_J = 125\text{ }^\circ\text{C}$, $I_C = 100\text{ A}$, $L = 500\text{ }\mu\text{H}$,
 $V_{CC} = 360\text{ V}$, $V_{GE} = 15\text{ V}$




93185_13

Fig. 13 - Typical t_{rr} Diode vs. dl_F/dt
 $V_{rr} = 200\text{ V}$, $I_F = 50\text{ A}$




93185_12

Fig. 12 - Typical IGBT Switching Time vs. R_g
 $T_J = 125\text{ }^\circ\text{C}$, $L = 500\text{ }\mu\text{H}$, $V_{CC} = 360\text{ V}$,
 $I_C = 100\text{ A}$, $V_{GE} = 15\text{ V}$




93185_14

Fig. 14 - Typical I_{rr} Diode vs. dl_F/dt
 $V_{rr} = 200\text{ V}$, $I_F = 50\text{ A}$




93185_15

Fig. 15 - Typical Q_{rr} Diode vs. dl_F/dt
 $V_{rr} = 200\text{ V}$, $I_F = 50\text{ A}$




93185_16

Fig. 16 - Maximum Thermal Impedance Z_{thJC} Characteristics (IGBT)



93185_17

Fig. 17 - Maximum Thermal Impedance Z_{thJC} Characteristics (Diode)



* Driver same type as D.U.T.; $V_C = 80\% \text{ of } V_{ce(max)}$
 * Note: Due to the 50 V power supply, pulse width and inductor will increase to obtain I_d

Fig. 18a - Clamped Inductive Load Test Circuit




Fig. 18b - Pulsed Collector Current Test Circuit




Fig. 19a - Switching Loss Test Circuit





Fig. 19b - Switching Loss Waveforms Test Circuit




ORDERING INFORMATION TABLE



- 1** - Vishay Semiconductors product
- 2** - Insulated Gate Bipolar Transistor (IGBT)
- 3** - T = Trench IGBT technology
- 4** - Current rating (100 = 100 A)
- 5** - Circuit configuration (D = Single switch with antiparallel diode)
- 6** - Package indicator (A = SOT-227)
- 7** - Voltage rating (60 = 600 V)
- 8** - Speed/type (U = Ultrafast)


CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95036
Packaging information	www.vishay.com/doc?95037

SOT-227

DIMENSIONS in millimeters (inches)



Notes

- Dimensioning and tolerancing per ANSI Y14.5M-1982
- Controlling dimension: millimeter



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.