

**Features:**

- Low Profile Design
- Dual Latching Co-Extruded Hinge
- Non-Metallic Construction
- Easy to Cut and Handle
- Available with Adhesive Back
- “Office White” Color
- Full Line
- UL Listed and CSA Certified



**Benefits:**

- Neat Appearance, Low Protrusion or Obtrusive
- Conveniently Holds Wires in Place Without Clips
- Resists Scratching and Denting
- Saves Labor Costs
- Speeds Installation
- Blends Aesthetically with Decor
- Supports Complete Installations
- Applicable for Power and Low Voltage

# PW1 WallTrak® Low Profile Non-Metallic Raceway



Raceway		Catalog Number	Length	Color	
<b>Base and Cover</b> Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.			<b>PW1BC5</b>	5 ft.	Office
			<b>PW1BC7</b>	7 ft.	White
		A: .50" (12.70) B: 1.19" (30.30)			
<b>Base and Cover (with adhesive)</b> Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.			<b>PW1ABC5</b>	5 ft.	Office
			<b>PW1ABC7</b>	7 ft.	White
		A: .50" (12.70) B: 1.19" (30.30)			
Boxes		Catalog Number	Color		
<b>One-Gang Low Profile Box</b> For shallow switches and receptacles.			<b>PW1LPB</b>	Office White	
			A: 3.25" (82.55) B: 4.90" (124.46) C: 1.13" (28.70)		
<b>One-Gang Standard Box</b> For standard switches and receptacles.			<b>PW1SBA</b>	Office White	
			A: 3.25" (82.55) B: 4.90" (124.46) C: 1.63" (41.40)		
<b>One-Gang Deep Box</b> For deep devices or applications where additional room is beneficial.			<b>PW1DBA</b>	Office White	
			A: 3.25" (82.55) B: 4.90" (124.46) C: 1.91" (48.51)		
<b>Two-Gang Deep Box</b> For deep switches, receptacles and communication devices. (Use only two-gang KP or IFP plates).			<b>PW1TGB</b>	Office White	
			A: 5.06" (128.52) B: 4.90" (124.46) C: 1.91" (48.51)		
<b>Round Lighting Fixture Box</b> To hang fixtures.			<b>PW1LFB</b>	Office White	
			A: 5.31" (134.87) B: 1.04" (26.41)		
Fittings		Catalog Number	Color		
<b>Internal Elbow</b>			<b>PW1IE</b>	Office White	
			A: 1.75" (44.45) B: 1.43" (36.32) C: 1.75" (44.45)		
<b>External Elbow</b>			<b>PW1EE</b>	Office White	
			A: 1.50" (38.10) B: 1.43" (36.32) C: 1.50" (38.10)		
<b>Flat Elbow</b>			<b>PW1FE</b>	Office White	
			A: 2.18" (55.37) B: 2.18" (55.37) C: .60" (15.24)		
<b>Tee</b>			<b>PW1TC</b>	Office White	
			A: 2.93" (74.42) B: 2.18" (55.37) C: .60" (15.24)		
<b>Splice Cover</b>			<b>PW1SC</b>	Office White	
			A: 1.00" (25.40) B: 1.43" (36.32) C: .60" (15.24)		






### Fittings

#### End Cap

For closing end of raceway.



### Catalog Number

#### PW1EC


A: 1.00" (25.40)  
B: 1.24" (31.50)  
C: .50" (12.70)

### Color

Office White

#### Conduit Adapter/Ceiling Fitting

For connection conduit to raceway or ceiling feeds. Has 1/2 in. trade size KO and combination 1/2 in. and 3/4 in. trade size KOs.



#### PW1CA

A: 2.34" (59.44)  
B: 1.40" (35.56)  
C: 3.22" (81.79)

Office White

## Office White Plates and Outlets for Non-Metallic Raceway

### "KP" Plates

Duplex  
KP8



Style Line®  
KP26



Single Rec.  
(1.41" ID)  
KP7



Single Rec.  
(1.60" ID)  
KP720



Toggle  
KP1



Blank  
KP14



Coax (2)  
KP212



Coax/  
Jack  
KP2140



(2) Jacks  
KP2162



(3) Jacks  
KP2163



KP  
Module  
Bezel  
KPIMBZOW



### Two-gang Plates (Two-gang KP plates for use with PW12TGB only)

Two-  
Gang  
Duplex  
KP82



Two-  
Gang  
Style Line®  
KP262



Two-  
Gang  
Toggle  
KP2



Two-  
Gang  
Blank  
KP24



### Keystone IFP Plates

#### One-Gang Plates

2-Port  
IFP120W



3-Port  
IFP130W



4-Port  
IFP140W



6-Port  
IFP160W



#### Two-Gang Plates

Two-Gang  
6-Port  
IFP260W



Two-Gang  
9-Port  
IFP290W



Two-Gang  
12-Port  
IFP2120W



### Communication Plates and Frames

Style Line®  
IFP1260W



Duplex  
IFP180W



Style Line®  
Keystone  
2-Port  
ISF20W



Style Line®  
Keystone  
3-Port  
ISF30W



Style Line®  
Keystone  
4-Port  
ISF40W



Style Line®  
Keystone  
6-Port  
ISF60W



Duplex  
Keystone  
2-Port  
BR106C



Duplex  
Keystone  
4-Port  
Q106O



### liSTATION™ Frames and Modules

Front loading plate will accept any modules in three unit combinations. Angled fixtures to be used in bottom opening only.

1-Gang Plate Frame  
IMF10W



2-Gang Plate Frame  
IMF20W



### Snap Fit Connector Fittings

Snap Fit connectors to be used with any plate with a standard keystone opening. Not recommended for use with KP plates. For KP applications use KPIMBZOW bezel and appropriate iSTATION™ modules. Use appropriate iSTATION™ module for SC fiber adapters.

Blank (10 Pack)

SFB10



F Connector

SFFX



ST Fiber Connector

SFST



BNC

SFBOW



RCA

SFRC110R



Super S-Video

SFSV110BK



SC Duplex  
Adapter

FASCMPB6



SC to ST Duplex  
Adapter

FASTSCMPB6



### Xcelerator® Keystone Jacks

Cat. 5e, Office White  
T568A, T568B, RJ45  
HXJ5EOW



Cat. 6, Office White  
T568A, T568B, RJ45  
HXJ6OW



6 Position USOC,  
Office White, RJ25  
HXJUOW



Jack Color Options (Replaces OW Suffix)

AL=Almond

GY=Gray

BK=Black

W=White

OR=Orange

R=Red

Y=Yellow

B=Blue

GN=Green

EI=Elec Ivory



PW1 Series Non-Metallic Raceway Wire Fill Capacities														
	Power (THHN/T90 Nylon)			Voice		Data(Cooper Cables)					Data (Multimode Fiber optic cables)			
	14 AWG	12 AWG	10 AWG	4-Pair	25-Pair	Type RG59U	Cat. 5e	Cat. 6	Cat. 6A	Cat. 6A	(2) or (4) Fiber Round Cable	Fiber Optic Jumpers	Fiber Optic Zip Cord	
Wire O.D. (in.):				0.19	0.41	0.242	0.21	0.25	0.35	0.29	0.19	0.118	.12 X .24	
Wire Area (sq. in.):				0.0283	0.132	0.046	0.0346	0.0491	0.0962	0.0660	0.0283	0.0109	0.0288	
Series	Channel	Wire Fill Capacity												
	Area (sq. in.)				40%	40%	40%	40%	40%	40%	40%	40%	40%	
PW1	.30	6	10	4	4	0	2	3	2	1	2	4	11	4

Technical Data

















Physical Properties

(When tested in accordance with UL 5A)  
 Impact Resistance . . . . .5 ft. lbs.  
 Crush Resistance . . . . .300 lbs.  
 Temperature Range . . . . .-25.6° to 158° F  
 Flame Rating . . . . .UL94V-0  
 Material . . . . .UV Stabilized PVC

Codes/Standards

NEC Article . . . . .388  
 EIA/TIA . . . . .569A  
 UL Standard . . . . .UL 5A  
 Listings . . . . .E118895 / E119190  
 CSA Standard . . . . .C22.2 no. 62  
 Certified . . . . .LR87514

Other Non-Metallic Raceway Available from Hubbell

Trak		5' Base & Cover	5' Base & Cover w/adhesive	7' Base & Cover	7' Base & Cover w/adhesive	10' Base & Cover
 Super BaseTrak®		<b>PS3BC5</b>	—	—	—	<b>PS3BC10</b>
 BaseTrak® 2 Channel		<b>PB2B5</b> <b>PB2C5</b> <b>PB2SPL5</b>	—	—	—	<b>PB2B10</b> <b>PB2C10</b> <b>PB2SPL10</b>
 BaseTrak® 3 Channel		<b>PB3BC5</b>	—	—	—	<b>PB3BC10</b>
 WallTrak®		<b>PW2BC5</b>	<b>PW2ABC5</b>	<b>PW2BC7</b>	<b>PW2ABC7</b>	—
 LANTrak®		<b>PL1BC5</b>	<b>PL1ABC5</b>	<b>PL1BC7</b>	<b>PL1ABC7</b>	—
 Premise Trak® (Latching)		<b>PP1BC5</b>	<b>PP1ABC5</b>	<b>PP1BC7</b>	<b>PP1ABC7</b>	—
 Premise Trak 1® (Non-Latching)		<b>PT1BC5</b>	<b>PT1ABC5</b>	<b>PT1BC7</b>	<b>PT1ABC7</b>	—
 PlugTrak®		<b>PT155112*</b>	5', 5 Duplex Receptacles			
		<b>PT156112*</b>	6', 6 Duplex Receptacles			

\*Other Configurations Available. Consult Factory.

