



COMPANY

PRODUCTS

DISTRIBUTORS


CONTACT

RESOURCES



▶ Products ▶ **Heat Guns** ▶ Glue Guns ▶ Gas Torches ▶ Sensors

INDUSTRIAL HEAT GUNS



STEINEL'S heaviest duty heat guns were designed for toughest jobs.

STEINEL offers long life and durability in packaging, roofing and other industrial applications where these features are key.

These heat guns incorporate on-board microprocessors to automatically calibrate and regulate their heating elements. The heating elements themselves are fully encapsulated in ceramic and are **unsurpassed** in terms of even heating, durability and longevity.

Highly efficient DC brushless motors, guaranteed for life, add to the tool's high level of performance and reliability.

You can count on STEINEL to get the toughest jobs done.

HG 5000 E

Heavy Duty Heat Gun with microprocessor control and high performance air output (230V).

STEINEL HG 5000 E provides the ultimate in precision technology. Exclusive IntelliTemp™ control enables the user to select a target temperature to within +/- 5°F and to view actual output on the LED display. Heating elements for the HG 5000 E are easily changeable in the field and integrate SmartChip™ technology allowing the heat gun to automatically recalibrate to the new element.

DC Brushless Motor:	Guaranteed for the life of the tool.
Heating Element:	Built-in SmartChip holds specific data. 500 - 800 hours expected element life span. Conveniently field changeable.
Onboard Microprocessor:	Receives and interprets data from the SmartChip to automatically calibrate and regulate the heating element.
Variable Airflow:	Up to 28 cfm (800 liters), 3000 Pa Air Pressure
Variable Temperature:	Selectable from 80°F - 1100°F
LED Temperature Display:	Indicates actual and target temperatures in 10F increments.
Double Insulated Power Cord:	Rubber construction for increased safety. Field changeable without opening housing.
Outlet Tube:	50mm (approximately 2 inches)
Output:	3,400 watts
Voltage:	230 VAC / 50 Hz



Available with or without heavy duty metal carrying case.

Certifications:	CE listed
Full One Year Warranty:	Full One Year Warranty, Lifetime Motor Warranty
↳ Accessories	Accepts a specially designed range of nozzles and accessories.

HG 4000 E

Heavy Duty Heat Gun with microprocessor control (120V).

STEINEL HG 4000 E provides the ultimate in precision technology. Exclusive IntelliTemp™ control enables the user to select a target temperature to within +/- 5°F and to view actual output on the LED display. Heating elements for HG 4000 E are easily changeable the field and integrate SmartChip™ technology allowing the heat gun to automatically recalibrate to the new element.

DC Brushless Motor:	Guaranteed for the life of the tool.
Heating Element:	Built-in SmartChip holds specific data. 500 - 800 hours expected element life span. Conveniently field changeable.
Onboard Microprocessor:	Receives and interprets data from the SmartChip to automatically calibrate and regulate the heating element.
Variable Airflow:	Up to 21 cfm, 3000 Pa Air Pressure.
Variable Temperature:	Selectable from 80°F to 1100°F.
LED Temperature Display:	Indicates actual and target temperatures in 10F increments.
Double Insulated Power Cord:	Rubber construction for increased safety. Field changeable without opening housing.
Outlet Tube:	40mm (approximately 1 1/2 inches)
Output:	1,750 watts.
Voltage:	120 VAC / 60 Hz
Certifications:	UL / C-UL listed
Full One Year Warranty:	Full One Year Warranty, Lifetime Motor Warranty
↳ Accessories	Accepts a specially designed range of nozzles and accessories.



Available with or without heavy duty metal carrying case.

HG 2300 EM

Ergonomic Heat Gun with Electronic Thermocouple Control.

STEINEL's HG 2300 EM combines powerful output with an ergonomic, easy to use design. Variable temperature and airflow control ensure the perfect job every time. The HG 2300 EM features ultra quiet operation, fast heat-up, and requires no cool-down. Its modular construction is easy to repair, with heating element and power cord both conveniently field-changeable.

Temperature:	80°F – 1300°F
Variable Airflow:	Up to 15.4 cfm
Air pressure:	2940 Pa
Power Cord:	Rubber construction for increased safety. Field changeable without opening housing.
Output:	1,750 watts
Voltage:	120 VAC / 60 Hz
Nozzle Diameter:	40mm (same as HG 4000 E)



Certifications:	UL / C-UL	Available with or without heavy duty carrying case.
Warranty	Full One Year, Lifetime Motor Warranty	
▸ Kits	Available in industry specific kit presentations.	
▸ Accessories	Accepts a specially designed range of nozzles and accessories.	

STEINEL

9051 LYNDALE AVENUE SOUTH, BLOOMINGTON, MN 55423
TOLL FREE: (800) 852-4343 E-MAIL: SALES@STEINEL.NET