


EC14



EC15

### Product Type:

Appliversal - Terminations

### Application:

These earth clamps are available in two types –  
 RED – (AEC14) for dry, non corrosive atmospheres  
 BLUE – (AEC15) for corrosive or humid conditions

### Standards / Conformances:

- BS951

### Design Features:

- To suit popular terminal size range
- Caters for popular pipe sizes
- Simple and quick to use
- Conform to BS951

### Technical Information:

Part No.	Colour Ref	Terminal Size	Pipe size	Pack Qty
EC14	Red	2.5 – 10mm <sup>2</sup>	Ø12 – 32mm	20
EC15	Blue	2.5 – 10mm <sup>2</sup>	Ø12 – 32mm	20

### Part Number Table

Description	Part Number
Earth Clamp, Terminal	EC14
	EC15

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.