



Wiha Quality for Over 75 Years

Factory Preset Torque Drivers



An economical solution for accurate dedicated Torque Control
Tools Meet: ASME B107.14m, EN ISO 6789, BS EN 26789
Torque Accuracy of +/- 6%
Tools Have Unique Serial Number and Calibration Certificates
Accuracy Guaranteed to 5000 cycles or 1 year.

- Replaceable Blades
- Controls Costs
- +/- 6% Accuracy
- Consistent Fastening
- Soft Ergo Grips

Item No.	Torque Pre Set	Torque Nm	Handle Length
28503	5 in-lbs	.56 Nm	4.4"
28505	7.5 in-lbs	.85 Nm	4.4"
28507	10 in-lbs	1.1 Nm	4.7"
28509	12.5 in-lbs	1.4 Nm	4.7"
28511	15 in-lbs	1.7 Nm	4.7"
28513	20 in-lbs	2.2 Nm	4.7"
28515	25 in-lbs	2.8 Nm	4.9"
28517	30 in-lbs	3.4 Nm	4.9"
28518	35 in-lbs	3.9 Nm	4.9"
28519	40 in-lbs	4.5 Nm	5.2"
28521	50 in-lbs	5.6 Nm	5.2"
28523	60 in-lbs	6.8 Nm	5.2"
28525	70 in-lbs	7.9 Nm	5.2"