


LQM21PN2R2NGC#

"#" indicates a package specification code.

Available **General** 125°C Multi-layer Bias Thickness 1.0mm max. Reflow OK Flow OK RoHS

< List of part numbers with package codes >
LQM21PN2R2NGCD , LQM21PN2R2NGCB

Shape



L size	2.0 ± 0.15mm
W size	1.25 ± 0.15mm
T size	0.9 ± 0.1mm
Size code in inch (mm)	0805 (2012)

Notes

In operating temperature exceeding +85 , derating of current is necessary for LQM21P_GC series. Please apply the derating curve shown in

References

Packaging code	Specifications	Minimum quantity
D	180mm Paper taping	4000
B	Packing in bulk	1000

Mass (Typ.)	
1 piece	0.012g


Specifications

Inductance	2.2μH ± 30%
Inductance test frequency	1MHz
Rated current (Itemp) (Based on Temperature rise)	0.8A(Ambient temperature 85) 0.6A(Ambient temperature 125)
Max. of DC resistance	0.288
Avg. of DC resistance	0.23 ± 25%
Self resonance frequency (min.)	40MHz
Operating temperature range	-55 ~ 125
Class of magnetic shield	Magnetic shield of ferrite


⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


▪ Inductance-Frequency characteristics (Typ.)



▪ Inductance-Current characteristics (Typ.)



▪ Temperature rise characteristics (Typ.)



▪ Notice (Rating)

