

LTP Series

Polyolefin Heat Shrink Tubing

pro-POWER

RoHS
Compliant



Description:

The LTP series is the most flexible of the heat-shrinkable, polyolefin tubings. The LTP series has been engineered to offer a low shrink temperature. This allows the tubing to shrink rapidly, thereby minimizing heat exposure and possible damage to sensitive substrate materials or components.

Specifications:

Shrink Ratio	: 2:1
Shrink Temperature	: 100°C (212°F)
Colour	: Black

Physical

Tensile Strength	: 2100 PSI
Ultimate Elongation	: 450%
Longitudinal Change	: ±5%
Secant Modulus (2%)	: 11,000 PSI
Heat Aging	: Elongation
(168 hrs @ 175°C)	200% (Min) 250%
Heat Shock (4 hrs @ 250°C)	: No dripping, cracking, passes mandrel wrap test
Low Temperature Flexibility (4 hrs @ -55°C)	: No Cracking
Flexibility*	: 2

Electrical

Dielectric Strength	: 800V/mil
Volume Resistivity	: 10 ¹⁴ Ω-cm

Chemical

Corrosive Effect	: Non-corrosive
Solvent Resistance	
Tensile Strength	: 750 PSI
Dielectric Strength	: 400V/mil
Water Absorption	: 0.2%
Fungus Resistance	: Non-nutrient
Applicable Specifications	: MIL-R-46846 Type V, AMS-3587

The technical information provided consists of typical product data and should not be used for specification purposes. Unless otherwise noted, all tests are performed at room temperature.

*Flexibility : The materials are rated on a scale of 1-10.

1=most flexible and 10=most rigid

LTP Series

Polyolefin Heat Shrink Tubing

pro-POWER

Dimensions				Standard Packages					
			Recovered	4 Foot Lengths(+1", -0")			6 Inch Lengths(± 0.125")		
Size	Expanded I.D. (Min)	Recovered I.D. (Max)	Nominal Wall Thickness	Part Number	Qty	Total Footage	Part Number	Qty	Total Footage
3/64"	0.046"	0.023"	0.016"	LTP-003-4025-BLK	25	100FT	NA	---	---
1/16"	0.063"	0.031"	0.017"	NA	---	---	LTP-004-6036-BLK	36	18FT
1/8"	0.125"	0.062"	0.020"	LTP-008-4025-BLK	25	100FT	LTP-008-6028-BLK	28	14FT
3/16"	0.187"	0.093"	0.020	LTP-012-4025-BLK	25	100FT	NA	---	---
1/4"	0.250"	0.125"	0.025	LTP-016 4025-BLK	25	100FT	NA	---	---
3/8"	0.375"	0.187"	0.025	LTP-024-4025-BLK	25	100FT	LTP-024-6016-BLK	16	8FT
1/2"	0.500"	0.250"	0.025	LTP-032-4005-BLK	5	20FT	NA	---	---
3/4"	0.750"	0.375"	0.030	LTP-048-4005-BLK	5	20FT	NA	---	---
1"	1.000"	0.500"	0.035"	LTP-064-4005-BLK	5	20FT	NA	---	---
1 1/2 "	1.500"	0.750"	0.040"	LTP-096-4005-BLK	5	20FT	NA	---	---

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
 www.farnell.com
 www.newark.com
 www.cpc.co.uk

pro-POWER