


HOSE & CABLE PROTECTION

Product	Page
AccessTrak®, TrukTrak® and TredTrak®	2-5
FloorTrak®	6
CableTrak® Modular Carrier Track	7-9




HOSE AND CABLE PROTECTION



Features and Benefits



The AccessTrak® ramping system is a modular cable protection product that enables users to be ADAAG (American Disabilities Act Accessibility Guidelines) compliant and limits the exposure of cables and hoses to people and light vehicles passing over those cables and hoses. AccessTrak is an expandable five channel system that will protect cable and hose diameters up to 1.31 inches (33.0mm). For applications requiring more than five channels, AccessTrak can be expanded by width. In addition, AccessTrak is expandable by length to protect cables and hoses of any length. The AccessTrak ramping system provides a safe, flexible means of protecting cables and hoses in areas requiring ADA compliance.



Hubbell TrukTrak® and TredTrak® non-metallic cable protectors are designed to safeguard electrical cables and cords from vehicle and pedestrian traffic. The TrukTrak system comes in two, three and five channel sizes and will protect cables up to 3.25 inches (82.6mm) in diameter. It is ideal for the industrial environment where it is necessary to support heavy trucks and fork lifts. The TredTrak system is a five channel modular cable protection system that will protect cable diameters up to 1.28 inches (32.5mm). It is designed to support pedestrian and light vehicle traffic in public, institutional and commercial applications. It can also be interconnected to protect cables and cords of any length. The Hubbell modular cable protection line also permits compliance with NEC® requirements (Article 525) for insulating electrical cables and cord at carnivals, amusement parks, convention centers and similar public areas.



FloorTrak® is a flexible, non-metallic cover for cables that run over the floor when portable cords and cables cannot be concealed or routed away from traffic patterns. FloorTrak protects, organizes and reduces trip hazards. Four different sizes mean it will handle cables of up to 1.25 inches (31.8mm) in diameter. FT2, FT3 and FT4 are available in five PVC colors to blend with the various decors. FT10 is available in black and yellow colors only. The F10 Heavy Duty FloorTrak is ideal for applications such as industrial work areas, food processing plants and abusive areas where cable management is necessary.

NEC® is a registered trademark of the The National Electrical Code.

Hose and Cable Protection Systems

AccessTrak® System

Ordering Information and Specifications



AccessTrak Expanded by Length




AccessTrak Expanded by Width

Description	Catalog Number	Length in. (mm)	Height in. (mm)	Width in. (mm)	Weight lbs. (kg)	Channel Width in. (mm)	Channel Height in. (mm)
AccessTrak® System							
5 Channel AccessTrak kit*, blue and gray.	HBLAT5KITA	41.06" (1043.0)	4.00" (102.0)	42.90" (1090.0)	59.85 lbs. (27.15 kg)	1.34" (34.0)	1.31" (33.0)
5 Channel AccessTrak trough, blue and gray.	HBLAT5A	36.00" (914.0)	1.94" (49.0)	13.34" (339.0)	17.26 lbs. (7.83 kg)	1.34" (34.0)	1.31" (33.0)
AccessTrak trough end rails (set), gray.	HBLAT5ERA	2.50" (63.0)	4.00" (102.0)	13.28" (337.0)	5.21 lbs. (2.36 kg)		
AccessTrak ramps (set), blue.	HBLAT5RAMPA	36.00" (914.0)	1.94" (49.0)	14.50" (368.0)	24.78 lbs. (11.24 kg)		
AccessTrak ramp end rails (set), gray.	HBLAT5RAMPERA	2.50" (63.5)	4.00" (102.0)	14.75" (375.0)	6.30 lbs. (2.86 kg)		


Note: * Consists of (1) HBLAT5A; (1 set) HBLAT5ERA; (1 set) HBLAT5RAMPA; (2 sets) HBLAT5RAMPERA.

Assembled Kit

Accessibility label, blue symbol, white background




Trough




Trough (side view)




Ramp (top view)




Trough End Rails (side view)




Ramp End Rails (top view)



Ramp End Rails (side view)



Ramp (side view)



Specifications

Material	Polyurethane.
Operating Temperature	-40°F to +120°F (-40°C to +49°C).
Hinge Material	Reinforced fiberglass.
Safety Symbols	Per ANSI Z535.3-1991.
ADA Symbols	Per ADAAG "Symbols of Accessibility".


Load Capacity

Test Fixture Footprint in. (mm)	Measured Load lbs. (N) +/- 20% 70°F (21°C)	120°F (49°C)
7" x 7" (178 x 178)	10,000 (44,480)	8,000 (35,584)




Hose and Cable Protection Systems
TrukTrak® System

Ordering Information and Specifications



HBLTT5B







HBLTT545LB



HBLTT545RB

Description	Catalog Number	A Length in. (mm)	B Width in. (mm)	C Height in. (mm)	Weight lbs. (kg)	Channel	
						D Width in. (mm)	E Height in. (mm)
TrukTrak® System							
5 Channel TrukTrak®, blue and yellow.	HBLTT5B	36.0" (914)	20" (508)	2.31" (58.7)	29 lbs. (13.2 kg)	1.25" (31.8)	1.25" (31.8)
5 Channel TrukTrak® end caps (pair only), yellow.	HBLTT5ECB (Female)	7.50" (190)	20" (508)	2.31" (58.7)	4.7 lbs. (2.1 kg)	1.25" (31.8)	1.25" (31.8)
		(Male)	5.25" (133)	20" (508)	2.31" (58.7)	4.7 lbs. (2.1 kg)	1.25" (31.8)
5 Channel 45° right turn TrukTrak®, blue and yellow.	HBLTT545RB	25.0" (635)	20" (508)	2.31" (58.7)	13 lbs. (5.9 kg)	1.25" (31.8)	1.25" (31.8)
5 Channel 45° left turn TrukTrak®, blue and yellow.	HBLTT545LB	25.0" (635)	20" (508)	2.31" (58.7)	13 lbs. (5.9 kg)	1.25" (31.8)	1.25" (31.8)
3 Channel TrukTrak®, blue and yellow.	HBLTT3B	36.0" (914)	20" (508)	3.05" (77.5)	36 lbs. (16.3 kg)	2.25" (57.2)	2.25" (57.2)
3 Channel TrukTrak® end caps (pair only), yellow.	HBLTT3ECB (Female)	8.25" (209)	20" (508)	3.05" (77.5)	6.5 lbs. (2.9 kg)	2.25" (57.2)	2.25" (57.2)
		(Male)	6.38" (162)	20" (508)	3.05" (77.5)	6.5 lbs. (2.9 kg)	2.25" (57.2)
2 Channel TrukTrak®, blue and yellow.	HBLTT2B	36.0" (914)	22" (559)	4.13" (104.9)	44 lbs. (19.9 kg)	3.25" (82.6)	3.25" (82.6)



Features	Benefits
High density polyurethane construction.	Supports heavy loads and is weather resistant.
Modular interlocking design.	Easy installation, breakdown and storage.
Safety surface pattern.	Reduces slipping and skidding.
Safety blue and yellow colors.	High visibility.

Specifications	
Material	Polyurethane.
Operating Temperature	-40°F to +120°F (-40°C to +49°C).
Hinge Material	Reinforced fiberglass.
Safety Symbols	Per ANSI Z535.3.


No. of Channels	Test Fixture Footprint in. (mm)	Load Capacity	
		Measured Load lbs. (N) 70°F (21°C)	Measured Load lbs. (N) 120°F (49°C)
5 Channel	6.9" x 17.3" (175 X 439)	20,150 (89,627)	9,200 (40,921)
3 Channel	6.9" x 17.3" (175 X 439)	14,210 (63,206)	4,653 (20,696)
2 Channel	6.9" x 17.3" (175 X 439)	10,880 (48,394)	2,095 (9,318)

HOSE AND CABLE PROTECTION

Hose and Cable Protection Systems

TredTrak® System


Ordering Information and Specifications



HBLTRED5B




HBLTRED5YB



HBLTRED5XB

Description	Catalog Number	A	B	C	Weight lbs. (kg)	Channel	
		Length in. (mm)	Width in. (mm)	Height in. (mm)		Width in. (mm)	Height in. (mm)
TredTrak® System							
5 Channel TredTrak®, blue and yellow.	HBLTRED5B	36.0" (914)	17.5" (445)	1.95" (50)	18 lbs. (8.2 kg)	1.30" (33)	1.30" (33)
5 Channel TredTrak® end caps (pair only), yellow.	HBLTRED5ECB	(Female)	5.5" (139)	17.5" (445)	1.95" (50)	2.5 lbs. (1.13kg)	1.30" (33)
		(Male)	5.5" (139)	17.5" (445)	1.95" (50)	2.5 lbs. (1.13kg)	1.30" (33)
5 Channel TredTrak female end caps (2 females), yellow.	HBLTRED5ECFB	5.5" (139)	17.5" (445)	1.95" (50)	2.5 lbs. (1.13kg)	1.30" (33)	1.30" (33)
5 Channel "X" fitting, blue and yellow.	HBLTRED5XB	17.5" (445)	17.5" (445)	1.95" (50)	12 lbs. (5.43kg)	1.30" (33)	1.30" (33)
5 Channel "Y" fitting, blue and yellow.	HBLTRED5YB	17.5" (445)	17.5" (445)	1.95" (50)	12 lbs. (5.43kg)	1.30" (33)	1.30" (33)



Specifications

Material	Polyurethane.
Operating Temperature	-40°F to +120°F (-40°C to +49°C).
Hinge Material	Reinforced fiberglass.
Safety Symbols	Per ANSI Z535.3.


Load Capacity

Product	Test Fixture Footprint in. (mm)	Measured Load lbs. (N) +/- 20%	
		70°F (21°C)	120°F (49°C)
TredTrak	6.9" x 17.3" (175 x 439)	10,500 (46,700)	6,500 (28,900)
"X" Fitting	6.9" x 17.3" (175 x 439)	2,900 (12,900)	2,300 (10,230)
"Y" Fitting	6.9" x 17.3" (175 x 439)	2,900 (12,900)	2,300 (10,230)

HOSE AND CABLE PROTECTION



Hose and Cable Protection Systems
FloorTrak® Floor Cable Cover



FloorTrak 2

Catalog Number	Color	Length Feet (meters)
FT2BK10	Black	10.0' (3.05)
FT2BR10	Brown	10.0' (3.05)
FT2BG10	Beige	10.0' (3.05)
FT2GY10	Gray	10.0' (3.05)
FT2Y10	Yellow	10.0' (3.05)

FloorTrak 3

Catalog Number	Color	Length Feet (meters)
FT3BK5	Black	5.0' (1.52)
FT3BK25	Black	25.0' (7.62)
FT3BR5	Brown	5.0' (1.52)
FT3BR25	Brown	25.0' (7.62)
FT3BG5	Beige	5.0' (1.52)
FT3BG25	Beige	25.0' (7.62)
FT3GY5	Gray	5.0' (1.52)
FT3GY25	Gray	25.0' (7.62)
FT3Y5	Yellow	5.0' (1.52)
FT3Y25	Yellow	25.0' (7.62)

FloorTrak 4

Catalog Number	Color	Length Feet (meters)
FT4BK5	Black	5.0' (1.52)
FT4BK25	Black	25.0' (7.62)
FT4GY25	Gray	25.0' (7.62)
FT4Y5	Yellow	5.0' (1.52)
FT4Y25	Yellow	25.0' (7.62)

FloorTrak 10 (Heavy Duty)

Catalog Number	Color	Length Feet (meters)
FT10BK3	Black	3.0' (.914)
FT10BK5	Black	5.0' (1.52)
FT10Y3	Yellow	3.0' (.914)
FT10Y5	Yellow	5.0' (1.52)

Accessories


Description	Catalog Number
1" Wide, 75' Roll Double-Sided Adhesive Tape.	FTT1
2" Wide, 75' Roll Double-Sided Adhesive Tape.	FTT2

Specifications

Material	Rigid PVC.
Operating Temperature	0°F to +120°F (-18°C to +49°C).


Dimensions

FloorTrak	FT2	FT3	FT4	FT10 (Heavy Duty)
Width (A)	2.75" (69.9)	3.00" (76.2)	3.25" (82.6)	5.6" (142.24)
Height (B)	.53" (13.5)	.75" (19.1)	1.10" (27.9)	1.7" (43.18)
Center Hole (Cx)D	.60" x .31" (15.2) x (7.9)	.75" x .50" (19.1) x (12.7)	1.21" x .75" (30.7) x (19.1)	1.81" x 1.25" (45.98 x 31.75)



CARRIER TRACK

MODULAR CARRIER TRAK





Non-metallic Cable/Hose Carriers

Protect cables and hoses on reciprocating machinery. Safety and reliability are increased when cables and hoses are kept together, away from moving components and operators. Durable links are molded from fiber-reinforced virgin nylon which is highly wear-resistant, self lubricating and not damaged by salt, hard water and lubricating oils or hydrocarbons such as fuels.




Modular Trak is available in a wide variety of configurations and sizes to handle cable or hose up to 1.676" dia. Larger sizes are available with standard closed tops, flip-tops to facilitate cable/hose installation, or completely enclosed models designed to protect cables and hoses from dirt, chips, etc. Kits of all styles facilitate application and purchasing. Standard and flip-top configurations are also available in bulk which is especially attractive to OEM and other high volume users. Refer to following pages for details.

Easy Assembly of Kits or Bulk Trak



Extenders or bulk sections snap easily into place. Each Extender provides one foot additional travel with end mounting, two feet additional travel with center mounting. Individual links may be removed to arrive at exact length.



Flip-Top




Quickly Install Cables and Hoses

Snap-In Separators (Optional for P16 and P25)

Group Cables and Hoses
OPTIONAL Snap-in Separators (see dimension "N") may be ordered for Types P16 and P25. Simple field installation.

Pkg of 12 P16 separators:
Model No. **P16SP**

Pkg of 12 P25 separators:
Model No. **P25SP**




MODULAR TRAK - KITS & BULK

BASIC KITS (C) include enough track to form the curve and provide for three ft. of machine travel (standard mounting) or six ft. of machine travel (center mounting). Mounting hardware included.

EXTENDERS (D) include one foot of track only - no hardware. Extenders are inserted into the BASIC KIT to provide additional travel and required overall length. Links snap together. Individual links can be easily removed with a screwdriver to provide custom length.

BULK TRAK is ideal for high volume users. Shipped in 10' lengths packed in 12" x 12" x 12" cartons or 3" lengths packed in 12.5" x 12.5" x 40" cartons. Bulk track does NOT include brackets. Order brackets (sets of 6 only) separately.



SELECTION

- 1. WINDOW.** See columns A & B below. Select trak that accommodates height and width of hose/cable bundle.
- 2. TRAVEL.** Measure machine travel. Determine if fixed point of trak is to be at end (standard mount) or in center of machine travel. See drawings, left.
- 3. ORDER TRAK.**
 - A. BASIC KIT (C)** provides 3' travel (standard mount), up to 6' for center mount.
 - B. EXTENDER KITS (D)** Provide 1' travel. Order as many as needed for travel.


Formula: Track travel (ft) minus 3 (rounded to next highest number) equals extender kits required.

NOTE: Individual links may be removed to obtain exact length. See DIMENSIONS page for length (pitch) of each size link.

A Max. Height Largest O.D. Hose/Cable in. (mm)	B Max. Width Hose/Cable Bundle in. (mm)	C Basic Kit 3 Ft. Travel (With brackets) Model No.	D Extender 1 Ft. Travel (No brackets) Model No.	Bulk Trak 3 Ft. Lengths Brackets NOT included Model No.	Total Length in Carton ft.	Brackets Male & Female 6 sets Model No.
0.286 (7)	0.531 (13)	P10-1-1.4-3.0	EP10-1-1.4-1.0	BP10-1-1.4	318	BB10-1
0.286 (7)	0.900 (23)	P10-2-1.4-3.0	EP10-2-1.4-1.0	BP10-2-1.4	264	BB10-2
0.382 (9)	0.900 (23)	P10-2-1.9-3.0	EP10-2-1.9-1.0	BP10-2-1.9	264	BB10-2
0.410 (10)	1.350 (34)	P13-1-2.0-3.0	EP13-1-2.0-1.0	BP13-1-2.0	120	BB13-1
0.740 (19)	1.350 (34)	P13-1-3.7-3.0	EP13-1-3.7-1.0	BP13-1-3.7	120	BB13-1
0.410 (10)	2.052 (52)	P13-2-2.0-3.0	EP13-2-2.0-1.0	BP13-2-2.0	96	BB13-2
0.740 (19)	2.052 (52)	P13-2-3.7-3.0	EP13-2-3.7-1.0	BP13-2-3.7	96	BB13-2
0.410 (10)	2.772 (70)	P13-3-2.0-3.0	EP13-3-2.0-1.0	BP13-3-2.0	72	BB13-3
0.740 (19)	2.772 (70)	P13-3-3.7-3.0	EP13-3-3.7-1.0	BP13-3-3.7	72	BB13-3
0.382 (9)	1.350 (34)	P16-1-1.9-3.0	EP16-1-1.9-1.0	BP16-1-1.9	90	BB16-1
0.688 (17)	1.350 (34)	P16-1-3.4-3.0	EP16-1-3.4-1.0	BP16-1-3.4	90	BB16-1
0.382 (9)	2.052 (52)	P16-2-1.9-3.0	EP16-2-1.9-1.0	BP16-2-1.9	84	BB16-2
0.688 (17)	2.052 (52)	P16-2-3.4-3.0	EP16-2-3.4-1.0	BP16-2-3.4	84	BB16-2
0.382 (9)	2.772 (70)	P16-3-1.9-3.0	EP16-3-1.9-1.0	BP16-3-1.9	63	BB16-3
0.688 (17)	2.772 (70)	P16-3-3.4-3.0	EP16-3-3.4-1.0	BP16-3-3.4	63	BB16-3
0.382 (9)	3.654 (93)	P16-4-1.9-3.0	EP16-4-1.9-1.0	BP16-4-1.9	42	BB16-4
0.688 (17)	3.654 (93)	P16-4-3.4-3.0	EP16-4-3.4-1.0	BP16-4-3.4	42	BB16-4
0.680 (17)	2.340 (59)	P25-1-3.4-3.0	EP25-1-3.4-1.0	BP25-1-3.4	36	BB25-1
0.680 (17)	3.825 (97)	P25-2-3.4-3.0	EP25-2-3.4-1.0	BP25-2-3.4	24	BB25-2
0.956 (24)	3.825 (97)	P25-2-4.7-3.0	EP25-2-4.7-1.0	BP25-2-4.7	24	BB25-2
1.546 (39)	3.825 (97)	P25-2-7.7-3.0	EP25-2-7.7-1.0	BP25-2-7.7	24	BB25-2
1.575 (40)	3.825 (97)	P25-2-11.6-3.0	EP25-2-11.6-1.0	BP25-2-11.6	24	BB25-2
0.956 (24)	5.940 (151)	P25-3-4.7-3.0	EP25-3-4.7-1.0	BP25-3-4.7	18	BB25-3
1.546 (39)	5.940 (151)	P25-3-7.7-3.0	EP25-3-7.7-1.0	BP25-3-7.7	18	BB25-3
0.468 (12)	1.350 (34)	T0815-2.3-3.0	ET0815-2.3-1.0	-	-	-
0.650 (16)	1.800 (82)	T1020-3.2-3.0	ET1020-3.2-1.0	-	-	-
0.900 (23)	1.800 (82)	T1020-5.8-3.0	ET1020-5.8-1.0	-	-	-
0.824 (21)	2.700 (69)	T1530-4.1-3.0	ET1530-4.1-1.0	-	-	-
1.350 (34)	2.700 (69)	T1530-7.7-3.0	ET1530-7.7-1.0	-	-	-
1.176 (30)	4.050 (103)	T2045-5.8-3.0	ET2045-5.8-1.0	-	-	-
1.676 (43)	4.050 (103)	T2045-8.3-3.0	ET2045-8.3-1.0	-	-	-



MODULAR TRAK DIMENSIONS



NOTES

- *MOUNTING:**
End Mounted trak travel equals *machine* travel.
Center Mounted trak travel equals 1/2 *machine* travel.
- **WEIGHT** per foot of trak only. Add weight per foot of hose/cable bundle.

SERIES	W	H	R	WGT** (lbs/ft.)	B	CLEARANCE C	OVERALL O	K	M	SEPARATOR N	PITCH P	OVERALL V
P10-1-1.4-...	0.59	0.75	1.43	0.20	3.86	2.00	1.00	5.68	1.33	-	1.250	1.03
P10-2-1.4-...	1.00	0.75	1.43	0.25	3.86	2.00	1.00	5.68	1.33	-	1.250	1.44
P10-2-1.9-...	1.00	0.75	1.91	0.25	4.82	2.00	1.00	5.41	1.33	-	1.250	1.44
P13-1-2.0-...	1.50	0.98	2.05	0.44	5.44	3.00	1.34	5.50	1.19	-	1.812	2.12
P13-1-3.7-...	1.50	0.98	3.70	0.44	8.74	3.00	1.34	7.56	1.19	-	1.812	2.12
P13-2-2.0-...	2.28	0.98	2.05	0.48	5.44	3.00	1.34	5.50	1.19	-	1.812	2.91
P13-2-2.7-...	2.28	0.98	3.70	0.48	8.74	3.00	1.34	7.56	1.19	-	1.812	2.91
P13-3-2.0-...	3.08	0.98	2.05	0.54	5.44	3.00	1.34	5.50	1.19	-	1.812	3.70
P13-3-3.7-...	3.08	0.98	3.70	0.54	8.74	3.00	1.34	7.56	1.19	-	1.812	3.70
P16-1-1.9-...	1.50	1.00	1.91	0.55	5.44	3.00	1.62	5.72	1.19	0.14 Ⓣ	1.812	2.12
P16-1-3.4-...	1.50	1.00	3.44	0.55	8.50	3.00	1.62	7.85	1.19	0.14 Ⓣ	1.812	2.12
P16-2-1.9-...	2.28	1.00	1.91	0.64	5.44	3.00	1.62	5.72	1.19	0.14 Ⓣ	1.812	2.91
P16-2-3.4-...	2.28	1.00	3.44	0.64	8.50	3.00	1.62	7.85	1.19	0.14 Ⓣ	1.812	2.91
P16-3-1.9-...	3.08	1.00	1.91	0.74	5.44	3.00	1.62	5.72	1.19	0.14 Ⓣ	1.812	3.70
P16-3-3.4-...	3.08	1.00	3.44	0.74	8.50	3.00	1.62	7.85	1.19	0.14 Ⓣ	1.812	3.70
P16-4-1.9-...	4.06	1.00	1.91	0.84	5.44	3.00	1.62	5.72	1.19	0.14 Ⓣ	1.812	4.69
P16-4-3.4-...	4.06	1.00	3.44	0.84	8.50	3.00	1.62	7.85	1.19	0.14 Ⓣ	1.812	4.69
P25-1-3.4-...	2.60	1.75	3.40	1.00	9.30	3.00	2.50	8.31	1.19	0.15 Ⓣ	2.500	3.70
P25-2-3.4-...	4.25	1.75	3.40	1.20	9.30	3.00	2.50	8.31	1.19	0.15 Ⓣ	2.500	5.36
P25-2-4.7-...	4.25	1.75	4.78	1.20	12.06	3.00	2.50	10.52	1.19	0.15 Ⓣ	2.500	5.36
P25-2-7.7-...	4.25	1.75	7.73	1.20	17.96	3.00	2.50	11.84	1.19	0.15 Ⓣ	2.500	5.36
P25-2-11.6-...	4.25	1.75	11.67	1.20	25.84	3.00	2.50	15.59	1.19	0.15 Ⓣ	2.500	5.36
P25-3-4.7-...	6.60	1.75	4.78	1.50	12.06	3.00	2.50	10.52	1.19	0.15 Ⓣ	2.500	7.70
P25-3-7.7-...	6.60	1.75	7.73	1.50	17.96	3.00	2.50	11.84	1.19	0.15 Ⓣ	2.500	7.70
T0815-2.3-...	1.50	0.81	2.34	0.62	6.34	2.75	1.31	5.32	2.56	-	1.125	2.20
T1020-3.2-...	2.00	1.00	3.25	0.83	8.34	2.75	1.50	7.89	2.81	-	1.375	2.76
T1020-5.8-...	2.00	1.00	5.88	0.83	13.61	2.75	1.50	9.39	2.81	-	1.375	2.76
T1530-4.1-...	3.00	1.50	4.12	1.48	10.92	2.75	2.25	10.77	4.00	-	2.000	3.93
T1530-7.7-...	3.00	1.50	7.75	1.48	18.18	2.75	2.25	14.70	4.00	-	2.000	3.93
T2045-5.8-...	4.50	2.00	5.88	2.20	14.94	2.75	2.75	13.02	4.75	-	2.562	5.55
T2045-8.3-...	4.50	2.00	8.38	2.20	19.94	2.75	2.75	17.59	4.75	-	2.562	5.55

Ⓣ Brackets for BP16 and BP25 (bulk) shipped six male and six female per box. Brackets included with 3 ft. basic (non-bulk) kits.



HOSE AND CABLE PROTECTION