

FEC-3000 IP-65 Water-Proof Bench Scales



PRODUCT DESCRIPTION

These compact, sturdy portable series of scales are ideal for use in harsh working environments and food service applications. They have a stainless steel case which is dust and water-proof to IP-65. They are simple to use having a membrane keypad with a four key operation.

- Dust-tight & water-protected to IP-65 rating - protected against dust & water splashing
- Weighs in kg, g, lb, oz & lbz/oz
- Stainless steel case with adjustable non-slip rubber feet and a bulls eye level bubble
- 175 x 165mm stainless steel weighing pan
- Large 32mm LCD display with backlight
- Automatic backlight when weight is added to the pan (can be disabled)
- Zero tracking ensures stable and repeatable readings
- Stability indicator
- Simple four key operation
- Plus/minus weighing
- Parts counting from 10, 20, 50 or 100 samples pieces
- Overload warning display
- Low battery indication
- Auto power-off - can be user disabled for continuous use
- Supplied with batteries and an adapter. (The adapter supplied is not waterproof so the scale is not protected to IP-65 when the adapter is used)

TECHNICAL SPECIFICATION

Capacity	3000g
Resolution	0.1g
Min Pcs Wt	1g
Accuracy	±0.2g
Power	6x 1.5V AA Alkaline Batteries (ALR-6) Mains Power Adapter (Supplied)
Dimensions	175 x 165mm (Pan), 245 x 195 x 70mm (Unit)
Weight	2Kg