

IR-801 Laser Infrared Thermometer



PRODUCT DESCRIPTION

This pocket size and easy-to-use infrared thermometer with Class II laser sighting is ideal for non-contact measurement of surface temperatures. Suitable for food preparation, plant & general maintenance, HVAC, transport & automotive, asphalt, health & safety, diesel and fleet maintenance.

- -50° to 350°C x 0.1°
- Measures °C or °F
- Just point, pull the trigger and read the display
- Class II laser to identify the centre point of the area being measured
- Distance to spot size ratio is 13 to 1 at the focal point
- Fixed emissivity at 0.95
- Response time less than 500 milliseconds
- 25mm LCD display with backlight
- Automatic data hold when trigger released
- Mix/Max memory
- Auto power off after 20 seconds of no activity
- Low battery indication
- Backlight and laser can be user disabled
- Impact-resistant ABS plastic case
- Supplied with manual and battery

TECHNICAL SPECIFICATION

Range	-50° to 350°C
Resolution	0.1°C
Accuracy	±2% of reading ±2°C
Power	1 x 9V PP3 Alkaline Battery (ALR-61)
Dimensions	160 x 99 x 28mm
Weight	176g