

Data Sheet

SP066xxVBNC


Page 1/4

Order Number

SP066xxVBNC

xx=number of poles

Illustration



see enlarged drawing at the end of the document

Product specification

- spring clamp terminal block, pluggable
- centerline 5.08 mm, direction of connection vertical (0°)
- fittable without loss of poles
- color black
- push-button, wire entry uncodeable side parallel to plug direction
- Connection data

CRIUS V / A / AWG 250 / 12 / 28 - 12

SEV 0.08 - 2.5 mm² 250 V / 4 kV / 12 A

Data Sheet

SP066xxVBNC

Page 2/4

Order Number

SP066xxVBNC



xx=number of poles

Technical Data

General Data

min. number of positions	2		
max. number of positions	24		
Insulating material class	CTI 600		
clearance/creepage dist.	3.58 mm		
protection category	IP 20		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	630 V	630 V
Stossspannung	2.5 kV	6 kV	4 kV

Connection data

 V / A / AWG	250 / 12 / 28 - 12
 0.08 - 2.5 mm ²	250 V / 4 kV / 12 A

Material

insulating material	PA66
flammability class	V0

Climatic properties

Data Sheet

SP066xxVBNC

Page 3/4

Order Number

SP066xxVBNC

xx=number of poles

upper limit temperature	105 °C
-------------------------	--------

lower limit temperature	-40 °C
-------------------------	--------

General

tolerance	ISO 2768 -mH
-----------	--------------

Matching Part

312191	Type 219
--------	----------

312201	Type 220
--------	----------

314781	Typ 478
--------	---------

314791	Typ 479
--------	---------

Accessories

700025-01-5 (on request)	Kodierstern blau
--------------------------	------------------

700025-01-9	Kodierstern weiß
-------------	------------------

840020-02 (on request)	Drahtbrücke 0.8 RM 5.0
------------------------	------------------------


Data Sheet

SP066xxVBNC

Page 4/4
Order Number
SP066xxVBNC
xx=number of poles

Illustration

Drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 5.08 [0,200]$