


Product data sheet

Characteristics

XVS96BMWN

electronic alarm - 16 tones - 0..96 dB - NPN
output - white - IP54



Main

Range of product	Harmony XVS
Product or component type	Electronic alarm
Device short name	XVS

Complementary

Colour	White
Material	PC/ABS (body) PC (terminal cover)
Product weight	0.4 kg
Marking	CE
Product mounting	DIN96 panel mounting
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	354 mA at 24 V 292 mA at 24 V 292 mA at 12 V 250 mA at 12 V
Clamping connection capacity	<= 1 x 1.5 mm ²
Width	96 mm
Height	96 mm
Depth	58.1 mm

Environment

Discrete output type	NPN
Signalling type	16 tones alarm
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-20...50 °C
Class of protection against electric shock	Class II conforming to EN/IEC 61140
IP degree of protection	IP54 conforming to EN/IEC 60529
[Us] rated supply voltage	24 V AC/DC 12 V AC/DC
Noise level	0..96 dB (continuous or intermittent tone) at 1 m

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0808 - Schneider Electric declaration of conformity

Electronic Alarm

Dimensions

