

Product data sheet

Characteristics

XVS14MMW

multisound siren XVS - 43 tones - 0..105 dB - white - IP53



Main

Range of product	Harmony XVS
Product or component type	Multisound siren
Device short name	XVS

Complementary

Colour	White
Material	PC/ABS (body)
Product weight	1.2 kg
Marking	CE
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	50 mA at 240 V
Electrical connection	Cable: 6.5...8.5 mm, 0.52 mm ² / AWG 20 (power circuit) Cable : 6.5...8.5 mm, 0.33 mm ² / AWG 22 (signalling circuit)
Width	140 mm
Height	114 mm
Depth	223 mm

Environment

Signalling type	43 tones siren
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Class of protection against electric shock	Class II conforming to EN/IEC 61140
IP degree of protection	IP53 conforming to EN/IEC 60529
[Us] rated supply voltage	240 V AC
Noise level	0...105 dB (continuous or intermittent tone) at 1 m

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0808 - Schneider Electric declaration of conformity

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Siren

Dimensions

