

## For Patient-Care Vicinity - UL 60601-1 Medical-Grade Power Strip with Surge Protection and 4 Hospital Grade Outlets, 1410 Joules

MODEL NUMBER: **SPS415HGULTRA**



### Description

The SPS415HGULTRA is the first Medical-Grade Outlet Strip with Surge Suppression and full UL 60601-1/60950-1 compliance. Tested to U.S. and Canadian safety standards, it is the first of its kind to be agency approved for use in patient-care areas, including physicians' offices, imaging centers, laboratories and more. The SPS415HGULTRA is ideal for protecting electrical equipment from damaging surges and spikes within patient vicinity. Features include switchless design to prevent accidental shutoff, four NEMA 5-15R-HG hospital-grade outlets with safety covers, 1410 joules of surge suppression, NEMA 5-15P-HG hospital-grade plug and 15A resettable circuit breaker.

### Features

- Surge protection
- Approved for use in Patient-Care Areas
- Rugged all-metal housing stands up to the most demanding environments
- 4 x NEMA 5-15R-HG outlets with safety covers
- 1410 joules of surge suppression
- 15-ft. cord with NEMA 5-15P-HG plug
- Switchless design prevents accidental shutoff
- 15A circuit breaker
- Multiple installation options with integral mounting flanges and slots
- UL60601-1 and UL 60950-1 compliant
- U.S. Patent No. 7,375,939 & U.S. Patent No. 8,339,759

## Specifications

### Highlights

- Full UL 60601-1/60950-1 compliance
- Approved for use within 6-ft. of patient-care areas
- 4 outlets, 15-ft. cord with NEMA 5-15P hospital-grade plug
- 1410 joules of surge suppression
- 15A resettable circuit breaker
- Switchless design prevents accidental shutoff
- Integrated locking outlet safety covers guard against contact with unused outlets
- Diagnostic LED indicates that power is present and surge protected (with no ground faults or line/neutral reversals)
- US Patent # 7,375,939 & U.S. Patent No. 8,339,759

### Applications

- AC power distribution surge suppression with hospital-grade receptacles and plug in healthcare applications where durability and reliability are required, including areas where NEC requires hospital-grade receptacles
- Patient rooms, treatment rooms, exam rooms, etc.

### Package Includes

- SPS415HGULTRA Medical-Grade Outlet Strip with Surge Suppression
- Owner's manual with warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

OVERVIEW	
Style	Strip
Model Type	For Patient-Care Areas
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A resettable circuit breaker
Outlet Safety Covers	Yes
Outlet Orientation	Single row of 4
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
LEDS ALARMS & SWITCHES	
LED Indicators	Proper wiring and surge protection working
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1410
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Weight (lbs.)	3.2



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Weight (kg)	1.5
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Yes
Receptacle Color	White
Color (AC Line Cord)	White
<b>CERTIFICATIONS</b>	
Approvals	TUV tested to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.