

PT-E550WVP

Handheld Electrician Labelling Printer



Top Features:

Backlit graphic display

- Easy-to-read text and the ability to preview your label before printing.

Multiple power options

- Supplied with an AC adaptor and a rechargeable Li-ion rechargeable battery. Also works with 6 AA batteries (not supplied)

Lots of built-in contents

- Customise labels using a choice of 9 fonts, 7 frames and 384 symbols

Built-in auto full & half cutter

- Guaranteed to cut strong adhesive tapes
- Perfect for printing multiple/sequentially numbered labels
- With cut/pause to help reduce waste

Wi-Fi enabled

- Print to the device via the network
- Transfer content such as label templates, databases or custom symbols wirelessly from your PC to the PT-E550W
- Establish a P2P connection with your mobile devices (iOS and Android) in the direct mode to create label layouts on your Smartphone

Standard PC style keyboard

- Makes typing efficient.

Convenient labelling

- Handheld design and battery power lets you print labels wherever they are required.

Smart label application keys to save time

- General/Faceplate
- Cable Wrap/Cable Flag/Heat Shrink Tube/¹Self-laminated
- Patch Panel / Punch Down Block
- Serialize / Advanced Serialize

Specialist HSe heat shrink tubes available

- HSe-211 (5.8mm)
- HSe-221 (8.8mm)
- HSe-231 (11.7mm)
- HSe-241 (17.7mm)
- HSE-251 (23.6mm)

General

Carton contents	PT-E550WVP labelling machine 24mm strong adhesive black on yellow 8m tape cassette 12mm flexible ID black on white 8m tape Li-ion rechargeable battery AC adaptor Wrist strap Documentation USB-mini cable Software CD Carry case
Language support	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Brazilian Portuguese, Turkish

Dimensions & Weights

Without carton	126(w) x 250(d) x 94(h) † 1.05 kg
With carton	393(w) x 334(d) x 126(h) † 3.25 kg
Master carton	413(w) x 348(d) x 390(h) † 11.04 kg

Built In Features

Keyboard	70 Key Rubber QWERTY/QWERTZ/AZERTY
Dedicated number keypad	Yes
Interfaces	USB, Wi-Fi
Operating system support	Microsoft Windows® Vista, Windows® 7, Windows® 8, Mac OS/X 10.7to 10.9.
Display type	Backlit Graphic Monochrome LCD with label preview capability
Display resolution	16 characters by 3 lines † 128 x 64 dots
Printing speed	Up to 30mm/second
Print resolution	180dpi
Maximum print height	18.0mm
Cutter type	Auto Full & Half (with cut/pause feature) (fluorine-coated to cut strong adhesive tapes)
Label length	15mm minimum † 999mm maximum
Maximum lines per label	7 (for 24mm wide tape)
Tape margins	Auto Cut: On/Off, Half Cut: On/Off, Chain Printing: On/Off, Special Tape: On/Off
Vertical text printing	Yes
Mirror printing	No
Copies	1 to 99
Automatic numbering	Yes (1 – 99, Normal, Simultaneous, Advanced)

Label Creation

Smart label application keys	General, Faceplate, Cable Wrap, Cable Flag, Heat Shrink Tube, Patch Panel, Punch Down Block
Fonts	14 † Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Calgary, Belgium, Atlanta, Adams, Brunei, Sofia, Germany, Letter Gothic
Font styles	9 (excl. Normal) † Normal, Bold, Outline, Shadow, Solid, Italic, Italic Bold, Italic Outline, Italic Shadow, Italic Solid
Font sizes	6, 9, 12, 18, 24, 36, 42, 48 point
Symbols	384
Frames	7
Barcodes	9 † CODE39, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128 (UCC/EAN128), CODE128

Memory

Max. characters per label	1,500
Label memory locations	99 (or up to 18,297 characters)
Transferred content	6 MB † Label templates: up to 99 Custom symbols: up to 99 Databases: up to 99

Supplies

Tape type	TZe, HGe, HSe (Heat Shrink Tube)
Tape widths	3.5, 6, 9, 12, 18 & 24mm

Optional Accessories

Batteries	BA-E001 Li-ion rechargeable battery AA alkaline/rechargeable batteries (LR6/HR6) x 6
AC adaptor	AD-E001