




[Heatsinks home](#)
[Contact technical sales](#)
[Find another heatsink type](#)

Please see the [accessories page](#) for more details on clips, wire forms and interface material or [contact us](#).



Length	Part Number Without Pins	Clip	Thermal Rating °C/W	Stock Category
50.0	PPL0500B	n/a	5.00	A
75.0	PPL0750B	n/a	3.70	A
100.0	PPL1000B	n/a	3.10	A
150.0	PPL1500B	n/a	2.30	A

Where a device is shown it is for illustrative purposes only. The heatsink is supplied without a device. All ABL heatsinks are normally supplied black anodised to assist thermal performance.

Thermal Resistance is calculated based on a distributed heat load on anodised heatsink with vertically mounted fins based on a 60°C temperature rise. Under general operating conditions the thermal mounting arrangement of devices is not known and therefore the figures should be used only as a guide to selection.

We recommend that the effectiveness of any heatsink is tested in the specific operating environment in which it will be subjected. All information is for reference purposes only.