



HAND TORCHES

HIGH POWER CREE LED

T9505 LED HAND TORCH 100 LUMENS


Lightweight and pocket sized, the impressively powerful T9505 punches well above its weight.

Specification:

- > High Power 100 Lumen Cree XP-E R3 LED
- > 3 Lighting modes: high, dimmed, flash
- > One-handed rapid slide focus mechanism - spot (x1) to flood (x6)
- > Beam intensifying plano-convex optical lens
- > Robust high grade aluminium body
- > Water & dirt resistant, tested to IP64
- > Battery life: high - 3hrs, dimmed - 7hrs
- > Size: 98 x 26mm



100 LUMENS



Beam	Max Range	Weather Rating	Impact Resistant	Power Supply	Battery Life
Spot x1 : Flood x6	80m	IP64	1M	1 x AA (not supplied)	Up to 7 hours

NEW



Handy pocket size design



T9510 LED HAND TORCH 120 LUMENS


Offering up to 16hrs of quality light from a single set of batteries, the T9510 is ready for action whenever it's needed.

Specification:


- > High Power 120 Lumen Cree XR-E Q5 LED
- > 3 Lighting modes: high, dimmed, flash
- > One-handed rapid slide focus mechanism - spot (x1) to flood (x10)
- > Beam intensifying plano-convex optical lens
- > Robust high grade aluminium body
- > Water & dirt resistant, tested to IP64
- > Battery life: high - 6hrs, dimmed - 16hrs
- > Size: 107 x 30mm



120 LUMENS



Beam	Max Range	Weather Rating	Impact Resistant	Power Supply	Battery Life
Spot x1 : Flood x10	150m	IP64	1M	3 x AAA (not supplied)	Up to 16 hours



Plano-convex optical lens



T9520 LED HAND TORCH 150 LUMENS


The versatile T9520 hand torch has a remarkable 250m spot beam range and an extremely broad x30 flood beam.

Specification:

- > High Power 150 Lumen Cree XR-E Q5 LED
- > 3 Lighting modes: high, dimmed, flash
- > One-handed rapid slide focus mechanism - spot (x1) to flood (x30)
- > Beam intensifying plano-convex optical lens
- > Robust high grade aluminium body
- > Water & dirt resistant, tested to IP64
- > Battery life: high - 5hrs, dimmed - 14hrs
- > Size: 133 x 40mm



150 LUMENS



Beam	Max Range	Weather Rating	Impact Resistant	Power Supply	Battery Life
Spot x1 : Flood x30	250m	IP64	1M	3 x AAA (not supplied)	Up to 14 hours



Rapid slide focus mechanism

