

Data Sheet

SP046xxVBNC

(ASP046)


Page 1/5

Order Number

ASP046xx

xx=number of poles

Illustration



see enlarged drawing at the end of the document

Product specification

- spring clamp terminal block, pluggable
- centerline 5.08 mm, direction of connection vertical (0°)
- fittable without loss of poles
- color black
- eccentric lever, wire entry undcodeable side parallel to plug direction
- Connection data

CRIUS V / A / AWG 300 / 10 / 28 - 16

SEV 0.08 - 1.5 mm² 450 V / 4 kV / 10 A

Data Sheet

SP046xxVBNC

(ASP046)

Page 2/5

Order Number

ASP046xx



xx=number of poles

Technical Data

General Data

min. number of positions	2		
max. number of positions	24		
Insulating material class	CTI 400		
clearance/creepage dist.	4 mm		
protection category	IP 20		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	500 V	500 V
Rated test voltage	2.5 kV	4 kV	2.5 kV

Connection data

 V / A / AWG	300 / 10 / 28 - 16
 0.08 - 1.5 mm ²	450 V / 4 kV / 10 A

Material

insulating material	PA46
flammability class	V0

Climatic properties

Data Sheet

SP046xxVBNC

(ASP046)

Page 3/5

Order Number

ASP046xx

xx=number of poles

upper limit temperature	105 °C
-------------------------	--------

lower limit temperature	-40 °C
-------------------------	--------

General

Tolerance	ISO 2768 -mH
-----------	--------------

Matching Part

311781	Type 178
--------	----------

314781	Typ 478
--------	---------

312921	Type 292
--------	----------

312901	Type 290
--------	----------

312881	Type 288
--------	----------

312861	Type 286
--------	----------

312301	Type 230
--------	----------

312291	Type 229
--------	----------

312201	Type 220
--------	----------

312191	Type 219
--------	----------

314791	Typ 479
--------	---------

Matching Part to

312861	Type 286
--------	----------

Data Sheet

SP046xxVBNC

(ASP046)

Page 4/5
Order Number
ASP046xx
xx=number of poles

312881

Type 288

Accessories

700025-01-9

Kodierstern weiß

Data Sheet

SP046xxVBNC

(ASP046)

Page 5/5


Order Number

ASP046xx

xx=number of poles

Illustration

Drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 5 [0,200]$