

## SATELLITE SIGNAL SPLITTERS




Fig. 1



Fig. 2



Fig. 4



Fig. 5

### 2 GHz Satellite Splitters (Economy)

Retail Part No.	Bulk Part No.	Figure Number	Description	Plating	Frequency (MHz)	Insertion Loss(dB)	Isolation(dB)	Return Loss In(dB)	Return Loss Out(dB)
	SD-504-BU	1	4-way 5-2050 MHz	Nickel	5-2050	N/A	N/A	N/A	N/A

### 2 GHz Satellite Splitters 8-way (Economy)

Retail Part No.	Bulk Part No.	Figure Number	Description	Plating	Frequency(MHz)	Insertion Loss(dB)	Isolation(dB)min	Return Loss(dB)min
SD-528		2	8-way PP 5-2400 MHz	Nickel	0-5 5-47 47-1000 1000-1750 1750-2150 2150-2400	13.359 13.008 13.182 15.551 15-813 16.989	23.486 24.435 26.501 22.859 22.299 21.956	10 8 8 8 8 8

Note: PP=Power Passing

### Satellite Attenuator Pads

Retail Part No.	Bulk Part No.	Figure Number	Plating	Specifications
	SD-553-BU	4	Nickel	40-2400 MHz; 75Ω; Insertion Loss-3dB; Return Loss-20dB

### "F" Coax Terminator

Retail Part No.	Bulk Part No.	Figure Number	Description	Quantity/ Retail Pack
32-436	32-436-BU	5	"F" Terminator 75 Ohm 1/2 Watt @ 5%	5