# **GSP500 Series**

# **AC-DC Power Supplies**



# 500 Watts

- Convection/Forced-cooled Ratings
- Universal 85 264 VAC Input
- IT & Medical Safety Approvals
- < 0.5 W Standby Power
- -40° C to +70° C Operation
- Remote On/Off
- 5 V/2 A Standby Output
- 3 Year Warranty



The GSP500 has been designed to offer a full 500W of output power in a very small mechanical footprint, whilst still providing peak power to 650W, a 5V standby output with 2Amps of current capability and an input standby power draw of < 0.5W when the inhibit is activated.

Approved for both IT and medical applications the series has output versions from 12V to 48V and can be supplied as a U channel for system cooling or with optional very quiet integral fans (-EF). These fans are intelligently controlled to provide the most optimised accoustic noise in the system and further more the GSP500 can provide up to 180W without forced cooling, thus allowing fans to be switched off during periods of lower system loading.

#### **Dimensions:**

GSP:

 $6.00 \times 4.00 \times 1.65$ " (152.4 × 101.6 × 41.9 mm) (-EF):  $6.71 \times 4.00 \times 1.65$ " (152.4 × 101.6 × 41.9 mm)


## **Models & Ratings**

Output	Output C	Current V1	Standby	/ Supply	Fan Supply	Max Outp	out Power	Model Number (1)
Voltage	Convection	Forced	Convection	Forced	ran Supply	Nom	Peak (2)	Wiodel Nullibel
12.0 VDC	15.00 A	42.0 A	5 V/1 A	5 V/2 A	12 V/0.3 A	500 W	650 W	GSP500PS12-EF
24.0 VDC	7.50 A	21.0 A	5 V/1 A	5 V/2 A	12 V/0.3 A	500 W	650 W	GSP500PS24-EF
48.0 VDC	3.75 A	10.5 A	5 V/1 A	5 V/2 A	12 V/0.3 A	500 W	650 W	GSP500PS48-EF

### **Notes**

- 1. Remove suffix -EF for use with integral system cooling.
- 2. Peak power available for 100 ms maximum with 10% duty cycle, not recommended for use as pulsed output.

## **Mechanical Details**






Input					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage - Operating	85	115/230	264	VAC	Derate output power <90 VAC. See fig 1.
Input Voltage - Fault condition			300	VAC	5 second max
Input Frequency	47	50/60	63	Hz	
Power Factor		>0.9			230 VAC, 100% load
Input Current - Full Load		5.0/2.4		A	115/230 VAC
Inrush Current		60		A	
		0.3	0.5		All models, when inhibit activated
		2.8			GSP500PS12 - 115 VAC
		1			GSP500PS12 - 230 VAC
No Load Input Power		2.8		W	GSP500PS24 - 115 VAC
		1.2			GSP500PS24 - 230 VAC
		4.8			GSP500PS48 - 115 VAC
		2.3			GSP500PS48 - 230 VAC
Earth Leakage Current		80/220	250	μA	115/230 VAC/50 Hz Typ., 264 VAC/60 Hz Max.
Input Protection	F16 A/250 V inte	rnal fuse in both lin	ies		,

Output					
Characteristic	Minimum	Typical	Maximuµm	Units	Notes & Conditions
Output Voltage - V1	12		48	VDC	See Models and Ratings table
Initial Set Accuracy			±1	%	50% load, 115/230 VAC
Output Voltage Adjustment				%	No adjustment
Minimum Load	0			A	
Start Up Delay		0.5	2	S	115/230 VAC full load from input AC turn on
Hold Up Time	20			ms	
Drift			±0.2	%	After 20 min warm up
Line Regulation		0.01	0.5	%	90-264 VAC
Load Regulation		0.2	0.5	%	0-100% load
Transient Response - V1			4	%	Recovery within 1% in less than 500 μs for a 50-75% and 75-50% load step
Over/Undershoot - V1		0 /		%	
Ripple & Noise - V1		0.5	1	% pk-pk	20 MHz bandwidth
Overvoltage Protection - V1	115		140	%	Vnom DC. Output 1, recycle input to reset
Overload Protection - V1	110		150	% I nom	See fig. 2. Trip and Restart
Short Circuit Protection - V1					Shutdown & auto recovery
Temperature Coefficient			0.05	%/°C	
Overtemperature Protection					Shutdown & auto recovery


## **Input Voltage Derating Curve**

Figure 1



## **Output Overload Characteristic**

Figure 2 GSP500PS12 example (others similar).





General					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		90		%	230 VAC Full load (see fig.3-5)
Isolation: Input to Output	4000			VAC	
Input to Ground	1500			VAC	
Output to Ground	500			VDC	
		65			PFC Converter
Switching Frequency	50		200	kHz	Main Converter
		100			Standby Converter
Power Density			12.6	W/in³	
Mean Time Between Failure		216		kHrs	MIL-HDBK-217F, Notice 2 +25 °C GB
Maiaht		1.87 (0.85)		lb (kg)	GSP500PSxx models
Weight		1.94 (0.88)		lb (kg)	GSP500PSxx-EF models





Figure 5 48 V Models






Signals & Controls	
Characteristic	Notes & Conditions
Power Fail (AC-OK)	Open collector referenced to negative sense, transistor normally off when AC is good (see fig. 5) AC OK: Provides ≥ 5 ms warning of loss of output from AC failure off when AC is healthy.
Inhibit	Uncommitted isolated optocoupler diode, powered diode inhibits both V1 and fan supply (see fig. 6)
Output Good	LED Indicator
Fan Speed Control GSP500PSxx-EF Models	The fan speed is set to one of 4 states (high, mid, low & off) dependant on the internal power supply ambient temperature, input voltage and output load at any given time.
Standby Supply	5V/2A Isolated supply present when AC applied.


### Power Fail (AC-OK)

### Figure 5



### Remote On/Off (Inhibit)

Figure 6




- PAY/11	onmer	1
		шч

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-40		+70	°C	See derating curve, fig. 7
Storage Temperature	-40		+85	°C	
Cooling	12			CFM	GSP500PSxx models
Humidity	5		95	%RH	Non-condensing
Operating Altitude			5000	m	
Association For Noise	03/	TBA		Lw db(A)	Full Speed
Accoustic Fan Noise GSP500PSxx-EF Models		TBA		Lw db(A)	Mid Speed
GOI 3001 3XX-EI Wodels		TBA		Lw db(A)	Low Speed
Shock					±3 x 30g shocks in each plane, total 18 shocks. 30g = 11ms (+/-0.5msec), half sine. Conforms to EN60068-2-27 & EN60068-2-47
Vibration					Single axis 10 - 500 Hz at 2g sweep and endurance at resonance in all 3 planes. Conforms to EN60068-2-6

## **Thermal Derating Curve**

Figure 7



# **GSP500 Series**





# **EMC: Emissions**

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Conducted	EN55011/22	Class B		
Radiated	EN55011/22	Class A		
Harmonic Fluctuations	EN61000-3-3			

-M	•	<b>Immunity</b>
	<b>U</b> .	

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Low Voltage PSU EMC	EN61204-3	High severity level	as below	
		Class A		All models
Harmonic Current	EN61000-3-2	Class C		> 50 W
Radiated	EN61000-4-3	3	А	
EFT	EN61000-4-4	3	А	
Surges	EN61000-4-5	Installation class 3	A	
Conducted	EN61000-4-6	3	A \	
	EN55004	Dip >95% (0 VAC), 8.3ms	A	
	EN55024 (100 VAC)	Dip 30% (70 VAC), 416ms	B	
		Dip >95% (0 VAC), 4160ms	В	
	ENESSO 4	Dip >95% (0 VAC), 10.0ms	A	
	EN55024 (240 VAC)	Dip 30% (168 VAC), 500ms	В	
	(240 1/10)	Dip >95% (0 VAC), 5000ms	В	
5		Dip >95% (0 VAC), 10.0ms	Α	
Dips and Interruptions	EN60601-1-2	Dip 60% (40 VAC), 100ms	Α	Derate Output Power to 250 W
	(100 VAC)	Dip 30% (70 VAC), 500ms	А	
		Díp >95% (0 VAC), 5000ms	В	
		Dip >95% (0 VAC), 10.0ms	А	
	EN60601-1-2	Dip 60% (96 VAC), 100ms	Α	
	(240 VAC)	Dip 30% (168 VAC), 500ms	А	
		Dip >95% (0 VAC), 5000ms	В	

# Safety Approvals


Safety Agency	Safety Standard	Notes & Conditions		
CB Report	IEC60950-1:2005 Ed 2	Information Technology		
CB Report	IEC60601-1 Ed 3 Including Risk Management	Medical		
UL	UL60950-1 (2007), CSA 22.2 No.60950-1-1:08	Information Technology		
	ANSI/AAMI ES60601-1:2005 & CSA C22.2, No.60601-1:08	Medical		
TUV	EN60950-1:2006	Information Technology		
100	EN60601-1/A12:2006	Medical		
CE	LVD & RoHS			
Equipment Protection Class	Class I	See safety agency conditions of acceptibility for details		

	Means of Protection	Category	
Primary to Secondary 2 x MOPP (Means of Patient Protection)		IEC60601-1 Ed 3	
Primary to Earth 1 x MOPP (Means of Patient Protection)		1LC00001-1 Ld 3	



# **Mechanical Details**

### GSP500-EF



Fan Connector <sup>(3)</sup> S3B-PH-KL(LF)		
Pin	Function	
1	+12 V	
2	N/C	
3	GND	

Logic Connector <sup>(3)</sup> JST B10B-PHDSS		
Pin	Function	
1	+Sense	
2	-Sense	
3	Power Rail	
4	N/C	
5	Current Share	
6	Current Share	
7	+Inhibit	
8	-Inhibit	
9	+5V Standby	
10	-5V Standby	

### Notes

<sup>1.</sup> All dimensions in inches (mm).


<sup>2.</sup> Tolerance .xx =  $\pm 0.02$  (0.50); .xxx =  $\pm 0.01$  (0.25)


Fan connector mates with JST housing PHR-3 and SPH-002T-P0.5S crimp terminals or equivalent. Logic connector J301 mates with JST housing PHDR-10VS and SPHD-001T-P0.5 crimp terminals.





# **Mechanical Details**


### **GSP500**
















Fan Connector <sup>®</sup> S3B-PH-KL(LF)	
Pin	Function
1	+12 V
2	N/C
3	GND

Logic Connector <sup>(3)</sup> JST B10B-PHDSS		
Pin	Function	
1	+Sense	
2	-Sense	
3	Power Rail	
4	N/C	
5	Current Share	
6	Current Share	
7	+Inhibit	
8	-Inhibit	
9	+5V Standby	
10	-5V Standby	

### **Notes**

- 1. All dimensions in inches (mm).
- 2. Tolerance .xx =  $\pm 0.02$  (0.50); .xxx =  $\pm 0.01$  (0.25)
- 3. Fan connector mates with JST housing PHR-3 and SPH-002T-P0.5S crimp terminals or equivalent. Logic connector J301 mates with JST housing PHDR-10VS and SPHD-001T-P0.5 crimp terminals.



# Thermal Considerations - GSP500PSxx Models Only

In order to ensure safe operation of the PSU in the end-use equipment, the temperature of the components listed in the table below must not be exceeded. Temperature should be monitored using K type thermocouples placed on the hottest part of the component (out of direct air flow). See below for component locations.

Temperature Measurements (At Ambient 50 °C)		
Component	Max Temperature ℃	
T1 Coil	120 °C	
L3 Coil	120 °C	
Q7 Body	120 °C	
Q102 Body	120 °C	
C20	105 °C	
C102	105 °C	

## Service Life

The estimated service life of the GSP500PSxx Series is determined by the cooling arrangements and load conditions experienced in the end application. Due to the uncertain nature of the end application this estimated service life is based on the actual measured temperature of a key capacitors with in the product when installed by the end application. The worst case of the two figures should be taken as the indicative service life in 24/7 operation.

The graph below expresses the estimated lifetime of a given component temperature and assumes continuous operation at this temperature.

## **Estimated Service Life vs Component Temperature**

