



PART No.	Threads	F	H	T	C
3100/101/1	4-40	0.241	.114	0.014	0.180
6-32 AJ6	6-32	5/16	9/64	1/64	0.200
8-32 AJ6	8-32	3/8	5/32	1/64	0.250
10-24 AJ6	10-24	3/8	5/32	1/64	0.280
10-32 AJ6	10-32	3/8	5/32	1/64	0.280
1/4-20 AJ6	1/4-20	7/16	7/32	1/64	0.365
1/4-28 AJ6	1/4-28	7/16	7/32	1/64	0.365
5/16-18 AJ6	5/16-18	1/2	17/64	1/64	0.400
5/16-24 AJ6	5/16-24	1/2	17/64	1/64	0.400
3/8-16 AJ6	3/8-16	9/16	21/64	1/64	0.475
3/8-24 AJ6	3/8-24	9/16	21/64	1/64	0.475
7/16-20 AJ6	7/16-20	11/16	3/8	1/32	0.575
1/2-13 AJ6	1/2-13	3/4	27/64	1/32	0.650
1/2-20 AJ6	1/2-20	3/4	27/64	1/32	0.650
5/8-18 AJ6	5/8-18	15/16	35/64	1/32	0.787
3/4-10 AJ6	3/4-10	1-3/32	41/64	1/32	0.900
5/8-24 AJ6	5/8-24	15/16	35/64	1/32	0.787
3/8-32 AJ6	3/8-32	9/16	21/64	1/64	0.475
5/8-11 AJ6	5/8-11	15/16	35/64	1/32	0.787
3/4-16 AJ6	3/4-16	1-3/32	41/64	1/32	0.900
7/16-14 AJ6	7/16-14	11/16	3/8	1/32	0.575

NOTES:  
DIMENSIONS ARE IN INCHES.

REV.	DESCRIPTION			DATE
	MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.	TITLE: <b>ADJUST-A-SEAL</b>	ENG. DAN LAW	02.15.13
			DWN. DAN LAW	02.15.13
			CHKD. KEN F.	02.15.13
MAT'L	GRADE 5 OR 8	APM-HEXSEAL CORPORATION	SCALE	DWG. NO. 3100/101/G/ASSY
FINISH:	ZINC PLATED			